

Meter Accessories

For the DP41, DP24, DP25, DP26, DPF50, DPF400, DPF701, DPF5100, PTC41, DP116, DP119 and the iSeries

BUMPER BAND® Color-Coded Protective Guards

Bumper Band guards are made from a flexible material designed to provide additional moisture protection and protect against accidents. Available in 1/8 and 3/64 DIN sizes, Bumper Band guards are compatible with DP40 Series and DP24, DP25, DP26, DP119 and DP116 Series meters. Guards are available in gray, yellow, black, blue, green, red, orange, purple and white.



To Order Visit omega.com/spc_meter_acc for Pricing and Details

Model No.	Size
DP40-BB(*)	1/8 DIN
DP116-BB(*)	3/64 DIN

Panel Punches Available, Visit omega.com/panelpunches

*Specify color code: “-GY” (gray), “-YL” (yellow), “-BK” (black), “-BL” (blue), “-GR” (green), “-RD” (red), “-OR” (orange), “-VL” (purple) or “-WH” (white).
Ordering Example: DP40-BB-YL, yellow protective guard for 1/8 DIN meters.



PATENTED

Tilt Bench Stand DP41-TBS (DP41 Series Only)

DP41-TC, thermocouple thermometer. See omega.com/dp41

KMTXL-125G-6 thermocouple probe, (sold separately). Visit omega.com/kmtxl_nmtxl.

Convert Your DP41 High-Performance Panel Meter into a Benchtop Meter!

Economical Tilt Bench Stand
 The DP41-TBS allows the DP41 to be used as a benchtop meter at fixed angles, or it can act as a carrying handle to facilitate moving the meter.

Splash-Proof Covers
 Splash-proof covers provide additional protection for instruments. Following NEMA 4 (IP66) guidelines for windblown dust and rain, splashing water and hose-directed water, SPC covers form a protective seal around the instrument bezel. Available in 1/4, 1/8, 1/16 and 3/64 DIN sizes for compatibility with most panel meters.

To Order Visit omega.com/spc_meter_acc for Pricing and Details

Model No.	Size
SPC364	3/64 DIN cover (DP116 & DPF50 Series)
SPC116-S	For 1/16 DIN square cover
SPC116-R	For 1/16 DIN rectangular cover
SPC14	1/4 DIN cover, spring-clip-mounted
SPC18	1/8 DIN cover, spring-clip-mounted
SPC4	1/8 DIN cover, thumb-screw-mounted
DPP-2	3/64 DIN panel punch
DPP-4	1/16 DIN square panel punch
DPP-5	1/8 DIN panel punch

Ordering Examples: SPC116-S splash-proof cover for 1/16 DIN square meters.
 DPP-5, panel punch for 1/8 DIN cut out.

