

# General Purpose Micro-Fog Air Line Lubricators for Compressed Air


L07-200-MPAA

- ✓ Compact Design with 360° Visibility Sight-Feed Dome
- ✓ Provides Air Line Lubrication to One or More Air Tools or Devices
- ✓ Screw on Transparent Polycarbonate Bowl
- ✓ Bowl Size 31 ml (1 fl oz)
- ✓ Disassemble Without Tools or Removal From the Air Line
- ✓ ¼" PTF Gauge Ports
- ✓ Minimum Flow Requirement 0.24 dm<sup>3</sup>/s (0.5 scfm) @ 6.3 bar (90 psig)
- ✓ Maximum Pressure 10 bar (150 psig)

General purpose micro-fog air line lubricators are designed for in-line use as a single source lubrication for compressed air. These micro-fog lubricators have a 360° visible sight-feed dome for easy adjustment and monitoring. They include PTF threads, screw on-off transparent bowl which holds 31 ml (1 fl oz), and require a minimum air flow of 0.24 dm<sup>3</sup>/s (0.5 scfm) at 6.3 bar (90 psig). They are suitable for a wide range of pneumatic air line tools and components. These units can be panel mounted with a 30 mm (1.19") diameter mounting hole or can be used with the optional bracket and panel nut.



L07-200-MPAA, shown actual size.



## SPECIFICATIONS

### Operating Temperature\*:

-20 to 50°C (0 to 125°F)

Maximum Pressure: 10 bar (150 psig)

### Materials:

Body: Zinc

Bowl: Transparent polycarbonate

Sight-Feed Dome: Transparent nylon

Elastomers: Neoprene and nitrile

\* Air supply must be dry enough to avoid ice formation at temperatures below 2°C (35°F)

## To Order

MODEL NO.	PORT (in)	FLOW dm <sup>3</sup> /s (scfm)	WEIGHT kg (lb)
L07-200-MPAA	¼	6.7 (14)	0.13 (0.28)
ACCESSORY			
OM-AIR-18-025-003	Mounting bracket and plastic panel nut		

Ordering Example: L07-200-MPAA, general purpose micro-fog air line lubricator with ¼" port, 360° sight-feed dome, and transparent bowl and OM-AIR-18-025-003, mounting bracket with panel nut.