OMEGA-FLO® PVC SOLENOID VALVES FOR CORROSIVE APPLICATIONS

SPECIFICATIONS

1/2 to 2 NPT

SV-10 Series Starts at


\$540



- Ideal for Corrosive or Ultra-Pure Processes
- ✓ Single Power Operation
- ✓ Simple Installation
- ✓ Low-Noise Levels
- ✓ Tight Shut-Off
- Manual Override Standard
- Normally Closed

The SV-10 Series solenoid valves for corrosive applications use only plastic or elastomeric materials: PVC for the body, EPDM (standard) and FKM (optional) for isolating and main diaphragms, and a fully epoxyencapsulated pilot solenoid actuator. The pilot actuator has a pivoted armature design, which hermetically isolates the fluid medium from the armature. The magnetic forces generated are optimized mechanically using the lever principle.

The design of these valves reduces noise and the likelihood of water hammer. The main seat seal is a stable, long-lasting flat diaphragm that provides a tight shut-off at the valve seat. SV-10 Series valves are ideally suited for the control of difficult fluids, such as pure water, demineralized water, seawater, acids of medium concentration, salt solutions, and alkaline washing and bleaching dyes.



depend on orifice and operation of the

valve as well as on pressure and

viscosity of the medium.

Cycling Rate: Approx.

10 to 50 cpm

Duty Cycle: Continuous (100%)

Electrical Connection: F-type connector

42

28

0

Pressure Temperature Graph

126
112
98
84
70
56

PVC

Temperature (Medium)°F

104 122 140 158 176

SV-11, \$540, shown smaller than actual size.

Recommended Reference Book:
Valve Handbook,
FW-306, \$135.
See Section Y for Additional Books

Normally Closed Valves

MOST POPULAR MODEL HIGHLIGHTED!

To Order (Specify Model Number)						
Model No.	Price	Port Connection (NPT)	Cv	Orifice Diameter	Pressure Range (psi)	Weight kg (lb)
SV-11*	\$540	1/2	5.8	9/16"	7 to 85	0.6 (1.4)
SV-12	530	3/4	7.0	3/4"	7 to 85	0.8 (1.8)
SV-13*	545	1	16.3	1"	7 to 85	1.2 (2.6)
SV-14	713	11/4	18.6	11/4"	7 to 85	1.2 (2.6)
SV-15*	700	11/2	35.0	11/2"	7 to 85	2.2 (4.9)
SV-16	905	2	41.9	2"	7 to 85	2.2 (4.9)

Comes complete with operator's manual and mating connector.

Ordering Examples: SV-11, ½ NPT PVC solenoid valve, for $\%_{16}$ " orifice, \$540. SV-13-NO, 1 NPT PVC solenoid valve, for 1" orifice, normally open, \$545.

^{*}To order with, normally open contacts, add suffix "**-NO**" to model number, no extra charge (SV-12, SV-14, and SV-16 not available with normally open option).

Your One-Stop Source for Process Measurement and Control!

One Omega Drive | Stamford, CT 06907 | 1-888-TC-OMEGA (1-888-826-6342) | info@omega.com

www.omega.com



UNITED STATES

www.omega.com 1-800-TC-OMEGA Stamford, CT.

CANADA

www.omega.ca Laval(Quebec) 1-800-TC-OMEGA

GERMANY

www.omega.de Deckenpfronn, Germany 0800-8266342

UNITED KINGDOM

www.omega.co.uk Manchester, England 0800-488-488

FRANCE

www.omega.fr Guyancourt, France 088-466-342

CZECH REPUBLIC

www.omegaeng.cz Karviná, Czech Republic 596-311-899

BENELUX

www.omega.nl Amstelveen, NL 0800-099-33-44



More than 100,000 Products Available!

Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters