## **SELF-REGULATING IMMERSION HEATERS**

## With Stainless Steel or PFA-Covered Stainless Steel Sheaths





**VP Series** 

## **VP and VPT Series**

- Self-Regulating, Fully Grounded
- ✓ Stainless Steel—or PFA-Covered Stainless Steel Sheaths
- ✓ Solid State Heating Element, Temperatures Up to 100°C (212°F)
- Auto-Stabilized Temperature Ensures Uniform Heating
- Lightweight, Easy to Handle, Rapid Heating

The OMEGA® VP and VPT Series self-regulating, fully grounded immersion heaters are ideal for insertion into small tanks, vessels, and appliances as well as into compressors, oils, fluids, and plating cells. Available in stainless steel or a PFA sheath for corrosive environments, both models are shatterproof; are grounded with a 3-wire, 1.2 m (4') long power cord; and have a solid state heating element. Best suited for applications in which heating, excess temperature-protection controls, and regulating components must be fitted in a small space, these heaters are lightweight, easy-to-handle, rapid-heating [maximum surface temperature is 100°C (212°F) units designed not to overheat. Auto-stabilized temperature prevents hot spots, thereby ensuring uniform heating. Accessories include a ½ NPT PVDF screw plug adapter that holds the heater securely in place, and a polypropylene mounting flange that permits vertical suspension of the heater into small vessels.





Polypropylene mounting flange allows vertical suspension

## **SPECIFICATIONS**

Wattage:

VP-107, VPT-107: 100 VP-311, VPT-311: 300

Voltage:

120 or 240 Vac

**Power Leads:** 

**VP-107, VPT-107:** 1.2 m (4') power cord with 3-prong plug (no plug on 240V models);

**VP-311, VPT-311:** 0.9 m (3') flexible conduit and fitting with 3-conductor leads

**Sheath Length:** 

VP-107, VPT-107: 179 mm (7") VP-311, VPT-311: 279 mm (11")

**Heated Length:** 

VP-107, VPT-107: last 76 mm (3") VP-311, VPT-311: last 152 mm (6")

Diameter:

VP Series: 11 mm (%6") VPT Series: 13 mm (½")

Shipping Weight: Approx. 453 g (1 lb)

To Order	
Single-Element Heater	
Model No.	Description
VP-107/*	100 W stainless steel sheath immersion heater
VP-107-ADAP	½ NPT PVDF screw plug adaptor for VP-107/* immersion heater
VPT-107/*	100 W stainless steel sheath immersion heater with PFA covering
VPT-107-ADAP	½ NPT PVDF screw plug adaptor for VPT-107/* immersion heater
VPT-107-FLGE	Polypropylene mounting flange (used with VP-107-ADAP or VPT-107-ADAP)
Dual-Element Over-the-Side Small Tank Heater	
VP-311/*	300 W stainless steel sheath immersion heater
VPT-311/*	300 W stainless steel sheath immersion heater with PFA covering

<sup>\*</sup> Designate voltage (i.e., insert "**120V"** for 120 Vac or "**240V"** for 240 Vac).

Ordering Example: VPT-107/120V, 120 Vac, 100 W, PFA-covered immersion heater.

VP-311/240VAC, 300 W stainless steel sheath immersion heater.