

COMPACT STEAM BOILER

CMB Series





- Steam Pressures to 90 psig
- Steam Capacity (9 to 45 lb/Hr @ 0 to 90 psig)
- 3 to 15 kW (10 to 51 Mwh)
- 120, 208, 240 and 480V, 1 and 3 Phase
- ASME Section I Pressure Vessel Carbon Steel Code "M" (100 psig)
- 0.430" Dia. Copper Sheath Heating Elements with Run Dry Protection
- Automatic Mechanical Float Valve Water Feeder with Inlet Check Valve³
- Electronic Low Water Cutoff (Single Probe)
- Water Level Sight Glass and Blow Down Drain Valve
- Pressure Gauge (0 to 160 psig)
- ASME Safety Relief Valve

Steam Pressure Gauge provides visual indication of steam pressure.

Mechanical Float Valve Water Feeder can be connected directly to water main, eliminating complicated feed water piping³.

Water Level Sight Glass allows constant visual observation of water level in the generator.

Safe, Reliable Operation is assured by a separate low water cutoff that shuts down the generator if it accidentally runs low on water.



APPLICATIONS

CMB Low Pressure Steam Generator — Delivers 9 to 45 lb of steam per hour at 0 to 90 psig, and is used in many manufacturing processes. The CMB's small size and small capacity make it an ideal "point of use" steam source in industrial plants, computer rooms, laboratories, hospitals, jewelry stores, steam rooms and other spot heating applications. The CMB is also ideal for stand-by operations which require small amounts of steam or humidification during off season periods when the main plant boiler may be shut down. All CMB steam generators are inspected to rigid quality standards. They are factory tested under operating conditions and are ready to operate.

FEATURES

Pressure/Temperature Control easily adjusts operating pressure.

Pilot light indicates when boiler is on and element is heating.

To Order

Steam ₁ lb/Hr	Bhp	kW	Volts ₂	Ph	Dimensions (in)			Model No.	Wt. (lb)
					W	L	H		
9	0.3	3	120	1	17	15	23	CMB-3/120/1P	68
9	0.3	3	208	1	17	15	23	CMB-3/208/1P	68
9	0.3	3	240	1	17	15	23	CMB-3/240/1P	68
9	0.3	3	208	3	17	15	23	CMB-3/208/3P	68
9	0.3	3	240	3	17	15	23	CMB-3/240/3P	68
9	0.3	3	480	3	17	15	23	CMB-3/480/3P	68
18	0.61	6	208	1	20	30	37	CMB-6/208/1P	165
18	0.61	6	240	1	20	30	37	CMB-6/240/1P	165
18	0.61	6	480	1	20	30	37	CMB-6/480/1P	165
18	0.61	6	208	3	20	30	37	CMB-6/208/3P	165
18	0.61	6	240	3	20	30	37	CMB-6/240/3P	165
18	0.61	6	480	3	20	30	37	CMB-6/480/3P	165
27	0.91	9	208	3	20	30	37	CMB-9/208/3P	165
27	0.91	9	240	3	20	30	37	CMB-9/240/3P	165
27	0.91	9	480	3	20	30	37	CMB-9/480/3P	165
36	1.22	12	208	3	20	30	37	CMB-12/208/3P	165
36	1.22	12	240	3	20	30	37	CMB-12/240/3P	165
36	1.22	12	480	3	20	30	37	CMB-12/480/3P	165
45	1.52	15	208	3	20	30	37	CMB-15/208/3P	165
45	1.52	15	240	3	20	30	37	CMB-15/240/3P	165
45	1.52	15	480	3	20	30	37	CMB-15/480/3P	165

Ordering Examples: CMB-6/240/1P, 240V, 1 phase heater.

CMB-12/208/3P, 208V, 3 phrase heater.

1. At 212°F with 50°F feed water. 2. Other voltages are available. 3. For proper operation, the automatic water feed control unit requires a water supply pressure of 10 psig greater than the operating pressure of the steam generator.