

High-Temperature Jack Panels

For Standard Ceramic Connectors

NHJP Series

For Rugged
NHX or UHX
Ceramic
Connectors



OMEGA high-temperature jack panels feature ceramic connectors mounted in a steel plate for service temperatures up to 538°C (1000°F). These panels with UHX connectors are ideal when glazed ceramic or nylon connector panels would contaminate a vacuum system.

- ✓ For Rugged NHX or UHX Ceramic Connectors
- ✓ Heavy-Duty Steel Panel
- ✓ Compensated Hardware

Shown actual size.
All OMEGA® NHJP jack panels are shipped unassembled




CASS-18G-12-NHX.

PRICE AND QUANTITY DISCOUNT INFORMATION

Prices shown are for J, K, T, E, R, N, S, G, C, D, and U calibrations. To price more than one panel of any type, contact sales.

Use connector quantity discount schedule to determine pricing. Panel prices are not discounted.



Circuits Per Row (mm/inch)		1 Row 67 mm H (2 ⁵ / ₈ ")	2 Rows 111 mm H (4 ³ / ₈ ")	3 Rows 156 mm H (6 ¹ / ₈ ")	4 Rows 200 mm H (7 ⁷ / ₈ ")
6 145 L (5 ³ / ₄ ")	Model No.	NHJP1-06-[*]	NHJP2-12-[*]	NHJP3-18-[*]	NHJP4-24-[*]
12 260 L (10 ¹ / ₄ ")	Model No.	NHJP1-12-[*]	NHJP2-24-[*]	NHJP3-36-[*]	NHJP4-48-[*]
18 375 L (14 ³ / ₄ ")	Model No.	NHJP1-18-[*]	NHJP2-36-[8]	NHJP3-54-[*]	NHJP4-72-[*]

Note: All OMEGA® NHJP jack panels are shipped unassembled, with all necessary hardware for mounting included. Male connectors can be supplied in place of the female jacks. Consult Sales Department. Upper temperature limit is determined by alloy type.

*Insert J, K, T, E, R, N, S, G, C or D thermocouple calibration.

Ordering Example: NHJP1-18-K, single-row high-temperature jack panel with Type K connector.