

OMEGABUS® Digital Transmitters



D1000 and D2000 Series



- ✓ Complete Sensor to RS232C or RS485 Interface
- ✓ Input Modules for Thermocouples, RTDs, Voltages, Currents, Pulse and Frequency, and Bridge Inputs
- ✓ Isolated Inputs
- ✓ RS485 Format Permits Remote Communications up to 4000'
- ✓ D2000 Series Provide Linearization of Non-Standard Sensors
- ✓ Connect Up To 32 Modules On One Cable, Up to 124 Using a Repeater
- ✓ Alarm Outputs Standard
- ✓ Continuous Self Calibration, No Adjustment Requirements



The D1000 and D2000 Series digital transmitters are a complete family of easy to use interface modules for personal computers and other processor based equipment with standard serial I/O ports. The modules convert analog input signals to engineering units and transmit, in ASCII format, to any host computer with a standard RS-232C or RS-485 port. This modular design enables anyone familiar with a personal computer to construct a flexible and cost effective data acquisition system.

These modules can measure temperature, pressure, flow, voltages, currents and various types of digital signals. The D1000 series provide direct interface to a wide variety of sensors and perform all signal conditioning, scaling, linearization and conversion to engineering units. Each module also provides digital I/O lines for controlling devices through solid state relays or TTL signals. These digital I/O lines along with integral limit setting capability provide alarm and control outputs. With the exception of the D1400 RTD and D1500 bridge modules, every D1000 module contains an on-board event counter. The event counter will count up to ten million transitions on the digital input line.

All user selectable options (address, baud rate, alarms, etc.) are done through the communications port and stored in nonvolatile memory thereby eliminating switches or external adjustments of any kind.

The flexibility of this system allows users to mix and match the modules to fit their exact requirements. As many as 124 modules can be connected on one 4 wire cable. They can be placed remote from the host computer and from each other.

The D2000 series of user-programmable data acquisition and control modules allow direct interface of non-linear analog sensors to computers with serial I/O ports.



D1000 and D2000 Modules are Easily Arranged in Multidrop Fashion for Multiple Inputs

Use of these modules enables downloading up to 23 breakpoints through the communications port. With these breakpoints the user can program a module to virtually any transfer function.

The ability to provide an arbitrary user programmable nonlinear transfer function is the most powerful feature of the D2000 series. Use this feature to linearize non-standard sensors or to provide outputs in engineering units, which are nonlinear to the input. The D2000 series can be programmed to approximate square law, root, log, high-order polynomial or any other non-linear function.

The D2000 may also be empirically field-programmed when the exact transfer function is unknown.

If transmitting long distances is required, selection of the RS-485 communications format is encouraged. This permits remote operation of up to four thousand feet from the host computer. For computers which do not include a RS-485 port, OMEGA offers the A1000 RS-232C signal converter.

The modules are also capable of operating in a multidrop fashion supporting up to 32 units one one cable set. The A1000 may also be used as a repeater to allow as


many as 124 modules to be joined together. A utility software package (for IBM PC or compatibles) is also available. This software eliminates the need for programming skills to easily communicate with the modules. This software package is available upon request at no charge. Request model D1000-SW, for D1000, D2000, D3000 and D4000 models. (One per order).

All modules are supplied with screw terminal plug connectors and captive mounting hardware. Their encapsulated design allows for mounting in virtually any location including explosion proof housings and DIN rails.

Input Modules For Virtually Any Process Monitoring Application



Shown in Multidrop Fashion



Common Specifications

ANALOG

- ✓ Single channel analog input
- ✓ Analog Input isolation to 500 VRMS
- ✓ 15-bit measurement resolution
- ✓ 2 samples/sec throughout
- ✓ Autozero & autocalibration

DIGITAL

- ✓ 8-bit CMOS microcomputer

COMMUNICATIONS

- ✓ RS-232C, RS-485
- ✓ Up to 124 multidrop modules per communications port
- ✓ ASCII Format command/response protocol
- ✓ Can be used with 'dumb' terminal
- ✓ Parity options: odd, even, none
- ✓ All communications setups stored in memory
- ✓ Checksum can be added to any command or response
- ✓ User selectable channel address
- ✓ Selectable baud rates: 300, 600, 1200, 2400, 4800, 9600, 19.2 K, 38.4 K

Power Requirements: 10 to 30 Vdc, 0.75 W max

Case: ABS with captive mounting hardware

Connectors: Screw terminal plug (supplied)

TEMPERATURE RANGE

Operating: -25 to 70°C

Storage: -25 to 85°C

Relative Humidity: 0 to 95% noncondensing

Specifications for Specific Modules

D1100/D2100 VOLTAGE INPUT MODULES

Voltage Ranges: ±10 mV, ±100 mV, ±1V, ±5 V, ±10 Vdc, ±100 Vdc

Resolution: 0.01% of FS (4 digits)

Accuracy: ±0.02% of FS max

Zero Drift: ±1 count max (auto zero)

Span Tempco: ±50ppm/°C max

Input Burnout Protection: 250 Vac
Input Impedance: 1 MΩ min (≥ ±5V input), 100MΩ min (≤ ±1V input)

1 Digital Input/Event Counter, 2 Digital Outputs

D1200/D2200 Current Input Modules

Current Ranges: ±1 mA, ±10 mA, ±100 mA, ±1A, 4 to 20 mA dc

Resolution: 0.01% of FS (4 digits), 0.04% of FS (4-20 mA)

Accuracy: ±0.02% of FS, 0.04% of FS (4-20 mA)

Zero Drift: ±1 count max. (autozero)

Span Tempco: ±80 ppm/°C max

Voltage Drop: ±0.1V max

1 Digital Input/Event Counter, 2 Digital Outputs

D1300 THERMOCOUPLE INPUT MODULES

- ✓ Open thermocouple indication
- ✓ Input burnout protection to 250 Vac
- ✓ User selectable °C or °F
- ✓ Overrange indication
- ✓ Automatic cold junction compensation and linearization

Thermocouple Types: J, K, T, E, R, S, B, C

RANGES:

J = -200 to 760°C;

K = -150 to 1250°C;

T = -200 to 400°C;

E = -100 to 1000°C;

B = 0 to 1820°C;

S = 0 to 1750°C;

R = 0 to 1750°C;

C = 0 to 2315°C

Resolution: ±1.0°

Overall Accuracy From 0 to +40°C

Ambient: ±1.0°C max (J, K, T, E), ±2.5°C max (R, S, B, C)

Input Impedance: 100 MΩ min.

Lead Resistance Effect: <20μ V per 350Ω

2 Digital Inputs, Event Counter, 3 Digital Outputs

D1400 RTD INPUT MODULE

- ✓ Input protection to 120 Vac
- ✓ Automatic linearization and lead compensation
- ✓ User selectable °C or °F



D1500 Bridge Input Modules are ideally suited for most load cells. See OMEGA's Pressure, Strain and Force Handbook for a complete line of load cells.

RTD Types: α = .00385, .00392, 100 Ω @ 0°C

Ranges: .00385 = -200 to 850°C; .00392 = -200 to 600°C

Resolution: 0.1°

Accuracy: ±0.3°C

Input Connections: 2, 3, or 4 wire

Excitation Current: 0.25 mA

Lead resistance effect: 3 wire -2.5°C per Ω of unbalance; 4 wire - negligible

Max Lead Resistance: 50Ω

1 Digital Output D1450 THERMISTOR INPUT

Range: 0 to 100°C
Thermistor Type: 2252Ω
Accuracy: ±0.2°C
Resolution: 0.01°C/°F
Input Protection: 30 Vdc

1 Digital Input/Event Counter, 2 Digital Outputs

D1500/2500 BRIDGE INPUT MODULE

Range: ±30, ±100 mV, 1 to 6 Vdc
Accuracy: ±0.05% of FS max
Resolution: 10 μV (mV spans), 0.02% FS (V span)
Common Mode Rejection: 100 dB at 50/60 Hz

Input Protection: 30 Vdc
Excitation Voltage: 10 V, 5 Vdc
1 Digital Output

D1600/D2600 TIMER AND FREQUENCY INPUT MODULES

The D1600 module has two modes: frequency input with output data in hertz, or timer input with output data in seconds

Input impedance: 1 MΩ
Switching Level: Selectable 0V, 2.5V
Hysteresis: adjustable 10 mV to 1.0V
Input Protection: 250 Vac
1 Digital Input/Event Counters
FREQUENCY INPUT

Range: 1 Hz to 20 kHz
Accuracy: ±0.01% of reading, ±0.01 Hz
Resolution: 0.005% of reading, 0.01 Hz
Resolution: 0.01% (4 digits)
Tempco: ±20 ppm/°C

TIMER INPUT

Range: 100 μs to 30 s
Resolution: 0.005% of reading +10 μs
Accuracy: ±0.01% of reading ±10 μs
EVENT COUNTER

Input Bandwidth: 60 Hz,
(optional 20 KHz max)
 Up to 10 million positive transitions

D1700 DIGITAL INPUTS/OUTPUTS MODULE

D1711, D1712: 15 digital input/output bits, user can define any bit as an input or an output

Input Voltage Levels: 0 to 30V without damage

Input Switching Levels: High, 3.5V min., Low, 1.0V max

Outputs: Open collector to 30V, 100 mA max load

Vsat: 1.0V max @ 100 mA



Voltage, current and bridge input modules are readily interfaced to most pressure transducers. See OMEGA's Pressure, Strain and Force Handbook for a complete line of pressure transducers.

D1701, D1702: 7 DIGITAL INPUTS AND 8 DIGITAL OUTPUTS

Input Voltage Levels: ±30V without damage
Input Switching Levels: high, 3.5V min, low, 1.0V max

Outputs: Open collector to 30V, 30 mA max load
Vsat: 0.2V max @ 30 mA
 Internal pull up resistors for direct switch input
 Inputs/Outputs are read/set in parallel

Digital Inputs/Outputs		
RS232C Output	RS485 Output	Description
D1701	D1702	7 Digital in, 8 digital out
D1711	D1712	15 Digital in/out

Frequency, Time and Event Inputs		
RS232C Output	RS485 Output	Description
D1601	D1602	Frequency input
D1611	D1612	Timer input
D1621	D1622	Event counter

Voltage Inputs		
RS232C Output	RS485 Output	Input
D1101	D1102	10 mV
D1111	D1112	100 mV
D1121	D1122	1V
D1131	D1132	5V
D1141	D1142	10V
D1151	D1152	100V

Current Inputs		
RS232C Output	RS485 Output	Input
D1211	D1212	10 mA
D1221	D1222	1 mA
D1231	D1232	100 mA
D1241	D1242	1 A
D1251	D1252	4 to 20 mA

Thermocouple Inputs		
RS232C Output	RS485 Output	Input
D1311	D1312	J
D1321	D1322	K
D1331	D1332	T
D1341	D1342	E
D1351	D1352	R
D1361	D1362	S
D1371	D1372	B
D1381	D1382	C

RTD Inputs		
RS232C Output	RS485 Output	Input Curve
D1411	D1412	0.00385
D1421	D1422	0.00392

Thermistor Inputs		
RS232C Output	RS485 Output	Description
D1451	D1452	2252 Ω thermistor

Bridge Inputs			
RS232C Output	RS485 Output	Input	Excitation
D1511	D1512	30 mV	5V
D1521	D1522	30 mV	10V
D1531	D1532	100 mV	5V
D1541	D1542	100 mV	10V
D1561	D1562	1 to 6 V	10V

Comes complete with operator's manual on CD and Windows setup software.
 D1000 Series digital transmitters are also available with Modbus RTU protocol.
 To order transmitters Modbus RTU protocol, add suffix "M" at the end of the model number, no additional charge.

Ordering Example: D1311 type J thermocouple input RS-232C output digital transmitter and OCW-1, OMEGACARESM extends standard 1-year warranty to a total of 2 years.

OMEGABUS[®] Digital Transmitters D1000 and D2000 Models

D2000 Series Transmitter Modules

To Order		
Voltage Inputs		
RS232C Output	RS485 Output	Input
D2111	D2112	100 mV
D2121	D2122	1V
D2131	D2132	5V
D2141	D2142	10V

Pulse and Frequency Inputs		
RS232C Output	RS485 Output	Input
D2601	D2602	Frequency
D2611	D2612	Pulse

Current Inputs		
RS232C Output	RS485 Output	Input
D2221	D2222	1 mA
D2211	D2212	10 mA
D2231	D2232	100 mA
D2241	D2242	1 A
D2251	D2252	4 to 20 mA

Bridge Inputs			
RS232C Output	RS485 Output	Input	Excitation
D2511	D2512	30 mV	5V
D2521	D2522	30 mV	10V
D2531	D2532	100 mV	5V
D2541	D2542	100 mV	10V



Shown in Multidrop Fashion



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

