



Wireless Humidity and Temperature Transmitter Part of the NOMAD® Family OM-CP-RFRHTEMP101A

Starts at
\$269



- Measure Dew Point and Vapor Concentration
- Multiple Transmitter Configurations
- Automatically Converts a PC into a Strip Chart Recorder
- Programmable Start Time
- Memory Wraparound

The OM-CP-RFRHTEMP101A is a miniature, wireless, battery-powered, standalone humidity and temperature transmitter. This portable, easy-to-use device will read and transmit temperature and humidity measurements to the host computer, where the data can be analyzed in real-time. These readings are also logged to the device's memory for added data security. The convenient slide switch turns the transmitter on or off. Data is received at the PC using the OM-CP-RFC101A receiver, which attaches directly to the serial port. All received data is time and date stamped and stored directly in the PC.

The OM-CP-RFRHTEMP101A is a major leap in both size and performance. Its small size allows it to fit almost anywhere. Numerous units can be used to transmit data to the same receiving station. The Windows software converts a PC into a real-time strip chart recorder. Data can be printed in graphical and tabular format or exported to a text or Microsoft Excel file.

Specifications

Temperature Sensor: Semiconductor

Temperature Range: -30 to 70°C (-22 to 158°F)


Temperature Resolution: 0.1°C
Calibrated Accuracy: ±0.5°C, 0 to 50°C (32 to 122°F)

HUMIDITY CHANNEL

Humidity Sensor: Semiconductor
Humidity Range: 0 to 100% RH non-condensing

Humidity Resolution: 0.5% RH

Calibrated Accuracy: ±3% RH (±2% RH typical at 25°C)



Response Time: 90% change in 60 seconds in slow moving air
Calibration: Digital calibration through software
Start Time: Software-programmable start time and date (up to 6 months in advance)
Real-Time Recording: Transmits data to PC to monitor and record data in real-time
Memory: 5461 readings per channel

TEMPERATURE/HUMIDITY

Reading Interval: 1 reading every 30 seconds to 1 every 12 hours
Data Format: Date and time stamped; °C, °F, °K, °R; % RH, mg/ml of water concentration
Time Accuracy: ±1 minute/month [at 20 to 30°C (-4 to 86°F)]
Computer Interface: PC serial, RS-232C COM or USB (interface cable required); 57,600 baud
RF Baud Rate: 4800 baud
RF Carrier Communication: 418 MHz

OM-CP-RFRHTEMP101A, \$269, shown larger than actual size



Range: 36 m (120') line of sight
Power: 3.6 V lithium battery (included)
Battery Life: 1 year typical (1 minute reading rate @ 25°C)
Software: XP SP3/Vista and 7 (32-bit and 64-bit)
Operating Environment: -30 to 70°C (-22 to 158°F) 5 to 95% RH non-condensing
Dimensions: 20 H x 42 W x 68 mm D (0.8 x 1.7 x 2.7")
Weight: 60 g (2 oz)
Enclosure: ABS plastic

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description
OM-CP-RFRHTEMP101A	\$269	Wireless humidity and temperature data logger
OM-CP-RFRHTEMP101A-CERT	329	Wireless humidity and temperature data logger with NIST calibration certificate
OM-CP-RFC101A	199	Receiver package includes RF receiver, 1.22 m (4') RS-232 cable with DB9F termination, Windows software and operator's manual
OM-CP-RFC200A	249	Receiver package includes RF receiver, 3.7 m (12') USB cable, Windows software and operator's manual
OM-CP-BAT105	12	Replacement 3.6 V lithium battery

The OM-CP-RFC200A receiver package is required to operate the wireless transmitter. NIST calibration for temperature only.
Ordering Example: OM-CP-RFRHTEMP101A-CERT wireless humidity temperature transmitter with NIST calibration certificate and OM-CP-RFC200A Windows software, USB cable with receiving antenna, \$329 + 249 = \$578.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters