

# OMB-DBK44

## 2-Channel Multi-Purpose Isolated Signal Conditioning Card for OMB-LOGBOOK and OMB-DAQBOARD-2000 Series

Model OMB-DBK44

**\$319**



- ✓ Accepts Two OM5 Isolated Input Signal Conditioning Modules of Any Type
- ✓ Features On-Board Screw-Terminal Signal Connections

The OMB-DBK44 two-channel multi-purpose isolated signal conditioning card allows OMEGA's OMB-LOGBOOK and OMB-DAQBOARD-2000 Series data acquisition systems to accommodate two optional OM5 isolated signal conditioning modules of any type\*. Each user-configurable signal conditioning module offers 500 V isolation from the system and from other channels. It can accommodate an array of signals—from low-level thermocouple signals to strain gage signals.

The OMB-DBK44 features screw terminals that provide access to each channel's analog inputs, as well as to the excitation output if the card is used with a strain gage or RTD module. In addition, each OMB-DBK44 channel has a cold-junction sensor mounted adjacent to each screw terminal block. This permits OM5 thermocouple modules to output linearized and compensated temperature.


### Expansion Enclosures

The OMB-DBK44 can be housed in a variety of ways, such as in the OMB-DBK10 three-slot expansion-card enclosure, the OMB-DBK41 ten-slot analog expansion module, or within the expansion slot of an OMB-DAQBOOK-112 or OMB-DAQBOOK-216.

### Powering the OMB-DBK44

The OMB-LOGBOOK and OMB-DAQBOARD-2000 Series

\*OM5 modules must be purchased separately.



The OMB-DBK44, \$319, 2-channel multi-purpose isolated signal conditioning card

can provide power for the OMB-DBK44 via their P1 connectors. The OM5 modules used with the OMB-DBK44 typically require 5 V at 30 mA minimum, and can demand up to 175 mA in applications requiring excitation voltages.

An external 5 V power supply may be required if the power requirements exceed the data acquisition system's power output. The external 5 V source is connected to the OMB-DBK44 via on-board screw terminal connections.

Please note that for applications that demand more than four isolated channels, it is more economical to use the OMB-DBK42 sixteen-channel isolated module.

### Specifications

**Connector:** DB37 male, mates with P1 pinout on the OMB-LOGBOOK or OMB-DAQBOARD-2000 Series; screw terminals for signal inputs

### User Connections:

- 4 screw-terminals/channel;
- 2 screw-terminals for external 5 Vdc

### ISOLATION

#### Input Power to DAQ System:

0 V

#### Signal Inputs to DAQ System:

1500 Vdc

#### Input Channel-to-Channel:

500 Vdc

**Signal Modules:** Any OM5 series input module; cold-junction sensors for T/C modules are located by each channel terminal block; plug-in locations for Current Loop sensing resistors are provided for each channel

**Module Capacity:** 2 (input only) OM5 modules

**Weight:** .25 kg (8 oz) with no modules installed

**DC Input Fuse:** 4 A

**Cables:** Use OMB-CA-37-x with OMB-LOGBOOK and OMB-DAQBOARD-2000 Series

**AVAILABLE FOR FAST DELIVERY!**

To Order (Specify Model Number)		
Model Number	Price	Description
OMB-DBK44	\$319	2-Channel Multi-Purpose Isolated Signal Conditioning Card

**Ordering Example:** OMB-DBK44 2-channel multi-purpose isolated signal conditioning card, \$319.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters