


OMB-DBK9

8-Channel RTD Measurement Card for OMB-LOGBOOK and OMB-DAQBOARD-2000 Series



Model OMB-DBK9

\$519



OMB-DBK9, \$519, 8-channel RTD card accommodates three- and four-wire RTD's, shown smaller than actual size

- ✓ Provides 8 RTD Channels
- ✓ Supports 3- and 4-Wire RTD's
- ✓ Supports Three Ranges of RTD Resistance
- ✓ Features Resolution Over the Full-Range of -200 to 850°C Span

The OMB-DBK9 is an eight-channel RTD (resistance temperature device) measurement card for OMEGA's OMB-LOGBOOK and OMB-DAQBOARD-2000 Series data acquisition systems. The OMB-DBK9 supports up to 8 channels of 3- or 4-wire RTD's with resistances of 100, 500, or 1000 Ohm. RTD-type selection is made via a jumper on the card that configures all 8 channels.

Excitation Sources

The OMB-DBK9 provides bias for the RTD with eight constant current sources derived from the OMB-LOGBOOK or OMB-DAQBOARD-2000 Series Sinternal power supply.

Input Amplifier

The OMB-DBK9's instrumentation amplifier provides both a high and low resolution gain for each of the standard RTD types.

Software

Included software auto-matically controls the OMB-DBK9 to effortlessly supply you with correct temperature measurements. You need only indicate which RTD type is attached to each channel. Thereafter, whenever a measurement is requested from a channel, the entire measurement procedure including linearization occurs automatically.

The data acquisition systems are shipped with several Windows applications including a datalogging application that allows you to acquire RTD's and other measurements via a spreadsheet-style user interface. Also shipped is eZ-PostView, a post-acquisition application that permits you to display acquired data previously saved to a file.

Specifications

Connector: DB37 male, mates with P1 pinout on an OMB-LOGBOOK, OMB-DAQBOARD-2000; screw terminals provided for signal connections

Configurations: 3- or 4-wire

Alpha: 0.00385

Inputs: 8 channels

Temperature Ranges:

100, 500 or 1000 Ohm:
-200 to 850°C

RTD Excitation Current:

100 Ohm 500 µA
500 Ohm 227 µA
1000 Ohm 160 µA

Accuracy:

100, 500 or 1000 Ohm: ± 1.5°C

Resolution:

100, 500 or 1000 Ohm: 0.3°C

Cables: Use OMB-CA-37-x with OMB-LOGBOOK and OMB-DAQBOARD-2000 Series

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model Number	Price	Description
OMB-DBK9	\$549	8-Channel RTD Input Card

Ordering Example: OMB-DBK9 8-channel RTD input card, \$549.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters