

OMB-DBK40

18-Connector BNC Interface for OMB-LOGBOOK and OMB-DAQBOARD-2000 Series



Model OMB-DBK40

\$419



OMB-DBK40, \$419, 18-connector BNC analog interface, shown smaller than actual size

- ✓ **Features Eighteen BNC Connectors**
- ✓ **Provides Access to Sixteen Analog Inputs and Two Analog Outputs**

The OMB-DBK40 provides a convenient means of attaching analog signals from BNC cables to the OMB-LOGBOOK and OMB-DAQBOARD-2000 Series data acquisition systems.

The OMB-DBK40 features eighteen BNC connectors that accommodate sixteen analog input channels and two analog output channels. One of the OMB-DBK40's BNC connectors can be switch-selected as either the TTL trigger input or as the second analog output channel.

The OMB-DBK40 features a male DB37 connector that mates with the OMB-LOGBOOK or DAQBOARD P1 analog I/O connector.

The OMB-DBK40 also accommodates the five counter-timers when attached to the DAQBOARD P3 connector.

The OMB-DBK40 includes a 1.8 m (6') cable for attachment to an DAQBOARD P1 analog I/O connector or to an DAQBOARD P3 I/O port. Attachment to the DAQBOARD P3 further requires the use of an optional OMB-CA-60 adaptor cable.

Specifications

Connector:

DB37 male, mates with P1 pinout on the OMB-LOGBOOK or OMB-DAQBOARD-2000 Series or with P3 pinout on the DAQBOARD-2000 Series; BNC connectors for signal inputs

Analog Input Connection:

One BNC connector for each of 16 analog input channels

Single-Ended Mode:

Center conductor carries signal; outer conductor carries signal ground

Differential Mode:

Center conductor of 2 adjacent BNC connectors carries input high and input low signals; outer conductor of both is attached to system ground

Analog Output Connection:

One BNC connector for each of 2 analog output channels; center conductor carries signal, outer carries signal ground

TTL Trigger Input Connection:

One analog output BNC connector (J18) can be switched for a TTL trigger input connection; in TTL trigger mode, the second analog output channel is unavailable on the BNC connector

Cable: 1.8 m (6')

Dimensions: 156 x 138 x 60 mm (6.8 x 5.3 x 2.3")

Weight: .6 kg (1 lb, 5 oz)

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

| Model Number | Price | Description |
|--------------|-------|----------------------------|
| OMB-DBK40 | \$419 | 18-Connector BNC Interface |

Ordering Example: OMB-DBK40 is an 18-connector BNC interface, \$419.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters