

OMB-DBK45

4-Channel Simultaneous Sample and Hold Card with Low-Pass Filter

Model OMB-DBK45

\$839



- ✓ **User-Configurable Low-Pass Filter from DC to 50 kHz Cutoff**
- ✓ **Convenient BNC Input Connectors**


The OMB-DBK45 card provides OMEGA's OMB-LOGBOOK and OMB-DAQBOARD-2000 Series data acquisition systems with four differential analog input channels equipped with low-pass filters and simultaneous sample-and-hold.

The OMB-DBK45 provides a wide selection of full scale inputs. Each channel features its own instrumentation amplifier with gain ranges of x1, x10, x100, x200, and x500, as well as individually configurable low-pass filters. This lets you maximize your signal via the OMB-DBK45's input ranges, low-pass filter the output, and simultaneously sample and hold all channels before digitizing with the OMB-LOGBOOK and OMB-DAQBOARD-2000 Series.

Up to sixty-four OMB-DBK45 cards can be attached to one OMB-LOGBOOK and OMB-DAQBOARD-2000 Series, for a total of 256 differential inputs.

Low-Pass Filters

Each OMB-DBK45 channel is equipped with a low-pass filter that is user configured for cut-off frequencies from DC to 50 kHz, and for Butterworth, Chebyshev, or Bessel characteristics. The OMB-DBK45's frequency determining resistor and capacitor locations are on machined-pin IC sockets for maximum flexibility. The card is provided with blank plug-in headers for each channel, to which you can add passive components for particular frequencies.



The OMB-DBK45, \$839, provides 4 channels of simultaneous sample and hold, as well as low-pass filtering

Preconfigured plug-in headers for several preselected cutoff frequencies are optionally available.

Specifications

Connector: DB37 male, mates with P1 pinout on the OMB-LOGBOOK, OMB-DAQBOOK or DAQBOARD data acquisition systems; BNC connectors for signal inputs

Number of Channels: 4
Number of Cards Addressable: 64
Input Type: Differential
Voltage Input Ranges:

- 0 to ± 5 Vdc
- 0 to ± 500 mVdc
- 0 to ± 50 mVdc
- 0 to ± 25 mVdc
- 0 to ± 10 mVdc

Number of Poles/Filter: 3
Types of Filters: Bessel, Butterworth, & Chebyshev
Frequency Range: 0.1 Hz to 50 kHz; the frequency is set by installation of 4 to 6 resistors and/or capacitors in the provided socket locations
Acquisition Time:
 0.6 μ s (10 V excursion to 0.1%);
 0.7 μ s (10 V excursion to 0.01%)

Channel-to-Channel

Aperture Uncertainty: 50 ns
Output Droop Rate: 0.1 μ V/ μ s
Input Gains: x1, 10, 100, 200, 500, & user determined up to 500
Input Offset Voltage:
 [500 + 5000/G] μ V max (nullable)
Input Offset Drift:
 [± 5 + 100/G] μ V/ $^{\circ}$ C max
Input Bias Current: 100 pA max
Input Offset Current: 50 pA max
Input Impedance: 5×10^{12} Ohms parallel with 6 pF (without 100 K bias resistors enabled)
Switchable Bias Resistors:
 100 K each to analog common
Gain Errors:

- x1 0.04% max
- x10 0.1% max
- x100 0.2% max
- x200 0.4% max
- x500 1.0% max

Dimensions: 82 x 209 x 19 mm
 (3.25 x 8.25 x 0.75")

Cables:

Use OMB-CA-37-x with OMB-LOGBOOK and OMB-DAQBOARD-2000 Series

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model Number	Price	Description
OMB-DBK45	\$839	4-Channel Simultaneous Sample and Hold Card with Low-Pass Filter

Ordering Example: OMB-DBK45 is a 4-channel simultaneous sample and hold card with low-pass filter, \$839.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters