


PLASTIC PADDLEWHEEL FLOW METERS



FPB1400 Series



FPB1406-RTD shown smaller than actual size.

- ✓ Easy to Install and Operate
- ✓ Mounts in Any Direction
- ✓ Only One Moving Part
- ✓ Visual Flow Indication
- ✓ Female NPT Ports
- ✓ Polypropylene or PVDF Models

Fluid flowing through the FPB1400 causes the paddlewheel to spin. As the magnets embedded in the paddle spin past the sensor, electrical pulses are produced in which frequency is proportional to the flow rate. The number of pulses per desired time interval and the K-factor (number of pulses/gallon) make it is easy to calculate the flow rate and volume passing through the unit.

SPECIFICATIONS

Accuracy: ±1% FS
Maximum Temperature: 60°C (140°F)
Maximum Pressure: 10 bar (150 psig)
Power: 5 to 24 Vdc @ 2 mA
Output Signal: NPN open collector (load 30 mA maximum)
Body Dimensions:
 56 H x 108 L x 53 mm D
 (2.2 x 4.25 x 2.2")

Cable: Flow 1.8 m (6'), RTD 0.3 m (1') (-RTD models)

RTD: Platinum 0.00385 TCR, meets EN 60751, Class B (-RTD models)

Maximum Pressure Drop: 15 psi on size 2 units 20 psi on all other sizes

Viscosity: Calibrated 1 cSt, up to 50 cSt with field calibration

Response Time: At 1 sec 10 to 90% of full scale, at 2 sec below 10% of full scale

Wetted Materials

Polypropylene Models

Body: Polypropylene
LID: Acrylic
Paddlewheel: PVDF
Shaft: Nickel tungsten carbide
Bearings: Sapphire jewels
O-Rings: EPDM
RTD: 316 SS casing

PVDF Models

Body: PVDF
LID: PVDF
Paddlewheel: PVDF
Shaft: Zirconia ceramic
Bearings: Sapphire jewels
O-Rings: PTFE
RTD: 316 SS casing (-RTD models)



DPF701 smaller than actual size. Visit omega.com/dpf701

To Order

Model No.	Description	Model No. with RTD	Ports NPT	Maximum Difference Pressure bar (psi)	Range GPM (LPM)
FPB1402	Polypropylene flow meter	FPB1402-RTD	3/8	1 (15)	0.04 to 5.0 (0.15 to 18.9)
FPB1404	Polypropylene flow meter	FPB1404-RTD	1/2	1.4 (20)	0.08 to 10 (0.3 to 37.6)
FPB1406	Polypropylene flow meter	FPB1406-RTD	3/4	1.4 (20)	0.15 to 17 (0.6 to 64.4)
FPB1408	Polypropylene flow meter	FPB1408-RTD	1	1.4 (20)	0.35 to 35 (1.3 to 132.5)
FPB1412	PVDF flow meter	FPB1412-RTD	3/8	1 (15)	0.04 to 5.0 (0.15 to 18.9)
FPB1414	PVDF flow meter	FPB1414-RTD	1/2	1.4 (20)	0.08 to 10 (0.3 to 37.6)
FPB1416	PVDF flow meter	FPB1416-RTD	3/4	1.4 (20)	0.15 to 17 (0.6 to 64.4)
FPB1418	PVDF flow meter	FPB1418-RTD	1	1.4 (20)	0.35 to 35 (1.3 to 132.5)

Accessory

DPF701 1/8 DIN digital display, 115 Vac 7.5 to 13 Vdc powered

Comes complete with operator's manual.

Ordering Example: FPB1408, polypropylene flow meter with DPF701, digital display meter.

FPB1406-RTD, polypropylene flow meter with RTD temperature sensor and DPF701, digital display meter.