

HANDHELD DIGITAL AIRFLOW/ TEMPERATURE METERS

HHF92A



Optional



HHF92A shown smaller than actual size with rugged carrying case (included).

- ✓ CFM Function
- ✓ Measures Air Velocity and Temperature
- ✓ Dual LCD Display
- ✓ Min/Max/Avg Air Velocity Measurements
- ✓ Auto Power Shut Off
- ✓ Battery Powered (9V Alkaline Included)

SPECIFICATIONS

Air Flow	Resolution
80 to 6900 ft/min	1.00
0.4 to 35 m/sec	0.01
0.9 to 78 mph	0.10
0.8 to 68 knots	0.10
1.4 to 126 km/hr	0.10
Accuracy:	
80 to 6900 ft/min	±3% of full scale
0.4 to 35 m/sec	±3% of full scale

Temperature	Resolution	Accuracy
-10 to 50°C	0.1	±0.6°C
14 to 122°F	0.1	±1.0°F

Battery: 9V alkaline (included)
Battery Life: 100 hr (under normal usage)
Display: LCD
Display Size: 37 x 42 mm (1¼ x 1½")
Max. Reading: 9999
Dimensions: 183 x 76 x 45 mm (7.2 x 3 x 1.8")
Fan Diameter: 70 mm (2¾")
Auto Power Off: 20 minutes
Data Hold: Standard

OMEGA's HHF92A digital anemometer measures airflow in several different units: ft/min, mph, knots, meters/sec and km/h. Other features include the ability to measure temperature in °F or °C, and to give min/max/avg air velocity readings.

To Order

Model No.	Description
HHF92A	Anemometer kit
CAL-3-FLOW	NIST traceable 4-point calibration certificate
MN1603	Replacement 9V battery

Comes complete with hard carrying case, integral probe, 9V battery and operator's manual.
Ordering Example: HHF92A, handheld anemometer/thermometer.