GAS MASS FLOW METERS COMEGA AND CONTROLLERS For Clean Gases

With Optional Integral Display

FMA-A2000 Series



- ✓ ±1% Accuracy
- Linear Analog Output
- Low Cost
- Thermal Technology
- For Flow Rates Up to 100 SLM

CE OMEGA

OMEGA ENGINEERING, INC.

1-800-TC-OMEGA*** (1-800-826-0342)

One Omega Drive P.O. Box 4047 Stamford, CT 06007-0047

FLOW

1

Range

Power Supply Included

Model#

Serial#

Gas _____ Ref Cond _____ Max Pressure

£



FMA-A2417 with display, shown smaller than actual size.

The FMA-A2000 Series electronic mass flow meters/ controllers provide high performance, versatility, and state-of-the-art design in one compact package. The FMA-A2000 uses capillary-type thermal technology to directly measure mass flow of gases. No temperature, pressure, or square root corrections are required. The FMA-A2300/2400 Series comes with an LCD display, and all models have linear 0 to 5 Vdc and 4 to 20 mA output.

The FMA-A2000 measures the mass flow rate of gases in 24 ranges from 0 to 100 SLM. For the complete listing, refer to the range table on page D-20. The FMA-A2000 Series is compatible with most non-corrosive gases. The user is advised to check the wetted materials against gas compatibility.

OMEGA's mass flow controllers use an internal electromagnetic proportional valve to control the mass flow rate. A command signal can be supplied either by the internal setpoint pot or by a 0 to 5 Vdc external source.

FMA-A2117 without display, shown smaller than actual size.

1

SPECIFICATIONS


Accuracy: ±1% of full scale including linearity Repeatability: ±0.15% full scale or better Turndown Ratio: 100:1 Response Time: 5 seconds **Gas Ambient Temperature:** 0 to 50°C (32 to 122°F) **Temperature Coefficient:** 0.05% full scale per 1°C or better **Pressure Coefficient:** 0.01% full scale per psi or better **Minimum Pressure Requirements:** Meters: 1 inch of H2O Controllers Up to 1 SLM: 1 psi **Controllers Greater than** 20 SLM: 20 psi **Differential Pressure for** Mass Flow Controllers: <5 LPM. 5 to 50 psi standard >5 LPM, 20 to 40 psi standard Maximum Gas Pressure: Polyacetal: 250 psig 316 SS: 500 psig Leak Integrity: 1 x10⁻⁶ cc/min of He or better Wetted Parts: Standard: Polyacetal, FKM O-rings Optional: 316 SS, FKM O-rings **Connections:** ¹/₄ FNPT standard; 1/4" compression fitting for all stainless steel models Input/Output Connection: 9-pin sub-D connector Control Signal: 0 to 5 Vdc **Control Valve:** Electromagnetic normally closed Output Signal: Linear 0 to 5 Vdc, 1000 Ω min load, 4 to 20 mA, 500 Ω loop resistance **Mounting Threads:** 316 SS Body: %2" thread Polyacetal: Self tap #4/6 screw Input Power: Meters: 24 Vdc @ 150 mA, 115 Vac, 220 Vac with AC adaptor Controller: 24 Vdc @ 300 mA, 115 Vac, 220 Vac with AC adaptor Dimensions: See drawing Weight: 1.25 kg (2.75 lb) with power supply



Pango Table

Code	SCCM	Code	SLM C	Code	SLM
00	0 to 10	06	0 to 1	14	0 to 35
01	0 to 20	07	0 to 2	15	0 to 40
02	0 to 50	08	0 to 5	16	0 to 45
03	0 to 100	09	0 to 10	17	0 to 50
04	0 to 200	10	0 to 15	18	0 to 55*
05	0 to 500	11	0 to 20	19	0 to 60*
—	—	12	0 to 25	20	0 to 65*
—	—	13	0 to 30	21	0 to 70*
	_	_	_	22	0 to 75*
	—	—	—	23	0 to100*

* FMA-A2100/2300 Series only



To Order			
Model No.	Description		
FMA-A21(*)	Mass flow meter without display, ranges 0 to 10 SCCM to 0 to 100 SLM		
FMA-A22(*)-SS-(**)	Mass flow controller without display, with control valve, ranges 0 to 10 SCCM to 0 to 50 SLM, 316 SS body		
FMA-A23(*)	Mass flow meter with display, ranges 0 to 10 SCCM to 0 to 100 SLM		
FMA-A24(*)-SS-(**)	Mass flow controller with display and control valve, ranges 0 to 10 SCCM to 0 to 50 SLM, 316 SS body		

Compatible Meters; DPF50, DPF60, DPF300, DPF5500, DPF403. Visit us online for more details.

Accessories

Model No.	Description		
FMA-200PWA	Replacement socket plug-in power supply for 90 to 260 Vac		
SSLK-14-14	316 SS compression fitting 1/4 NPT for 1/4" OD tube		
Comes complete with operator's manual 9-pin sub-D connector, power supply and			

vith operator's manual, 9-pin sub-D connector, power supply and NIST calibration (5 data points).

* Insert range code from table at top of page to complete model number.

For optional 316 stainless steel body, add suffix "-SS" to model number for additional cost ($\frac{1}{4}$ " compression fittings standard). SS body standard on FMA-A22 and FMA-A24 controllers. Note: All controller flow ranges specified are for nitrogen or air at 20 psig; when used for other gases, a correlation factor is needed to determine the flow rate.

** Specify gas, inlet/outlet pressure, temperature.

For 10-point NIST calibration certificate, add suffix "-NIST10" to model number for additional cost. Ordering Examples: FMA-A2316, mass flow meter with display, calibrated for nitrogen at 20 psig inlet, room temperature for 0 to 45 SLM. ΔP : 5 to 20 psi.

FMA-A2102-SS, 316 stainless steel body mass flowmeter without display, 0 to 50 SCCM.