# RF CAPACITANCE POINT LEVEL SENSORS

## LV800 Series



- Superior 0.5 pF
  Sensitivity Ensures
  Reliability
- Build-Up Immunity Helps Eliminate False Signals
- High Intensity LED Indicating Light (Ordinary Location Integral Sensors Only)
   Simple 2-Step Manual

Simple 2-Step Manual Calibration

LV800 Series RF capacitance sensors offer cost-effective point level monitoring with reliability you can count on. Omega® provides you with the most affordable solution for your application. Omega's RF capacitance probes are designed to provide a high level of sensitivity, stability and durability for powder and bulk solids applications, as well as liquid and slurry applications.

#### **Principal of Operation**

A radio frequency is applied to the probe and is continually analyzed to determine the influence caused by the surrounding environment. As material contacts the probe, the radio frequency shifts indicating an increase in capacitance (C). The active probe of the unit and the vessel's wall make up the 2 plates, (A) of a capacitor which are separated by a fixed distance (D). The probe's insulator and surrounding air provide the dielectric material [with dielectric constant (K)]. As the air (K=1.0) is displaced with any other material (K > 1.0), the capacitance effect (C) is enhanced, thereby changing the application's impedance. This influence is measured within the circuitry and compared to a reference established by the sensitivity setting. The setting determines how much influence must be present before the output changes. The driven shield section of the probe enables the circuitry to ignore product build-up on the probe that would otherwise cause false sensing. The

driven shield is activated with the same radio frequency potential as the sensing probe. Since current can not flow between identical potentials, the driven shield blocks current flow from the active probe to the vessel wall through the material build-up, thereby eliminating the sensing of the material build-up.





LV802 Dimensions: mm (inch)

SENSITIVITY SETTING OF THE LV800						
SENSITIVITY DESCRIPTION	NO. OF ADJ. TURNS	MATERIAL DIELECTRICS	TYPICAL APPLICATIONS			
HIGH	0 to 1	1.5 to 3.0	PLASTICS, SOAP, OILS RUBBER, CEMENT			
MED	1 to 3	3.0 to 9.0	GRAINS, FERTILIZERS, FEED, SALT			
LOW	> 3.0	> 9.0	WASTEWATER, SLURRIES ANY WATER BASED SOLUTIONS			



### Applications

LV800 Series capacitance point level sensors are versatile devices providing high and low level readings in bins, silos, tanks, hoppers, and other vessels. LV800 Series superior sensitivity range allows users to properly adjust units to meet the needs of a wide variety of applications. Whether your application is for a powder, liquid, granular solid, or viscous material, the LV800 Series product line offers the right solution.

Typical Applications include, but not limited to							
Chemicals	Plastics	Pellets					
Feed/Grain	Rubber	Pharmaceuticals					
Liquids	Wastewater	Sand					
Food Ingredients	Slurries	Cement					
Powders	Paint and Coatings	Coal					
Granular Solids	Oils	Paper Pulp					

Specifications for LV800 Series					
Power	115 Vac (±15%), 2.5 VA, 50/60 Hz, or 230 Vac (±15%), 2.5 VA, 50/60 Hz (depending on model)				
Altitude	2000 m (6562') maximum				
Installation Category					
Pollution Degree	4 (reduced to 2 by enclosure) suitable for indoor/outdoor use				
Ambient Operating Temperature	-40°C (-40°F) to 65°C (150°F)				
Internal Bin Temperature*	To 80°C (176°F) with aluminum mount [<40°C (104°F) ambient]				
Output Relay	SPDT, 5A @ 250 Vac, 30 Vdc maximum				
External Indicators	Red and green LEDs indicating power and operating mode (ordinary location units only)				
Sensitivity	Multi-turn potentiometer adjustment 0.5 pf to 150 pf				
Stability	±0.027 pf per °C (±0.015 pf per °F) @ 0.5 pf setting				
Time Delay	0.25 to 15 sec delay-to-activate, adjustable 0.25 sec delay-to-deactivate, fixed				
Fail-Safe	Switch selectable - HI/LO				
Build-Up Immunity	Protected via driven shield to 150 $\Omega$ load				
Enclosure	Cast aluminum screw-on cover, beige polyester powder coat, NEMA 4 (IP66)				
Conduit Connection	Two (2) ¾ NPT connections				
Approvals	CSA(US) CSA(C) ordinary locations, CE mark (ordinary location only)				

\* Influenced by mounting, material thermal conductivity and ambient temperature.

#### **Probe Specifications**

Standard or Food Grade Probe				
Mounting	1¼ NPT aluminum			
Probe Material	9.5 mm (%") dia. 316 SS probe and guard, PPS and nylon insulators			
Probe Length	406 mm (16") from aluminum mounting			
Temperature (Probe Only)	PPS: 232°C (450°F) maximum, nylon: 148°C (300°F) maximum			
Pressure	3.5 bar (50 psi) maximum (aluminum connection), 10 bar (150 psi) maximum (¾ NPT SS)			
Stub Probe (LV802)				
Mounting	1¼ NPT aluminum			
Probe Material	9.5 mm (%") dia. 316 SS probe and guard, PPS			
Probe Length	228.6 mm (9")			
Temperature (Probe Only)	PPS 232°C (450°F) maximum			
Pressure	3.5 bar (50 psi) maximum (aluminum connection)			

To Order							
Model No.	Probe Type	Power	Probe Connection				
LV801	40 cm (16") PPS	115 Vac	1¼ NPT AI				
LV802	23 cm (9") PPS	115 Vac	1¼ NPT AI				
LV803	40 cm (16") PPS	230 Vac	1¼ NPT AI				
LV804	40 cm (16") food grade nylon	115 Vac	1¼ NPT AI				
LV805	40 cm (16") PPS	115 Vac	11/4 and 3/4 NPT stainless steel				

Comes complete with operator's manual.

Ordering Examples: LV801, 40 cm (16") PPS probe, 115 Vac, 1<sup>1</sup>/<sub>4</sub> NPT Al connection.

LV804, 40 cm (16") food grade nylon probe, 115 Vac,  $1\frac{1}{4}$  NPT Al connection.