
## NEMA 6 (IP68) SIDE MOUNTED LIQUID LEVEL SWITCHES

For High, Low, or Intermediate Level Sensing

LVN-90 Series

3 YEAR




- User Selectable, Normally Open or Normally Closed
- ✓ Mounts Horizontally

These liquid level switches are sealed with potting compound. The only path for liquid to the electrical switch would be through the wires. If the wires are terminated in an appropriate manner [eg. NEMA 6 (IP68) connectors], the level switch will meet or exceed a NEMA 6 (IP68) rating, making them suitable for submersion with years of worry free operation in moistureladen environments. A sealed SPST switch provides consistent accuracy and high repeatability with the effects of shock, vacuum or vibration minimized.

The switch is extremely versatile since it is user selectable as a normally open or normally closed by simply reversing the float or the mounting of the switch. The standard NPT male fittings allow for quick installation in either the top or bottom of the tank or vessel.







## SPECIFICATIONS

**Operating Temperature:** 

LVN-90 thru LVN-92: -40 to 82°C

(-40 to 180°F)

**LVN-93:** -40 to 149°C (-40 to 300°F)

Maximum Pressure Rating:

100 to 500 psi

Mounting: ½ NPT Switch: SPST Switch Actuation:

Approximately 1/2 the float travel in liquid

of 1.0 specific gravity

Lead Wires: 20 awg. 24" PVC

To Order					
	Switch		Maximum		Float
Model No.	Rating	Stem/Float	Temp.°C (F)	Pres.	Spec. Gravity
LVN-90	50 VA	CPVC	82 (180)	100 psi	0.71
LVN-91	50 VA	PVDF	82 (180)	100 psi	0.88
LVN-92	50 VA	Polypropylene	82 (180)	100 psi	0.49
LVN-93	50 VA	316 SS	149 (300)	500 psi	0.85

Comes complete with operator's manual.

Ordering Examples: LVN-93, 316 stainless steel level switch.

LVN-90, CPVC level switch.