LVU-150-R Series





ULTRASONIC LEVEL SENSORS

- Not Sensitive to Changes In Viscosity, Density, or Conductivity
- SPST Relay Standard
- Resists Vapor and Turbulence
- ✓ NEMA 6 (IP68) Submersible Sensor and Cable

OMEGA's ultrasonic sensors deliver accurate and reliable liquid level detection with an SPST mechanical relay output. The technology provides a high level of ultrasonic sensitivity, including resistance to vapor and turbulence. The ultrasonic sensor utilizes a fork-shaped sensor which contains two piezoelectric crystals, one of which acts as the ultrasonic transmitter, and the other as a receiver. If the air gap between the points of the fork fills with liquid, the sonic wave passes from one crystal to the other.

SPECIFICATIONS

Accuracy: ±1 mm (0.04") in water Repeatability: ±0.5 mm (0.02") in water Dead Band Hysteresis: 1 mm in water Voltage Input: 12 to 36 Vdc

Current Output: 25 mA maximum Relay:

GP: 120 Vac/Vdc @ 1 A CE: 60 Vac/Vdc @ 1 A

Switch Mode:

Selectable, NO or NC states

Wetted Materials: Polypropylene (PP)

or Perfluoroalkoxy (PFA)

Temperature Rating: -40 to 80°C

(-40 to 176°F)


Maximum Pressure Rating: PP:150 psi @ 25°C (76°F) derated @ 1.667 psi

per °C above 25°C (76°F)

Loop Resistance: $600~\Omega$ @ 24 Vdc Standard Cable Length: 3~m (10') Maximum Cable Length: 305~m (1000')

Dimensions:

76.2 or 114.3 L x 26.7 mm Dia. (3.0 or 4.5 x 1.05") (¾ NPT) **Enclosure Rating:** NEMA 6 (IP68) submersible sensor and cable



To Order			
Model No.	Description	Material	Size (inch)
LVU-150-R	Ultrasonic sensor	PP	3 x ¾ NPT
LVU-151-R	Ultrasonic sensor	PFA	3 x ¾ NPT
LVU-152-R	Ultrasonic sensor	PP	4.5 x ¾ NPT
LVU-153-R	Ultrasonic sensor	PFA	4.5 x ¾ NPT

Comes complete with operator's manual and 3 m (10') cable.

Two extended cable lengths available. For 7.62 m (25') add suffix "-25" to model number, for PP models, or PFA models, for additional cost. For 15.24 m (50') add suffix "-50" to model number for PP models, or PFA models, for additional cost.

Ordering Examples: LVU-150-R, polypropylene ultrasonic sensor, $3 \times \sqrt[3]{4}$ NPT **LVU-153-R,** PFA ultrasonic sensor, $4.5 \times \sqrt[3]{4}$ NPT.