









# Replacement Electrodes



## Replacement Electrodes for Leeds and Northrup Systems

These electrodes have been designed as Improved Replacement for L&N style electrodes used in the 7758, 7773, 7774, 7775, 7776 and 7779 mounting. The pH glass electrode (117393) uses an industrially proven "Process Glass" which covers all temperature ranges, thereby replacing the 117389, 117390 and 117391. All electrodes have the same physical configurations as the original equipment, while incorporating the latest technologies for improved performance. These technologies include "Plunger" for pH glass electrodes and our porous PTFE liquid junction in the reference electrodes.

**To  
Order  
(Specify  
Model  
Number)**

	Dbl. Junc. Reference	Sgl. Junc. Reference	pH Electrode	Fluoride Electrode	Comb. pH Electrode	Hi. Temp pH Probe	Polymer Body	Polymer ATC	Glass ATC
									
Model	PHRE-L1	PHRE-L2	PHRE-L3	PHRE-L4	PHRE-L5	PHRE-L6	PHRE-L7	PHRE-L8	PHRE-L9
Replaces	035832	117392	117393	117485	117486	117494	117495	152137	152139
Use For	7773, 7779	7773, 7779	758, 773, 779	758, 775, 776	774, 775, 776	774, 775, 776	7773, 779	7773, 779	7773, 779
Price	\$80	\$75	\$80	\$275	\$95	\$110	\$85	\$70	\$70

**Ordering Example:** PHRE-L1, Double junction reference electrode, \$80.



## UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

## CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

## GERMANY

[www.omega.de](http://www.omega.de)

Deckenpfronn, Germany  
0800-8266342

## UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488

## FRANCE

[www.omega.fr](http://www.omega.fr)

Guyancourt, France  
088-466-342

## CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)

Karviná, Czech Republic  
596-311-899

## BENELUX

[www.omega.nl](http://www.omega.nl)

Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters