

Alarm Module and Isolator



Model PHA-51

\$215

Models
PHA-51 and PHA-52

Dual Alarm Modules

- ✓ Adds Alarm Relay Capability to Common Analog Outputs
- ✓ Ideal for Use with Two Wire Transmitters
- ✓ Independent Setpoint and Dead Band Controls for Each Relay
- ✓ Relays Energize on Increasing or Decreasing Input Value-Switch Selectable
- ✓ NEMA 4X Gasketed Enclosure Provides Watertight Protection



The Model PHA-51 and PHA-52 dual alarm modules provide an ideal way to add alarm capability to a control system loop. The module's two relays each have setpoint and deadband controls and an LED to indicate on/off relay status. Relay phasing switches individually select each relay to operate in response to increasing or decreasing input signal value. For compatibility with many systems, input levels are user selectable. The PHA-51 accepts 0 to 20 mA, 4 to 20 mA, or 0 to 5Vdc inputs and the PHA-52 takes 0 to 50 mV, 0 to 100 mV, 0 to 5 Vdc.

Specifications

Inputs: PHA-51: 0 to 20 mA, 4 to 20 mA, 0 to 5 Vdc; PHA-52: 0 to 50 mV, 0 to 100 mV, 0 to 5 Vdc

Outputs: 0 to 5 Vdc, 100 K ohms min. load; 0 to 1 mA, 100 ohms max.

Power: 100 - 130 Vac

Relays: Setpoints: 0 to 100% of Input Signal Range; Deadbands: 0 to 50% of Signal Input Range; Contact Rating: SPDT, 3A max. resistive, 250 Vac max. 3A max. resistive, 30 Vdc max.

Dimensions: 120.6mm H x 120.6mm W x 63.5mm D x (4.75" x 4.75" x 2.5")

Weight: 567g (1.25 lb)

Model PHA-50

Loop Powered Isolator

- ✓ Prevents Ground Loops
- ✓ Transformer Isolated
- ✓ Loop Powered
- ✓ Virtually Zero Temperature Drift

The PHA-50 loop-powered isolator provides an isolated 4 to 20 mA output equal to the 4 to 20 mA non isolated input. This one to one current isolator is used in 4 to 20 mA two wire circuits to prevent ground loops. To eliminate moisture and humidity problems, the electronics are encapsulated in epoxy and the output is compensated for virtually zero temperature drift. The PHA-50 can be surface mounted in any position, and a trimpot control to adjust the output span is accessed by removing a protective cap.

Model PHA-50

\$175

Specifications

Input: 4 to 20 mA non isolated

Output: 4 to 20 mA Isolated

Insertion loss at 20 mA: 4.5 Vdc (this represents a max. resistance of 225 ohms into the 4 to 20 mA loop)

Allowable Isolated Load: 20 to 500 ohms

Isolation: 1000 Vac or dc, transformer isolated

Sensitivity: 0.01 mA

Stability: 0.01 mA

Non-linearity: ±0.03% of span

Accuracy: ±0.1%

Temperature Range: -20 to 50°C

Dimensions: 62.2mm H x 53.3mm W x 48mm D (2.45" x 2.10" x 1.89")

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model No.)		
Model No.	Price	Description
PHA-50	\$175	Loop power isolator
PHA-51	215	Dual alarm module (4-20 mA, 0-5 Vdc)
PHA-52	255	Dual alarm module (millivolt, 0 to 5 Vdc)



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters