



## Measure pH of Soil Directly with a Special pH Electrode

### PHH-200



- ✓ **Amplified, ATC Electrode:** The Advanced PHE-200 Incorporates a Temperature Sensor and has a Tiny Amplifier for Excellent Stability and Quick Response
- ✓ **Automatic Calibration:** Choose Between Six Memorized Buffers to Automatically Calibrate the Instrument
- ✓ **Messages on the Display:** The Operator is Helped by Graphic Symbols Visualized on the LCD
- ✓ **Supplied Complete:** The Ground Auger Allows Direct Measurements or for Greatest Accuracy Use the Beaker and Soil Preparation Solutions

The PHH-200 kit has been designed to address the question of correct and rapid measurement of pH directly in soil. Every item in this kit has been made to facilitate measurements in the field without compromising accuracy. The PHH-200 can test the pH of soil directly or after preparation of a diluted sample. In order to measure the pH directly; the kit includes a plastic auger to perforate the ground. The pH and temperature can be directly tested with the 4-in-1 conic shaped electrode in even a slightly moist soil. For higher degrees of accuracy, or for stony ground where the electrode may be damaged, use the PHTS-200 test solution. This solution is included in the package to help you measure the pH more precisely by diluting a sample of the soil in it. The PHH-200 is waterproof and sophisticated yet engineered for simplicity. The 4-in-1 pH electrode, PHE-200, has been designed for direct soil measurement. It has a conic, rugged tip and can be directly inserted in moist or soft soil. The electrode incorporates a temperature sensor right near the tip to enable it to measure and compensate for the temperature quickly. It also houses a miniaturized amplifier to boost the signal and provide greater stability in spot measurements. The dual-level LCD shows the pH value from 0 to 14 in hundredths of units. It also displays the temperature on the



PHH-200

secondary level at the same time. With a menu-driven custom microprocessor, the user is helped with clear prompts during operation and calibration. The batteries provide up to 1000 hours of continuous operation and indicate the battery level at any time. Calibration is completely automatic and the meter recognizes the buffers too. Any value set by the user as well as the calibration data is retained even during battery replacement. The PHH-200 is ergonomic and has been made for single-

handed use. Together with the meter you will also receive a handy booklet which explains how pH should be measured as well as general information about the correct limits in greenhouses, nurseries, fertilizer solutions as well as fruit and vegetable.

PHH-200 is supplied complete with portable waterproof pH meter, pH electrode, ground auger, beaker, soil preparation solution, batteries, and rugged carrying case.



PHH-200 comes with portable waterproof pH meter, pH electrode, ground auger, beaker, soil preparation solution, batteries, and rugged carrying case. DIN connector and 1 m (3.3') cable also included.

## Specifications

**Range:** 0.00 to 14.00 pH; 0.0 to 60.0°C (32 to 140°F)

**Resolution:** 0.01 pH; 0.1°C

**Accuracy (@20°C/68°F):** ±0.02 pH; ±0.5°C

**Typical EMC Deviation:** ±0.3 pH; ±1°C

**pH Calibration:** Automatic 1 or 2 points with 2 sets of 3 memorized buffers (4.00/7.00/10.00 or 4.00/6.86/9.18)

**Temp Compensation:**

Automatic from 0 to 60°C (32 to 140°F)

**Electrode:** PHE-200 with temp sensor, amplifier, DIN connector and 1 m (3.3') cable (included)

**Battery Type/Life:** 4 x 1.5 V "AAA" (included); 1000 hours approx. of continuous use

**Environment:** 0 to 50°C (32 to 122°F); 100% RH

**Dimensions:** 150 x 80 x 28 mm (5.9 x 3.1 x 1.1")

**Weight:** 210 g (7.5 oz.)

## To Order

Model No.	Description
PHH-200	Soil pH test kit
PHE-200	Replacement electrode
PHTS-200	Replacement test solution (Calcium Chloride) for stony ground soil
PHA-4	4.00 pH buffer solution 500 ml (1 pint) bottle
PHA-7	7.00 pH buffer solution 500 ml (1 pint) bottle
PHA-10	10.00 pH buffer solution 500 ml (1 pint) bottle
MN2400-12	12 "AAA" replacement batteries

*Comes complete with portable waterproof pH meter, pH electrode, DIN connector and 1 m (3.3') cable, ground auger, beaker, soil preparation solution, 4 "AAA" batteries, rugged carrying case and operator's manual.*

**Ordering Example:** PHH-200, soil pH test kit.

Order Online

**omega.com**<sup>®</sup>

Over 100,000 Products Available!

To download information and to order pH Field and Lab Instrument products online, visit [omega.com](http://omega.com)

**B-18**