

Mini See-Saw (Wave) Rockers

Product Discontinued

RCK-23 and RCK-24



as of November 2017

Different from 3D gyration motion, the RCK-23 and RCK-24 use a see-saw motion to create wave-like mixing process. These rockers are suitable for mixing various flat bottles, such as culture flasks, petri dishes etc.

With smaller footprint, but the high driving force, more platforms can be added by stacking two more platforms to accommodate more samples.

There are two models for this type of the rocker, both are microprocessor controlled. The digital model (RCK-23) provides digital timer with up to 9 hours setting and speed control in 1 RPM increment. The RCK-24 model provides 2 hours timers (in 10 minute integral) and 10 steps speed control without digital display.



RCK-23 shown smaller than actual size.

SPECIFICATIONS

Speed Range: 5 to 70 rpm

Rocking Type: See-saw, wave

Platform Dimensions: 235 x 235 mm (9.25 x 9.25")

Tilting Angle: 7°

Angle Adjustable: No, fixed at 7°

Timer

RCK-24: 120 minutes

RCK-23: Digital, 540 minutes

Speed Control Mode

RCK-24: 10 integral selection

RCK-23: Digital, 540 rpm

Maximum Load: 10 kg (22.04 lb)

Dimensions: 240 W x 300 D x 180 H mm (9.4 x 11.8 x 7.0")

Operation Temperature Range: 4 to 40°C (39.2 to 104°F)

Maximum Operation Humidity: 80%

Weight: 6 kg (13 lb)

Power Supply: 230V, 50 Hz, 50 W

To Order	
Model No.	Description
RCK-23	Mini see-saw rocker with digital display, timer and speed control
RCK-24	Mini see-saw rocker, digital control with 120 minute timer and speed adjustment

Comes complete with operator's manual.