

# **Transit Time Ultrasonic Flow Meters**

# **TFX-500w Clamp-On Meter**

#### **DESCRIPTION**

The TFX-500w transit time ultrasonic flow meter measures volumetric flow of clean water in pipes 10 in. or smaller. By clamping on the outside of the pipe, the ultrasonic meter installs without cutting or tapping the pipe.

## **FEATURES**

- Clamp-on, non-invasive flow meter
- · Bidirectional flow measurement system
- Measures flow rate, total and velocity of water flow
- Set up the meter through keypad interface or with SoloCUE® Flow Device Manager software
- · Compact enclosure uses large, easy-to-read graphical display
- Modbus RTU or BACnet MS/TP over RS485 and BEACON®/AquaCUE® connectivity

## **BENEFITS**

- Reduces installation costs, especially retrofits
  - ♦ Installs without cutting into the pipe
  - Eliminates flanges and pipe fittings
  - ♦ Eliminates draining and air purging
- Eliminates ingress or leak points in pipes
- · No moving parts to maintain
- No pressure head loss

#### **APPLICATION**

The TFX-500w meter is well suited for building automation, water distribution and wastewater collection in new and retrofit applications. In addition to having lower installation costs than an inline flow meter, the TFX-500w meter can be installed while the system continues to operate without interruption.

The TFX-500w meter is suitable for:

- Potable water
- Reclaimed water
- · Chiller water
- Boiler feed water
- Make-up water
- Condenser water
- Condensate



By connecting the TFX-500w meter to Badger Meter® AquaCUE or BEACON analytics cloud service, the meter becomes part of a system that tracks and monitors water use for commercial buildings, campuses and other large facilities.

#### **OPERATION**

Transit time flow meters use two transducers that function as both ultrasonic transmitters and receivers. The flow meters operate by alternately transmitting and receiving a frequency-modulated burst of sound energy between the two transducers. The burst is first transmitted in the direction of fluid flow and then against fluid flow. Since sound energy in a moving liquid is carried faster when it travels in the direction of fluid flow (downstream) than it does when it travels against fluid flow (upstream), a differential in the times of flight will occur. The sound's time-of-flight is accurately measured in both directions and the difference in time-of-flight calculated.





# **SPECIFICATIONS**

# System

Liquid Types	Water containing small amounts of suspended solids or gas bubbles			
Velocity Range	0.140 ft/s (0.0312 m/s) bidirectional			
Flow Accuracy	JZ, KZ, NZ, RZ, WZ			
Repeatability	±0.2% of reading			
Transducer Type	Clamp-on ultrasonics			
Certifications integral mount transmitter with		General Safety (option): FM Class 3810:2018, ANSI/ISA 61010-1:2012, ANSI/IEC 60529:2004, CAN/CSA-C22.2 No. 61010-1:2012, CSA C22.2 No. 60529:2005 CE: EMC Directive 2014/30/EU		

# **Transmitter**

Power	DC Class II power supply is required; 928V DC @ 5 W maximum				
Requirements	Protection	Reverse polarity and transient suppression			
	Keypad	4-button navigation, membrane keypad with domed tactile feedback			
Display	Resolution	128 × 64 pixel LED backlit graphical display; adjustable brightness and timeout			
Enclosure	IP66; polycarbonate				
Ambient	Operational ambient	With display: -4140° F (-2060° C); without display: -40158° F (-4070° C)			
Temperature	Storage	-40176° F (-4080° C)			
	Velocity	feet/second, meters/second			
Units of	Totals	US Gallons, Million Gallons, Imperial Gallons, Million Imperial Gallons, Acre-Feet, Barrels, Liters, Hectoliters, Cubic Meters, Cubic Feet			
Measure	Flow rate	Acre Feet/Day, Liters/Second, Liters/Minute, Liters/Hour, Cubic Meters/Second, Cubic Meters/Minute, Cubic Meters/Hour, Cubic Meters/Hour, Cubic Feet/Minute, Cubic Feet/Minute, Gallons/Second, Gallons/Minute, Gallons/Hour, Million Gallons/Day, Imperial Gallons/Second, Imperial Gallons/Minute, Imperial Gallons/Hour, Barrel/Minute, Million Imperial Gallons/Day, Barrel/Day			
Mounting	Wall or pipe remote mount or integral mount; Enclosure can be rotated in 90° increments				
Inputs	Digital input	it 530V DC, 3.48k Ohm impedence, externally or internally sourced; totalizer reset or alarm unlatch			
Outputs	Pulse / Frequency / Digital /	Two outputs, each selectable as frequency, pulse, forward/reverse flow or alarm output; isolated open collector, 530V DC, 50 mA maximum, externally or internally sourced with pullup resistor Digital alarm output: configurable high or low Frequency output: 63 Hz10 kHz maximum Pulse (totalizer) output: 100 Hz maximum output open collector, pulse width 5500 ms programmable			
	Analog Output	020 mA and 420 mA drive up to 800 Ohms; minimum 16-bit resolution, isolated			
Networks	EIA-485 with selectable protocols	Modbus RTU, baud rates 9600, 19200, 38400, 57600, 76800, 115200 BACnet MS/TP, baud rates 9600, 19200, 38400, 57600, 76800, 115200			
	Endpoints	Connectivity to AquaCUE or BEACON cellular endpoints			
Configuration Port	USB, Type mini-B				
Alarms	Buffer previous alarms, warnings or errors				
Languages	English, French, Germ	an and Spanish selectable			
Security	Four levels: Read-only	, Operator, Service and Admin; 6-digit passcode number; selectable auto logout			

#### **Transducers**

Model	Construction	Cable Length	Pipe/Tubing Sizes 2,3
CACT, Fixed small pipe	CPVC, Ultem, Nylon cord grip Polyethylene cable jacket; –40…194° F (–40…90° C) <sup>1</sup>	100 ft (90 m) max.	0.52 in. (1250 mm)
RZ (IP54), Standard pipe	PBT glass filled, Ultem®, Nylon cord grip PVC cable jacket; –40250° F (–40121° C)	300 ft (90 m) max.	2.510 in. (DN65DN250)
NZ (IP67), Standard pipe	CPVC, Ultem, Nylon cord grip Polyethylene cable jacket; –40…194° F (–40…90° C)	300 ft (90 m) max.	2.510 in. (DN65DN250)
WZ (IP68), Standard pipe, Submersible	CPVC, Ultem, Nylon cord grip Polyethylene cable jacket; –40…194° F (–40…90° C)	300 ft (90 m) max.	2.510 in. (DN65DN250)
JZ, KZ (IP54), Standard pipe, Integrated rail	PBT glass filled, Ultem®, Nylon cord grip PVC cable jacket; –40250° F (–40121° C)	100 ft (30 m) max.	2.56 in. (DN65DN150) 2.510 in. (DN65DN250)

<sup>&</sup>lt;sup>1</sup> CA...CT integral mount temperature is limited by the transmitter temperature rating.

## **Configuration Software**

The flow meter can be programmed and configured with the SoloCUE Flow Device Manager software. The software also has troubleshooting tools for diagnosing and correcting installation problems.

**SoloCUE** 

Used to configure and troubleshoot flow meter. Software is compatible with Windows® 7 SP1, 8, 10




Figure 1: SoloCUE setup screen




Figure 2: SoloCUE diagnostics screen

#### **Additional Parts Required for Configuration**

Part Number	Description	
RC820648	USB Type A to mini B software cable (shielded to minimize noise)	


<sup>&</sup>lt;sup>2</sup> Recommendations based on unlined, new pipes with water. Recommended pipe or tubing sizes vary with pipe conditions and fluid.

<sup>&</sup>lt;sup>3</sup> PVC, CPVC, HDPE, PTFE, PDVF, stainless steel, ductile iron, aluminum, brass naval, carbon steel copper. Conduit not available with Easy Rail.

## **DIMENSIONS**

#### **TFX-500w Meter**

# **Enclosure, Integral and Remote, Front View**



# **Integral Enclosure Side View**




## **Remote Enclosure Side View**



## **Transducers**


# **Remote System with Standard Pipes**

## NZ/RZ/WZ (W, V or Z mount)



Model	Α	В	C	D
RZ	3.75 in. (95.25 mm)	2.35 in. (59.69 mm)	_	2.19 in. (55.63 mm)
NZ, WZ	2.95 in. (74.93 mm)	2.75 in. (69.8 mm)	3.00 in. (76.2 mm)	1.70 in. (43.2 mm)


#### Easy Rail JZ/KZ (W or V mount)



M	odel	Α	В	C	D	E	F
	JZ	13.62 in. (345.95 mm)	11.73 in. (297.94 mm)	0.75 in. (19.05 mm)	0.79 in. (20.06 mm)	2.76 in. (70.10 mm)	2.36 in. (59.94 mm)
	ΚZ	19.92 in. (505.97 mm)	18.03 in. (457.96 mm)	0.75 in. (19.05 mm)	0.79 in. (20.06 mm)	2.76 in. (70.10 mm)	2.36 in. (59.94 mm)

# **Remote System with Small Pipes**


#### CA...CT




# **Integral System**

# CA...CT

CA...CT (except CF and CL)




CF and CL U-Bolt Connections




Pipe Size	Pipe Material	А	В	С	D
	ANSI/DN	2.46 in. (62.48 mm)	2.36 in. (59.94 mm)	2.66 in. (67.56 mm)	0.84 in. (21.34 mm)
1/2 in.	Copper	2.46 in. (62.48 mm)	2.36 in. (59.94 mm)	3.33 in. (84.58 mm)	0.63 in. (16.00 mm)
	Tubing	2.46 in. (62.48 mm)	2.28 in. (57.91 mm)	3.72 in. (94.49 mm)	0.50 in. (12.70 mm)
	ANSI/DN	2.46 in. (62.48 mm)	2.57 in. (65.28 mm)	2.66 in. (67.56 mm)	1.05 in. (26.67 mm)
3/4 in.	Copper	2.46 in. (62.48 mm)	2.50 in. (63.50 mm)	3.56 in. (90.42 mm)	0.88 in. (22.35 mm)
	Tubing	2.46 in. (62.48 mm)	2.50 in. (63.50 mm)	3.56 in. (90.42 mm)	0.75 in. (19.05 mm)
	ANSI/DN	2.46 in. (62.48 mm)	2.92 in. (74.17 mm)	2.86 in. (72.64 mm)	1.32 in. (33.53 mm)
1 in.	Copper	2.46 in. (62.48 mm)	2.87 in. (72.90 mm)	3.80 in. (96.52 mm)	1.13 in. (28.70 mm)
	Tubing	2.46 in. (62.48 mm)	2.75 in. (69.85 mm)	3.80 in. (96.52 mm)	1.00 in. (25.40 mm)
	ANSI/DN	2.80 in. (71.12 mm)	3.18 in. (80.77 mm)	3.14 in. (79.76 mm)	1.66 in. (42.16 mm)
1-1/4 in.	Copper	2.46 in. (62.48 mm)	3.00 in. (76.20 mm)	4.04 in. (102.62 mm)	1.38 in. (35.05 mm)
	Tubing	2.46 in. (62.48 mm)	3.00 in. (76.20 mm)	4.04 in. (102.62 mm)	1.25 in. (31.75 mm)
	ANSI/DN	3.02 in. (76.71 mm)	3.40 in. (86.36 mm)	3.33 in. (84.58 mm)	1.90 in. (48.26 mm)
1-1/2 in.	Copper	2.71 in. (68.83 mm)	2.86 in. (72.64 mm)	4.28 in. (108.71 mm)	1.63 in. (41.40 mm)
	Tubing	2.71 in. (68.83 mm)	3.31 in. (84.07 mm)	4.28 in. (108.71 mm)	1.50 in. (38.10 mm)
	ANSI/DN	3.70 in. (93.98 mm)	3.42 in. (86.87 mm)*	5.50 in. (139.70 mm)	2.38 in. (60.45 mm)*
2 in.	Copper	3.70 in. (93.98 mm)	3.38 in. (85.85 mm)*	5.50 in. (139.70 mm)	2.13 in. (54.10 mm)*
	Tubing	3.21 in. (81.53 mm)	3.85 in. (97.79 mm)	4.75 in. (120.65 mm)	2.00 in. (50.80 mm)

<sup>\*</sup> Varies due to U-bolt configuration

#### PART NUMBER CONSTRUCTION



Conduit length must be less than or equal to cable length. Submersible Conduit limited to 100 ft (30 m). Conduit not available with Easy Rail.



<sup>&</sup>lt;sup>1</sup> Conduit length must be less than or equal to cable length. Submersible Conduit limited to 100 ft (30 m). Conduit not available with Easy Rail.

## **PARTS AND ACCESSORIES**

## **Couplant**

Part Number	Description
D002-2011-001	Dow Corning® Molykote® 111 Grease; 5.3 oz Tube; 150° F (65° C)
D002-2011-002	Dow Corning 732; Permanent Mount; 356° F (180° C)

Dow 111 grease is included with transducers.

# **Power Supplies**

Part Number	Description
68334-001	Wall Plug; 100264V AC In; 24V DC Out; -2050° C
68334-002	Module; 85264V AC In; 24V DC Out; -3070° C

For ordering transducers and transmitter separately, please contact factory.

# **Control. Manage. Optimize.**

Dynasonics is a registered trademark of Badger Meter, Inc. Other trademarks appearing in this document are the property of their respective entities. Due to continuous research, product improvements and enhancements, Badger Meter reserves the right to change product or system specifications without notice, except to the extent an outstanding contractual obligation exists. © 2021 Badger Meter, Inc. All rights reserved.