

HANDHELD/BENCHTOP HEAT GUNS

148000 Series



LIGHTWEIGHT HEAT GUN, 148002

Lightweight (only 28 oz) whisper-quiet, heavy-duty motor allows for fatigue-free use hour after hour.

Each heat gun includes a bench-stand, a silver 343°C (650°F) heating element and a deflector adaptor for shrink tubing. Flowrate is 3.8 CFM.

Replacement Element:
148004

HEAT GUN, 148003


This unit features an exclusive electronic temperature control which enables the user to select the temperature desired for each job and lock it in. A rubber-padded, non-slip, adjustable base allows the heat gun to be used in many benchtop operating positions. Flowrate is 17 CFM.

Replacement Element:
148023

STANDARD HEAT GUN, 148001

Adjustable air intake control and a powerful high speed universal motor allow for control of volume heat, hour after hour. Double-jacketed heater housing protects heating element and sturdy die-cast aluminum housing is rugged to protect motor assembly from hard knocks. A non-slip rubber-backed base permits rotation of heat gun for use in any position on your workbench. Flowrate is 23 CFM.

Replacement Element:
148004



To Order				
Model No.	Volts	Amps	Max Temp °C (°F)	Weight kg (lb)
148001	120	14	260 to 399 (500 to 750)	1.7 (3.75)
148002	120	4	343 (650)	0.8 (1.75)
148003	120	14	538 (1000)	1.7 (3.75)

Accessories

Model No.	Description
148005	Shrink tubing attachment for tubing up to ¼" OD
148006	Shrink tubing attachment for tubing up to 2" OD
148008	Pinpoint heat attachment directs ¼" heat
148009	Extra-wide (8") for shrink tubing up to ¾" OD

Heating Elements

Model No.	Color	Temperature °C (°F)	Volts	Watts
148013	Blue	260 (500)	120	340
148014	Silver	343 (650)	120	475
148015	Black	426 (800)	120	525

Ordering Example: 148001, 120V, 14 A handheld benchtop heat gun.