



AIR-SENSING THERMOSTATS FOR HEATING CABLES

RTAS Series Starts At
\$370



- ✓ Ambient Air-Sensing
- ✓ Complete with Integral Fluid Filled Thermostat
- ✓ Setpoint Range -18 to 107°C (0 to 225°F)
- ✓ Ideal for Freeze Protection or Comfort Heating
- ✓ Type RTAS-EP for Division II Areas

RTAS-EP Control Box –Interior View



- A. Cable grommet provides watertight seal between base and box (one supplied)
- B. Three position terminal block for easy wiring
- C. Power wiring entry
- D. Gasket provides watertight seal between box and lid. It is affixed to the lid and captures the mounting hardware.
- E. Thermostat switch (hermetically sealed in RTAS-EP)
- F. Scaled setpoint adjustment knob
- G. Ground wire connection (RTAS-EP only)

Type RTAS for ordinary areas



CAUTION AND WARNING!

Fire and electrical shock may result if products are used improperly or installed or used by non-qualified personnel. See inside back cover for additional warnings.

SPECIFICATIONS

Temperature Setpoint Range: -18 to 107°C (0 to 225°F)

Minor Scale Divisions: 5.6°C (10°F)

Switch Rating:

Type RTAS: 22 AMPS @ 120 to 480 Vac, SPDT

Type RTAS-EP: 11 AMPS @ 120 to 250 Vac, SPDT

Maximum Sensor Exposure Temperature: 121°C (250°F)

Sensor Dimensions: 14.3 mm OD x 7.6 cm (5/8 x 3") long

Operating Ambient Temperature Range: -40 to 71°C (-40 to 160°F)

Factory Pre-Set and Calibrated: 4.4°C (40°F) operation

Weight: 0.9 kg (2 lb)

Dimensions:

Length: 13.3 cm (5.25")

Width: 10.8 cm (4.25")

Height When Mounted on Pipe: 15.9 cm (6.25")

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
RTAS	\$370	Air-sensing thermostats
RTAS-EP	470	Air-sensing thermostat for Division II areas


Ordering Example: Model RTAS thermostat for heating cable, \$370.

Used with	Max. No. of Power Conn.
SRL-C, SRF-C	2
SRL-CR/CT, SRF-CR	2
CWM, CWM-C	1
CWM-CT	1
SRL-M/MC	2
SRL-MCR/MCT	2
SRM/E, SRM/E-CR	2
SRM/E-CT	2

PIPE-WALL SENSING BULB AND CAPILLARY THERMOSTATS FOR HEATING CABLES


B

RTBC Series
Starts At
\$375




RTBC Control Box—
Interior View

- ✓ Pipe Line or Tank Wall Sensing
- ✓ Complete with Integral Bulb and Capillary Thermostat
- ✓ Setpoint Range
18 to 204°C (0 to 400°F)
- ✓ For Process Temperature Maintenance
- ✓ Type RTBC-EP for Division II Hazardous Locations



RTBC-EP Control Box—Interior



RTBC, \$375,
shown smaller than
actual size.

SPECIFICATIONS

Temperature Setpoint Range: -18 to 204°C
(0 to 400°F)

Ambient Temperature Range: -40 to 71°C (-40 to 160°F)

Minor Scale Divisions: 5.6°C (10°F)

Switch Rating:

Type RTBC: 22 AMPS @ 120 to 480 Vac, SPDT

Type RTBC-EP: 11 AMPS @ 120 to 250 Vac, SPDT

Maximum Sensor Exposure Temperature: 230°C (450°F)

Dimensions:

Length: 13.3 cm (5.25")

Width: 10.8 cm (4.25")

Height (When Mounted on Pipe):
15.9 cm (6.25")

**Type RTBC
for regular
(non-hazardous)
applications**

- A. Cable grommet provides watertight seal between base and box (one supplied)
- B. Three position terminal block for easy wiring
- C. Power wiring entry
- D. Gasket provides watertight seal between box and lid. It's affixed to the lid and captures the mounting hardware
- E. Thermostat mounting bracket
- F. Setpoint adjustment knob
- G. Thermostat switch (hermetically sealed in RTBC-EP)
- H. Stainless steel sensing bulb, ¼" OD, 7¼" L with 10' capillary
- I. Ground wire connection (RTBC-EP only)

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model Number	Price	Description
RTBC	\$375	Bulb and capillary thermostat
RTBC-EP	530	Bulb and capillary thermostat for Division II Areas

Ordering Example: RTBC-EP, thermostat for heating cable, rated for Division II hazardous areas, \$530.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters