

TRANSDUCER INDICATOR SYSTEM

POWERS UP TO 10 LOAD CELLS

DP1028 Series

- ✓ Heavy Duty Metal Enclosure
- ✓ Front Panel System Check
- ✓ High and Low Level Inputs
- ✓ Powers up to Ten 350 Ohm Bridges
- ✓ Front Panel Shunt Calibration

DP1028
\$595
Model Shown



The Model DP1028 Transducer Indicator System is a heavy duty 4½ digit indicator with excitation for up to ten 350 ohm bridges. Standard features include a dead zero and front panel instrument calibration and transducer shunt calibration pushbuttons. With its rugged metal case and heavy duty power supply, the DP1028 has proven to be a highly reliable monitor in industrial applications.

SPECIFICATIONS

Accuracy: ±1 count over entire range

Excitation:

10, 12, 15 or 28 Vdc switch selectable capable of driving up to ten 350 ohm transducers

Input: Switch Selectable

High Level: 0-5 Vdc Transducers

Low Level: mV/V Transducers and Load Cells

Display: 4½ digits 0.6" (15 mm) high

Resolution: ±19,999 counts with dead zero for count by 10 up to 199,990

Zero: ±10% adjustable

Conversion Rate: 400 ms

Compensated Range:

0 to 55°C (32 to 131°F)



Model DP1028
Shown Smaller Than
Actual Size



Model LC1011-10K, \$895
Shown Smaller Than Actual Size
Capacity Range 500 to 2 Million pounds
See page F-92 for details

Temperature Stability: 0.01%/°C

Power: 115 Vac ±10% 50-60 Hz or 230 Vac 50-60 Hz ±10%

Case: Metal

Dimensions:

68 H x 107 W x 57 mm D
(2.68 x 4.20 x 6.20")

Panel Mount Option Dimensions:

70 H x 133 mm W (2.75 x 5.25")

Instrument Calibration Check:

A front panel pushbutton provides a quick check on the instrument's internal calibration

Transducer Shunt Calibration:

A front panel pushbutton enables the transducer's shunt calibration resistor

Most Popular Models Highlighted

To Order (Specify Model Number)		
MODEL NO.	PRICE	DESCRIPTION
DP1028	\$595	Benchtop 115 Vac powered indicator
DP1028-230	630	Benchtop 230 Vac powered indicator
Options:		
"-PM"	\$25	Panel mount option

Note: Power cord supplied. 115 Vac models have standard plug, 220 Vac models have stripped ends. **Ordering Examples:**

- 1.) DP1028-PM is the 115 Vac powered indicator system with panel mount option, \$595 + 25 = \$615
- 2.) DP1028-230, benchtop 230 Vac powered indicator system, \$630



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters