

ECONOMICAL DIGITAL MANOMETER FOR CLEAN DRY GASES



HHP8200 Series



- ✓ Digital Display of Gauge or Differential Pressure
- ✓ User Selectable Engineering Units
- ✓ Min and Max Memory
- ✓ RS232 Output with Optional Software
- ✓ Auto Power Off and Low Battery Indication
- ✓ Bright Backlit Display
- ✓ Connection Hose Tubing Included

The HHP8200 Series are low-cost handheld manometers capable of measuring differential pressure and positive or negative gauge pressure. Five models are available covering ranges from 0-5 to 0-100 psi. All models feature user selectable engineering units, MIN/MAX memory, and a bright backlit display for easy viewing in low light conditions.

SPECIFICATIONS

Accuracy: $\pm 0.3\%$ FS

Resolution: See "To Order" table

Engineering Units (User Selectable): psi, mbar, bar, inH₂O, cmH₂O, mmHg, ozin², kgcm², kPa, ftH₂O, inHg (except HHP4252: psi, mbar, bar, inH₂O, mmH₂O)

Storage Temperature: -20 to 60°C (-4 to 140°F)

Operating Temperature: 0 to 50°C (32 to 122°F)

Temperature Effects: $\pm 0.2\%$ FS typical ($\pm 1\%$ max)

Proof Pressure: See "To Order" table

Pressure Media: Clean, dry, non-corrosive gases

Response Time: 0.5 sec

Pressure Connections/ Tubing Size:

Hose barb for 4 mm ID tubing

Battery: 9V battery (included)

Battery Life: 30 hours (without backlight)

Dimensions:

182 H x 72 W x 30 mm D (7.16 x 2.83 x 1.18")

Weight: 150 g (5.3 oz)



HHP8215, shown smaller than actual size.

To Order

MODEL NO.	RANGE (psi)	RESOLUTION (psi)	PROOF PRESSURE (psi)
HHP8205	0 to 5	0.003	20
HHP8215	0 to 15	0.01	30
HHP8230	0 to 30	0.02	60
HHP8200	0 to 100	0.1	150

ACCESSORY

MODEL NO.	DESCRIPTION
HHF91-SW	Software and RS232 cable with 9 pin sub-D connector

Comes complete with 9V battery, connection hose, hard carrying case and operator's manual.

Ordering Examples: HHP4252, 0 to 2 psi manometer.

HHP4230, 0 to 30 psi manometer and HHF91-SW, optional software and RS232 cable.