

# LOW DIFFERENTIAL PRESSURE SWITCHES SPDT RELAY OUTPUT

## DISCONTINUED

### PSW-141 Series 0.1 to 10.0 inH<sub>2</sub>O Ranges

Starts at  
**\$143**



- ✓ Virtually Impervious to Changes in Position
- ✓ Fast Response Time Resulting from Low Internal Volume
- ✓ No Moving Parts—Solid State Circuitry for Long Life
- ✓ Compact Size
- ✓ Low Power Consumption

PSW141 Series low differential pressure switches operate on the capacitive principle and can sense very low positive or negative pressures. In a capacitive cell, a very lightweight, responsive diaphragm deflects slightly when pressure is applied. This deflection results in a change in capacitance, which is then detected and processed by solid state circuitry. Reliability and long life are inherent advantages of this design.

#### SPECIFICATIONS

Setpoint is adjusted by a 20-turn potentiometer for fine resolution

**Repeatability:** ±1% of setpoint

**Deadband:** Factory set to 7% of range to prevent relay chatter

**Media Compatibility:** Suitable for air or inert gases

**Overpressure:** 8x range maximum

**Port Connections:** 4.8 mm (3/16") Dia. tube; suitable for 3.2 mm (1/8") ID Tygon® tubing or 6.3 mm (1/4") OD polyethylene tubing

#### Electrical:

Input V	Range	Power
12 Vdc*	9.5 to 16 Vdc	0.25 W
24 Vdc*	19 to 32 Vdc	0.25 W
24 Vac	19 to 32 Vac	1.50 W
120 Vac	100 to 140 Vac	1.70 W

\* Reverse polarity protected



PSW-141-DR, \$176, shown smaller than actual size.



PSW-141-ER, \$143, shown smaller than actual size.

## DISCONTINUED

**Electrical Connections:** 3/8" terminal strip with #6 screw  
**Output:** SPDT (form "C") relay  
 1 A, 24 Vdc or 0.5 A; 120 Vac resistive  
 0.3 A, 24 Vdc or 0.2 A; 120 Vac inductive  
 300,000 cycles minimum  
**Isolation:** Input to output 500 Vrms min  
**Dimensions:** 36 H x 76 W x 131 mm L  
 (1.4 x 3.0 x 5.15")  
**Weight:** 230 g (0.5 lb)  
**Case Material:** Flame-retardant, glass-reinforced Noryl®

**Operating Temperature:**  
0 to 45°C (32 to 113°F)

**Temperature Effect on Setpoint:**  
±0.05%/°C

**Humidity Range:** 20 to 90% RH, non-condensing

**Shock:** 10 g (11 ms)

**Vibration:** 5 g to 50 Hz

**MOST POPULAR MODELS HIGHLIGHTED!**

#### To Order (Specify Model Number)

RANGE inH <sub>2</sub> O	MODEL NO.	PRICE	DESCRIPTION
<b>12 Vdc Power Models<sup>(1)</sup></b>			
0 to 0.1	PSW-141-AR	\$176	Energize on rising pressure <sup>(2)</sup>
0 to 0.2	PSW-141-BR	176	Energize on rising pressure <sup>(2)</sup>
0 to 0.3	PSW-141-CR	176	Energize on rising pressure <sup>(2)</sup>
0 to 0.5	PSW-141-DR	176	Energize on rising pressure <sup>(2)</sup>
0 to 1.0	PSW-141-ER	143	Energize on rising pressure <sup>(2)</sup>
0 to 2.0	PSW-141-FR	143	Energize on rising pressure <sup>(2)</sup>
0 to 3.0	PSW-141-GR	143	Energize on rising pressure <sup>(2)</sup>
0 to 5.0	PSW-141-HR	143	Energize on rising pressure <sup>(2)</sup>
0 to 10.0	PSW-141-IR	143	Energize on rising pressure <sup>(2)</sup>

Comes complete with operator's manual.

**Notes:** (1) For 24 Vdc power, specify model **PSW142**, no additional charge; for 120 Vac power specify model **PSW144**, no additional charge. (2) For switch energizing on falling pressure, change the suffix "-R" to "-F", no additional charge.

**Ordering Examples:** PSW142-ER, 24 Vdc powered switch with a range of 0 to 1.0 inH<sub>2</sub>O, energizes on rising pressure, \$143.

PSW-141-EF, 12 Vdc powered switch with a range of 0 to 1.0 inH<sub>2</sub>O, energizes on falling pressure, \$143.

#### ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
CM-4422	\$40	Reference Book: Hydraulics and Pneumatics

## DISCONTINUED

H 20





#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters