

PC BOARD MOUNTABLE POWER SUPPLIES WITH INDUSTRY-STANDARD PIN CONFIGURATIONS

PSC Series




- ✓ Regulated Power Supplies with Rugged Dependability
- ✓ 2 Types of Mounting Kits Available for Easy Installation
- ✓ Foldback Current Limiting Provides Outstanding Short Circuit Protection





PSC-D15, shown with PSC-022, mounting kit, shown smaller than actual size.



PSC-5, shown smaller than actual size.



PSC-D15, shown with PSC-08B, mounting kit, shown smaller than actual size



MOUNTING KITS

MODEL NO.	DESCRIPTION
PSC-022	PC card with 22-pin connector
PSC-08B	Barrier strip style connector

To Order		OUTPUT VOLTAGE	OUTPUT CURRENT	VOLTAGE ACCURACY	LINE & LOAD (NL TO FL) REGULATIONS
SINGLE OUTPUT	PSC-5	5 Vdc	500 mA	±1%	±0.05%
	PSC-9	9 Vdc	1000 mA	±0.5%	±0.05%
	PSC-12	12 Vdc	480 mA	±0.5%	±0.02%
	PSC-15	15 Vdc	400 mA	±0.5%	±0.02%
	PSC-18	18 Vdc	500 mA	±0.5%	±0.02%
	PSC-24	24 Vdc	375 mA	±0.5%	±0.02%
DUAL OUTPUT	PSC-D5	±5V or 10V	750 mA	±0.5%	±0.05%
	PSC-D12	±12V or 24V	120 mA	±0.5%	±0.02%
	PSC-D15	±15V or 30V	100 mA	±0.5%	±0.02%
	PSC-D15A	±15V or 30V	350 mA	±0.5%	±0.02%

Comes complete with operator's manual.

Ordering Examples: PSC-12, 12 Vdc, 480 mA power supply and PSC-08B, barrier strip connector.

PSC-24, 24 Vdc, 375 mA power supply.