

SMART PRESSURE TRANSMITTER

HIGH STABILITY, LOW DRIFT

25 inH₂O to 6000 psi


PX751 Series



PX751, shown smaller than actual size.

- ✓ 2-Way Communications, Remote Troubleshooting, Reranging, Reconfiguring, Access to Difficult-to-Reach or Hazardous Areas
- ✓ Improved Performance, Increased Accuracy, Greater Stability and Noise Resistance
- ✓ Diagnostic Capabilities, Continuous On-Line Self-Check, Selectable Failure Alarm, Loop Test
- ✓ Transmitter Includes Configuration, Calibration and Materials Data
- ✓ Greater Performance, Wider Rangeability (100:1), Transmitter Security, Selectable Linear/Square Root Output, Multi-Drop
- ✓ High Stability and Low Drift Ensure Accurate Measurements for Years
- ✓ Fast, Dynamic Response
- ✓ Tighter Control and Reduced Maintenance Costs
- ✓ Pressure and Temperature Output

**Coplanar Design—
Differential, Gage, or
Absolute Pressure!**



PX751C coplanar transmitter, with flange, shown smaller than actual size.

PX751C SMART TRANSMITTER

LCD Meter Options

The LCD meter can be digitally customized by the user to meet process needs. The meter can be configured to display engineering units, percent of range, or custom user scale, or to alternate between any 2 of these.

Power Supply

The DC power supply should provide power with less than 2% ripple. The transmitter requires a minimum of 250 Ω of loop resistance to communicate with a Hart™ based communicator. With 250 Ω drop, the transmitter will require a minimum of 16 Vdc to output 20 mA.

Diagnostics and Service

The diagnostic and service functions listed here are primarily for use after the transmitter is installed in the field.

The **Transmitter Test** feature helps verify that the transmitter is operating properly, and can be performed either on the bench or in the field. The transmitter test command initiates an extensive diagnostics routine that can quickly identify potential electronics problems. If the transmitter detects a problem, messages to indicate the source of the problem are displayed on the communicator screen.

The **Loop Test** feature is designed to verify proper loop wiring and transmitter output, and should only be performed after the user installs the transmitter. This function tests the output of the transmitter, the integrity of the loop, and the operations of any recorders or similar devices installed in the loop.

Calibration

Calibrating a smart transmitter is different from calibrating an analog transmitter. The smart transmitter requires 3 steps:

- **Rerange**—sets the 4 and 20 mA points to the desired pressures.
- **Sensor Trim**—adjusts the position of the factory characterization curve to optimize the transmitter performance over a specified pressure range or to adjust for mounting effects.



➤ **Analog Output Trim**—adjusts the analog output to match the plant standard or the control loop.

Advanced Functions

Cloning: Quickly copies the same configuration to multiple units. The cloning process involves configuring a transmitter, saving the configuration data, then sending a copy of the data to a separate transmitter.

Multidrop: Communication between the host and the transmitter takes place digitally with the analog output of the transmitter deactivated. With Hart™ smart protocol, up to 15 units can be connected on a single pair of twisted wires or over leased phone lines.

Burst Mode: Provides faster digital communications to control system by eliminating the time required for the control system to request data from the transmitter. Burst mode applies only to the transmission of dynamic data (pressure and temperature).

Low-Power Option

User-selectable 3-wire 1 to 5 Vdc or 0.8 to 3.2 Vdc outputs are available with the low-power option. The digital signal is superimposed on the voltage signal, available to any host conforming to Hart™ protocol. Low-power units operate on 6 to 12 Vdc with no load.

PX751C SMART TRANSMITTER

SPECIFICATIONS AND REFERENCE DATA



PX751H high-process temperature traditional flange differential and pressure gage, shown smaller than actual size.

SPECIFICATIONS

Service:

Liquid, gas and vapor applications

Zero and Span Adjustment:

Zero and span values can be set anywhere within the range limits stated in tables. Span values must be greater than or equal to the minimum span stated in the range limits tables.

4 to 20 mA Models


Output:

2-wire 4 to 20 mA output, user selectable for linear or square root; digital process variable superimposed on 4 to 20 mA signal, available to any host that conforms to the Hart™ protocol

Power Supply:

External power supply required. Standard transmitter operates on 10.5 to 55 Vdc with no load. A minimum of 250 Ω of loop resistance is required to communicate with a Hart™ based communicator. With 250 Ω drop, the transmitter will require a minimum of 16 Vdc to output 20 mA.

Load Limitations:



Communications require a minimum loop resistance of 250 Ω.

¹ For CSA approval, power supply must not exceed 42.2 V.

Low Power Models

Output: 3-wire 1 to 5 Vdc or 0.8 to 3.2 Vdc user selectable. Also user selectable for linear or square root output configuration. Digital process variable superimposed on 4 to 20 mA signal, available to any host that conforms to the Hart™ protocol.

Power Consumption: 3 mA, 18 to 36 mW

Minimum Load Impedance:

100 kΩ (V_{OUT} + wiring)

Indication:

Optional 2-line, 5-digit LCD meter

Overpressure Limits:

Transmitters withstand the following limits without damage

Gage/Differential Models (CA/CD):

Range 1:

0 to 2000 psig (0 to 13.8 MPa)

Ranges 2 to 5:

0 to 3626 psig (0 to 25 MPa)

Absolute Models (CA):

Range 0: 0 to 60 psia (0 to 413.7 kPa)

Range 1: 0 to 120 psia (0 to 827.4 kPa)

Range 2: 0 to 300 psia (0 to 2070 kPa)

Range 3: 0 to 1600 psia (0 to 11030 kPa)

Range 4: 0 to 6000 psia (0 to 41370 kPa)

High-Process Temperature Models (HP/HG)

All Ranges, 0 to 3626 psig

(0 to 25 MPa) "T" Style Gage and

Absolute Models (TA/TG):

Range 1: 0 to 750 psia (0 to 5.2 MPa)

Range 2: 0 to 1500 psia (0 to 10.3 MPa)

Range 3: 0 to 1600 psia (0 to 11.0 MPa)

Range 4: 0 to 6000 psia (0 to 41.4 MPa)

Range 5: 0 to 15000 psia (0 to 103.4 MPa)

Static Pressure Limits

Differential Pressure Models Only:

Operates within specification between static line pressure of 0.5 psia and 3626 psig; 2000 psig for range 1 (ranges 2 and 3 for high-accuracy models)

Burst Pressure Limits:

All Except Type T:

10,000 psig (69 MPa)

Type T:

Ranges 1 to 4: 11,000 psi (75.8 MPa)

Range 5: 26,000 psig (179 MPa)

Failure Mode Alarm: User selectable to drive output either high or low when gross transmitter failure is detected

Temperature Limits

Ambient: -40 to 85°C (-40 to 185°F);

with integral meter, -20 to 80°C (-4 to 175°F)

Storage: -46 to 110°C (-50 to 230°F);

with integral meter, -40 to 85°C

(-40 to 185°F)

Process Temperature Limits

Differential, Gage and Absolute:

Silicone Fill Sensor¹ with

Coplanar Flange -40 to 250°F²

Side Flange -40 to 300°F²

Level Flange

Horizontal Mount -40 to 250°F²

Vertical Mount -40 to 300°F²

Inert Fill Sensor Option¹ 0 to 185°F^{3, 4}

High-Temperature Models:

Fill Material Temperature Range

D.C. Silicone 200¹ -40 to 375°F

Inert -50 to 350°F

Neobee M-20¹ 0 to 375°F

Type "T" Gage and Absolute:

Silicone Fill Sensor¹ -40 to 250°F²

Inert Fill Sensor¹ -22 to 250°F²

Humidity: 0 to 100% RH

Turn-On Time: Performance within specifications less than 2.0 seconds after power is applied

Volume Displacement:

<0.08 cm³ (0.005 in³)

Damping: User selectable from

0 to 36 seconds for one time constant.

This software damping is in addition to sensor module response time.

All Models

Response Time:

Dead Time (Td): 45 ms nominal

Time Constant (Tc): 55 ms

Update Rate: 20 times/s minimum

Vibration Effect: < ±0.1% of URL per gram when tested from 15 to 2000 Hz in any axis relative to pipe-mounted process connection

Power Supply Effect:

<0.005% of calibrated span per volt

RFI Effects: ±0.1% of span from 20 to 1000 MHz, and field strength up to 30 V/m

Transient Protection (Optional):

Meets IEEE standard 587, Category B meets IEEE standard 473, surge withstand capability 2.5 kV crest, 1 MHz waveform

Process Connections (All Except Level, High-Pressure Gage and Absolute Models):

¼-18 NPT on 2½" centers;

½-14 NPT on 2, 2½, or 2¼" centers

Level Models:

High-Pressure Side: 2, 3 or 4",

Class 150, 300 or 600 flange

50, 80 or 100 mm: PN40 or ¼" flange

High Gage or Absolute Pressure:

¼-18, ½-14 female, G½ A DIN 16288

male (available in stainless steel for

ranges 1 to 4) or autoclave type F-250-C

(pressure relieved ¼-18 gland thread;

¼ OD high pressure tube 60° cone;

available in stainless steel for range

5 only)

Wetted Parts:

Flanges: Plated carbon steel

standard; stainless steel, Hastelloy

C or Monel optional (available on

PX751C only)

Wetted O-Rings: Glass-filled TFE

Housing: Low-copper aluminum with polyurethane paint

Cover O-Rings: Buna-N

Note: Calibrations at 20°C (68°F)

per ANSI Z210.1

¹ Process temperatures above 185°F (85°C)

require derating the ambient limits by a

^{1.5:1} ratio (0.06:1 ratio for Type H).

² 104°C (220°F) limit in vacuum service;

71°C (130°F) for pressures below 0.5 psia.

³ 71°C (160°F) limit in vacuum service.

⁴ Not available on model PX751CA.

COMMERCIAL GRADE—TYPE “C” DIFFERENTIAL, GAGE, AND ABSOLUTE PRESSURES

SPECIFICATIONS

Differential and Gage CD/CG Models

Accuracy: $\pm 0.075\%$ of span $\pm 0.100\%$ of span for differential range 1. For rangedowns greater than 10:1 of URL (15:1 for differential range 1), accuracy = $\pm \left[0.025 + \frac{0.005 (\text{URL})}{\text{Span}} \right] \%$ of span

Ambient Temperature Effect per 10°C (50°F):

- Spans 1:1 to 10:1:
 $\pm(0.0125\% \text{ URL} + 0.0625\% \text{ span})$
- Spans 10:1 to 100:1
 $\pm(0.025\% \text{ URL} + 0.125\% \text{ span})$
- Range 1: $\pm(0.1\% \text{ URL} + 0.25\% \text{ span})$

Static Pressure Effect (DP Model Only):

- Zero Error:** $\pm 0.1\%$ of URL/1000 psi (6.9 MPa) for line pressures from 0 to 2000 psi (0 to 13.7 kPa)—can be calibrated out at line pressure;
- $\pm 0.2\%$ of URL/1000 psi (6.9 MPa) for line pressure above 2000 psi (13.7 MPa)
- Range 1:** $\pm 0.25\%$ URL/1000 psi (6.9 MPa)
- Span Error*:** $\pm 0.2\%$ rdg/1000 psi (6.9 MPa)
- Range 1:** $\pm 0.4\%$ rdg/1000 psi (6.9 MPa)

*Ranges 4 and 5 must be field calibrated

Total Performance**:

$\pm 0.25\%$ of span for $\pm 28^\circ\text{C}$ (50°F) temperature changes, up to 1000 psi (6.9 MPa) line pressure, from 1:1 to 5:1 rangedown

** Total performance is based on the combined errors of reference accuracy, ambient temperature effect, and span line pressure effect.

Stability: $\pm 0.25\%$ of URL for 5 years for $\pm 28^\circ\text{C}$ (50°F) temperature changes, up to 1000 psi (6.9 MPa) line pressure

Range 1: $\pm 0.2\%$ URL for 1 year

Mounting Position Effect:

Zero shifts up to 2.5 inH₂O (0.62 kPa), which can be calibrated out; no span effect

Weight:

Type C: 6.0 lb (2.7 kg)

PX751CD coplanar design, shown smaller than actual size.



RANGES: PX751CA ABSOLUTE PRESSURE MODELS

RANGE	MINIMUM SPAN	RANGE AND SENSOR LIMITS	
		UPPER (URL)	LOWER (URL)
0	0.167 psia (8.7 mmHgA)	5 psia (26 mmHgA)	0 psia (0 mmHgA)
1	0.3 psia (2.07 kPa)	30 psia (206.8 kPa)	0 psia (0 kPa)
2	1.5 psia (10.34 kPa)	150 psia (1034.2 kPa)	0 psia (0 kPa)
3	8 psia (55.16 kPa)	800 psia (5515.8 kPa)	0 psia (0 kPa)
4	40 psia (275.8 kPa)	4000 psia (27580 kPa)	0 psia (0 kPa)

** Total performance is based on the combined errors of reference accuracy, ambient temperature effect, and span line pressure effect.

RANGES: PX751CD, CG, PD, PG, HD, HG, AND LEVEL MODELS

RANGE	MINIMUM SPAN		UPPER (URL)	RANGE AND SENSOR LIMITS (LRL)					
	GAGE AND DIFFERENTIAL TYPE C	HIGH ACCURACY TYPE H	ALL MODELS	DIFFERENTIAL CD/HD	GAGE CG/HG	LEVEL DIFFERENTIAL	LEVEL GAGE	HIGH-TEMP HD	HIGH-TEMP HG
1	0.5 inH ₂ O (0.12 kPa)	N/A	25 inH ₂ O (6.22 kPa)	-25 inH ₂ O (-6.22 kPa)	N/A	N/A	N/A	N/A	N/A
2	2.5 inH ₂ O (0.62 kPa)	2.5 inH ₂ O (0.62 kPa)	250 inH ₂ O (0.62 kPa)	-250 inH ₂ O (-62.2 kPa)	-250 inH ₂ O (-62.2 kPa)	-250 inH ₂ O (-62.2 kPa)	-250 inH ₂ O (-62.2 kPa)	-250 inH ₂ O (-62.2 kPa)	-250 inH ₂ O (-62.2 kPa)
3	10 inH ₂ O (2.48 kPa)	100 inH ₂ O (24.8 kPa)	1000 inH ₂ O (248 kPa)	-1000 inH ₂ O (-248 kPa)	0.5 psia (3.5 kPa abs)	-1000 inH ₂ O (-248 kPa)	0.5 psia (3.5 kPa abs)	-1000 inH ₂ O (-248 kPa)	0.5 psia (3.5 kPa abs)
4	3 psi (20.7 kPa)	30 psi (207 kPa)	300 psi (2070 kPa)	-300 psi (-2070 kPa)	0.5 psia (3.5 kPa abs)	-300 psi (-2070 kPa)	0.5 psia (3.5 kPa abs)	-300 psi (-2070 kPa)	0.5 psia (3.5 kPa abs)
5	20 psi (138 kPa)	200 psi (1380 kPa)	2000 psi (13800 kPa)	-2000 psi (-13800 kPa)	0.5 psia (3.5 kPa abs)	N/A	N/A	-2000 psi (-13800 kPa)	0.5 psia (3.5 kPa abs)


COMMERCIAL GRADE—TYPE “C” HIGH-PRECISION GRADE—TYPE “P” ORDERING GUIDE

Vacuum to 2000 psi

- ✓ Coplanar Flange
- ✓ Plated Carbon Steel Flange
- ✓ Stainless Steel Diaphragm
- ✓ 0.075% Accuracy
- ✓ 0.25% Long-Term (5-Year) Stability
- ✓ 5-Year Calibration Cycle



PX751C coplanar design, shown smaller than actual size.



PX751C coplanar transmitter, with flange, shown smaller than actual size.

PRESSURE TRANSDUCERS **B**

COMMERCIAL GRADE—TYPE C

To Order

MODEL NO.	URL	COMPATIBLE METERS
ABSOLUTE PRESSURE		
PX751CA-1	30 psia	DP41-E, DP25B-E, DP24-E
PX751CA-2	150 psia	DP41-E, DP25B-E, DP24-E
PX751CA-3	800 psia	DP41-E, DP25B-E, DP24-E
PX751CA-4	4000 psia	DP41-E, DP25B-E, DP24-E
GAGE PRESSURE		
PX751CG-2	250 inH ₂ O	DP41-E, DP25B-E, DP24-E
PX751CG-3	1000 inH ₂ O	DP41-E, DP25B-E, DP24-E
PX751CG-4	300 psig	DP41-E, DP25B-E, DP24-E
PX751CG-5	2000 psig	DP41-E, DP25B-E, DP24-E
DIFFERENTIAL PRESSURE		
PX751CD-1	25 inH ₂ O	DP41-E, DP25B-E, DP24-E
PX751CD-2	250 inH ₂ O	DP41-E, DP25B-E, DP24-E
PX751CD-3	1000 inH ₂ O	DP41-E, DP25B-E, DP24-E
PX751CD-4	300 psid	DP41-E, DP25B-E, DP24-E
PX751CD-5	2000 psid	DP41-E, DP25B-E, DP24-E

Standard features include plated carbon steel flange, stainless steel diaphragm, 4 to 20 mA output with digital signal based on Hart™ protocol, glass-filled TFE O-ring and silicone fill fluid.

Note: Standard configurations do not include calibration certificate. Contact factory prior to ordering if certificate is required.

Ordering Examples: PX751CD-1-B4, smart differential pressure sensor with coplanar flange and range of -2.5 to 25 inH₂O, 2" pipe mounting bracket.

PX751CG-2-B4, smart gage pressure sensor with coplanar flange and range of -25 to 250 inH₂O, 2" pipe mounting bracket.

OPTIONS FOR ALL MODELS AND INTEGRAL 2-, 3-, or 5-VALVE MANIFOLDS

SUFFIX	DESCRIPTION
-M	Low power 1 to 5 Vdc (not avail. w/haz location cert)
-SS	All stainless steel flanges for Type “C”
-IN	Inert fill fluid (N/A on CA models)
-B4	2" pipe mounting bracket for coplanar flange
-B6	2" pipe mounting bracket for H-style transmitters
-M5	5½ digit LCD meter

HIGH PROCESS TEMPERATURE—TYPE “H” DIFFERENTIAL AND GAGE PRESSURES ALL STAINLESS STEEL FLANGES

Vacuum to 2000 psi



- ✓ Stainless Steel Side Flanges Standard
- ✓ Process Temperatures to 191°C (375°F) with No Isolating Elements
- ✓ 4 to 20 mA and Digital Communications
- ✓ 0.075% Accuracy
- ✓ 100:1 Rangedown
- ✓ Long-Term Stability
- ✓ D.C. 200 Silicone Fill Fluid

PX751H, high-process temperature flange, shown with standard stainless steel side flanges, smaller than actual size.



SPECIFICATIONS

“H”—High-Process Temperature
Accuracy: $\pm 0.075\%$ of span; for rangedowns greater than 10:1 of URL, accuracy =

$$\pm \left[0.025 + 0.005 \left(\frac{\text{URL}}{\text{Span}} \right) \right] \% \text{ of span}$$

Ambient Temperature Effect per 10° C (50°F):

$\pm (0.025\% \text{ URL} + 0.125\% \text{ span} + 0.35 \text{ inH}_2\text{O})$; for spans below 30:1 rangedown, $\pm (0.035\% \text{ URL} + 0.125\% \text{ span} + 0.35 \text{ inH}_2\text{O})$

Static Pressure Effect:

Zero Error: $\pm 0.1\%$ of URL/1000 psi (6.9 MPa) for line pressures from 0 to 2000 psi (0 to 13.7 MPa)—can be calibrated out at line pressure; $\pm 0.2\%$ of URL/1000 psi (6.9 MPa) for line pressures above 2000 psi (13.7 MPa)

Span Error*:

$\pm 0.2\%$ of rdg/1000 psi (6.9 MPa)

* Ranges 4 and 5 must be field calibrated.

Stability:

Ranges 2 and 3:
 $\pm 0.1\%$ of URL
for 12 months

Ranges 4 and 5:
 $\pm 0.2\%$ of URL
for 12 months

Mounting Position Effect:

Zero shifts up to 5 inH₂O (1.27 kPa), which can be calibrated out; no span effect

Weight: 6.2 kg (13.6 lb)

To Order

MODEL NO.	RANGE (psi)	COMPATIBLE METERS
GAGE PRESSURE		
PX751HG-2	250 inH ₂ O	DP41-E, DP25B-E, DP24-E
PX751HG-3	1000 inH ₂ O	DP41-E, DP25B-E, DP24-E
PX751HG-4	300 psig	DP41-E, DP25B-E, DP24-E
PX751HG-5	2000 psig	DP41-E, DP25B-E, DP24-E
DIFFERENTIAL PRESSURE		
PX751HD-2	250 inH ₂ O	DP41-E, DP25B-E, DP24-E
PX751HD-3	1000 inH ₂ O	DP41-E, DP25B-E, DP24-E
PX751HD-4	300 psid	DP41-E, DP25B-E, DP24-E
PX751HD-5	2000 psid	DP41-E, DP25B-E, DP24-E

Standard features include stainless steel side flanges, stainless steel diaphragm, 4 to 20 mA output with digital signal based on Hart™ protocol, glass-filled TFE O-ring and D.C. 200 silicone fill fluid

Ordering Examples: **PX751HD-2-B6**, smart high-process temperature differential pressure sensor with stainless steel side flanges, D.C. 200 silicone fill and ranging of 2.5 to 250 inH₂O and 2" pipe mounting bracket.

PX751HG-4-B6, smart high-process temperature gage pressure sensor with stainless steel side flange, D.C. 200 silicone fill fluid, 2" pipe mounting bracket and range of 3 to 300 psi.

OPTIONS FOR ALL MODELS

SUFFIX	DESCRIPTION
-M	Low power 1 to 5 Vdc (not avail. w/haz location cert)
-SS	All stainless steel flanges for Type “C”
-IN	Inert fill fluid (N/A on CA models)
-B4	2" pipe mounting bracket for coplanar flange
-B6	2" pipe mounting bracket for H-style transmitters
-M5	5½ digit LCD meter

SINGLE ISOLATOR—TYPE “T”

DIFFERENTIAL, GAGE, AND ABSOLUTE PRESSURES

Vacuum to 10,000 psi

PX751TG, TA Gage and Absolute Pressure



- ✓ Gage or Absolute Pressure
- ✓ 0.075% Accuracy
- ✓ All Stainless Steel Wetted Parts
- ✓ 0.25% Long-Term (5-Year) Stability

SPECIFICATIONS

“T” Style Gage and Absolute:

Accuracy: $\pm 0.075\%$ of span; for rangedowns greater than 10:1 of URL, accuracy = $\pm \left[0.075 \left(\frac{\text{URL}}{\text{Span}} \right) \right] \%$ of span

For Absolute Range 0 With Turndown:

$>5:1$ of URL, accuracy = $\pm \left[0.025 + 0.01 \left(\frac{\text{URL}}{\text{Span}} \right) \right] \%$ of span

Total Performance

(Ranges 1 to 4 Only)**:

$\pm 0.25\%$ of span for 28°C ($\pm 50^\circ\text{F}$) temperature changes, from 1:1 to 5:1 rangedown

** Total performance is based on the combined errors of reference accuracy, ambient temperature effect, and span line pressure effect.

Ambient Temperature Effect per 10°C (50°F):

Spans 1:1 to 30:1:

$\pm(0.025\% \text{ URL} + 0.125\% \text{ span})$

Spans 30:1 to 100:1:

$\pm(0.035\% \text{ URL} + 0.125\% \text{ span})$

Range 0: $\pm(0.1\% \text{ URL} + 0.25\% \text{ span})$

Range 5: $\pm(0.1\% \text{ URL} + 0.15\% \text{ span})$

For High-Gage and Absolute

Range 1, Spans 1:1 to 10:1:

$\pm(0.025\% \text{ URL} + 0.125\% \text{ span})$

Spans 10:1 to 100:1:

$\pm(0.05\% \text{ URL} + 0.125\% \text{ span})$

Stability—Low Absolute Model:

Ranges 1 to 5:

$\pm 0.1\%$ of URL for 12 months

Ranges 0:

$\pm 0.2\%$ of URL for 12 months

Stability—High-Gage

and Absolute Models: $\pm 0.25\%$ of span for 5 years for 28°C ($\pm 50^\circ\text{F}$) temperature change

Mounting Position Effect: Zero shifts up to 0.62 kPa (0.09 psi), which can be calibrated out; no span effect

Weight: 1.4 kg (3.0 lb)



PX751T, gage or absolute pressure single input design, ½ NPT stainless steel fitting, shown with meter option, smaller than actual size.

PRESSURE TRANSDUCERS **B**

RANGE	RANGE AND SENSOR LIMITS		
	MINIMUM SPAN	UPPER (URL)	UPPER (LRL)
1	0.3 psia (2 kPa)	30 psi (207 kPa)	0 psi (0 kPa)
2	1.5 psi (2.07 kPa)	150 psia (1034 kPa)	0 psi (0 kPa)
3	8 psi (55 kPa)	800 psia (5516 kPa)	0 psi (0 kPa)
4	40 psi (276 kPa)	4000 psia (27,579 kPa)	0 psi (0 kPa)
5	2000 psi (13,800 kPa)	10,000 psia (68,948 kPa)	0 psi (0 kPa)

To Order		
MODEL NO.	URL	COMPATIBLE METERS
ABSOLUTE PRESSURE		
PX751TA-1	30 psia	DP41-E, DP25B-E, DP24-E
PX751TA-2	150 psia	DP41-E, DP25B-E, DP24-E
PX751TA-3	800 psia	DP41-E, DP25B-E, DP24-E
PX751TA-4	4000 psia	DP41-E, DP25B-E, DP24-E
PX751TA-5	10,000 psia	DP41-E, DP25B-E, DP24-E
GAGE PRESSURE		
PX751TG-1	30 psia	DP41-E, DP25B-E, DP24-E
PX751TG-2	150 psia	DP41-E, DP25B-E, DP24-E
PX751TG-3	800 psia	DP41-E, DP25B-E, DP24-E
PX751TG-4	4000 psia	DP41-E, DP25B-E, DP24-E
PX751TG-5	10,000 psia	DP41-E, DP25B-E, DP24-E

Standard features include SS diaphragm and ½ NPT process fitting, 4 to 20 mA output with digital signal based on Hart™ protocol, glass-filled TFE O-ring and silicone fill fluid.

Ordering Examples: PX751TA-1-B4, smart absolute pressure sensor with stainless steel input and range of 0.03 to 30 psia and 2" pipe mounting bracket.

PX751TG-2-B4, smart gage pressure sensor with stainless steel input and range of 1.5 to 150 psig and 2" pipe mounting bracket.

OPTIONS FOR ALL MODELS

SUFFIX	DESCRIPTION
-M	Low power 1 to 5 Vdc (not avail. w/haz location cert)
-SS	All stainless steel flanges for Type “C”
-IN	Inert fill fluid (N/A on CA models)
-B4	2" pipe mounting bracket for coplanar flange
-B6	2" pipe mounting bracket for H-style transmitters
-M5	5½ digit LCD meter