

PRECISION STRAIN GAGE RECTANGULAR CORNER ROSETTES AND RESIDUAL STRESS PATTERN

**Custom-Designed
Strain Gages
Available!
No Minimum Quantities.
Consult Engineering.**

To Order



GAGE PATTERN Leads not shown	MODEL NO. Pkg of 10	NOM. RESIS- TANCE (Ω)	DIMENSIONS mm (inch) [†]				MAX PERMITTED BRIDGE ENERGIZING VOLTAGE (Vrms)	TERMINATION	TEMP COMP	TERM PAD
			GRID		CARRIER					
			A	B	C	D				
RECTANGULAR CORNER ROSETTE										
 Shown actual size, 27 mm, leads not shown	SGD-13/120-RY91	120	11.0 5.0 27.0 27.0 (0.433) (0.197) (0.06) (0.06) Corner rosette extra-large 120 Ω				Ribbon Leads	ST	BPT-6	
	SGD-13/120-RY93	120					Ribbon Leads	AL		
	SGD-13/120-RY21	120					Solder Pads	ST		
	SGD-13/120-RY23	120					Solder Pads	AL		

Open-face gages available. Consult Pressure Sales and Engineering.

Note: For strain gage accessories visit us online

Ordering Example: SGD-13/120-RY91, 120 Ω nominal-resistance strain gage.

NOTE

ST = Steel
AL = Aluminum

To Order



GAGE PATTERN Leads not shown	MODEL NO. Pkg of 10	NOM. RESISTANCE (Ω)	DIMENSIONS mm (inch) [†]				MAX PERMITTED BRIDGE ENERGIZING VOLTAGE (Vrms)	TERMINATION	TEMP COMP	TERM PAD
			GRID		CARRIER					
			A	B	C	D				
RESIDUAL STRESS PATTERN ROSETTE										
 Shown actual size, 10.5 mm	SGD-1.5/120-SR11	120	1.20 1.33 10.50 10.50 (0.047) (0.052) (0.413) (0.413) Residual stress pattern 120 Ω				Ribbon Leads	ST	BPT-6	
	SGD-1.5/120-SR13	120					Ribbon Leads	AL		
	SSGD-1.5/120-SR41	120					Solder Pads	ST		
	SGD-1.5/120-SR43	120					Solder Pads	AL		

DISCOUNT SCHEDULE

1 to 10 pkgs.	Net
11 to 24 pkgs.	5%
25 to 49 pkgs.	10%
50 and up and OEM . .	Consult Factory

Open-face gages available. Consult Pressure Sales and Engineering.

Note: For strain gage accessories visit us online

Ordering Example: SGD-1.5/120-SR11, 120 Ω nominal-resistance strain gage.


**For Equations
Visit us online**

OMEGA® offers stress relief or residual stress pattern strain gages. These strain gages are mounted onto a test piece

that is already stressed. Instrumentation is attached to all 3 elements in the rosette. The stress magnitude is determined by unloading the test specimen by boring-out or drilling a

small hole in the center of the strain gage. By removing material you are releasing the stress, and measuring the relaxed residual stress in the vicinity of the hole. Hole diameter and depth is 1.85 mm (0.07")

TYPICAL STRAIN GAGE INSTALLATION




STRAIN GAGES E

PRECISION STRAIN GAGE

PRECISION SPECIFICATIONS CHART

TYPE SGD AND KFH



SPECIFICATIONS

	SGD SERIES	KFH SERIES—PRE-WIRED
Foil Measuring Grid	Constantan foil 5 microns thick	Constantan foil 6 microns thick
Carrier	Polyimide	Kapton®
Substrate Thickness	20 microns	15 microns
Cover Thickness	25 microns	9 microns
Connection Dimensions: mm (inch)	Solder pads or ribbon leads, tinned copper flat wire 30 L x 0.1 D x 0.3 mm W (1.2 x 0.004 x 0.012")	Pre-wired, 2 or 3 leads 27 AWG strand polyvinyl insulation 1 x 2 mm (0.04 x 0.08")
Nominal Resistance	Stated in "To Order" box	120 ±0.4 or 350 Ω
Resistance Tolerance Per Package	±0.15% to ±0.5% depending on gage spec	0.3%
Gage Factor (Actual Value Printed on Each Package)	2.0 ±5%	2.10 ±10%
Gage Factor Tolerance Per Package	1.00%	1.00%
THERMAL PROPERTIES		
Reference Temperature	23°C (73°F)	23°C (73°F)
SERVICE TEMPERATURE		
Static Measurements	-75 to 200°C (-100 to 392°F)	-20 to 100°C (-4 to 212°F)
Dynamic Measurements	-75 to 200°C (-100 to 392°F)	-20 to 100°C (-4 to 212°F)
TEMPERATURE CHARACTERISTICS		
Steel (and Certain Stainless Steels)	11 ppm/°C (6.1 ppm/°F)	10.8 ppm/°C (6 ppm/°F)
Aluminum	23 ppm/°C (12.8 ppm/°F)	—
Uncompensated	±20 ppm/°C (11.1 ppm/°F)	—
Temperature Compensated Range	-5 to 120°C (5 to 248°F)	10 to 80°C (50 to 176°F)
Tolerance of Temp Compensation	2 ppm/°C (1.0 ppm/°F)	1 ppm/°C (0.5 ppm/°F)
MECHANICAL PROPERTIES		
Maximum Strain	3% or 30,000 microstrain	5% or 50,000 microstrain
Hysteresis	Negligible	Negligible
Fatigue (at ±1500 microstrain)	>10,000,000 cycles	>10,000,000 cycles
Smallest Bending Radius	3 mm (1/8")	3 mm (1/8")
Transverse Sensitivity	—	Stated on each package