


# POWER SUPPLIES



U24Y101, shown smaller than actual size.

ACCESSORIES 

## SPECIFICATIONS

### Input:

- U24Y101: 110 Vac
- U24Y101-220: 220 Vac
- U48Y40: 110 Vac

**Operating Range:** -10 to 65°C  
(14 to 150°F)

### Output:

- U24Y101: 24 Vdc @ 1000 mA
- U48Y40: 48 Vdc @ 400 mA

### Dimensions:

- U24Y101: 76 H x 185 W x 75 mm D  
(3.0 x 7.28 x 2.94")
- U48Y40: 114 H x 130 W x 87 mm D  
(4.49 x 5.12 x 3.44")

### REGULATED PSR SERIES

**Input:** 115V or 230 Vac models

**PSR-24S Dimensions:**  
56 L x 49 W x 81 mm H  
(2.2 x 1.9 x 3.2")



- ✓ Regulated and Unregulated Power Supplies for Transducers and Transmitters
- ✓ 48V Available for High-Resistance Loops
- ✓ Compact, Rugged Design

## To Order

MODEL NO.	DESCRIPTION
PSR-24S	Regulated power supply, 24 Vdc, 400 mA, screw terminal, 115 Vac
PSR-24L	Regulated power supply, 24 Vdc, 400 mA, UL, 1.8 m (6') cord with stripped leads
PSR-24L-230	Regulated power supply, 24 Vdc, 400 mA, stripped leads, 230 Vac input, CE
U24Y101	Unregulated power supply, 24 Vdc, 1000 mA, 110 Vac power
U24Y101-220	Unregulated power supply, 24 Vdc, 1000 mA, 220 Vac power
U48Y40	Unregulated power supply, 48 Vdc, 400 mA for long loops (high resistance), 110 Vac

*Comes complete with operator's manual.*

**Ordering Example:** PSR-24L-230, 24 Vdc, 400 mA, stripped leads, 230 Vac input, CE.