# 

- Easy-to-Read Backlit LCD
- ✓ °C/°F Switchable
- ✓ 0.1°/1° Auto Ranging
- Thermocouple Selectable by Rear Panel Switches
- Front Panel Splash-Proof (IP65)
- Can Be Used with OS36, OS37, and OS38 Infrared Probes
- Optional RS-232
- Benchtop Portable Meters
- Rugged ABS Case
- Available as Single- or Six-Input Models

The DP5000A and BS6000 series of temperature panel and benchtop meters are both highly versatile and accurate. Available in thermocouple and infrared inputs, thermistor and RTD versions with 0.1 degree resolution, auto ranging to 1 degree above 1000°. The thermocouple versions are switch selectable for one of six thermocouple types from the rear panel. The DP5000A series is microprocessor driven and fully self-calibrating, offering exceptional accuracy and long term stability. The backlit LCD is easy to read in any light

Specifications for DP5000A and BS6000 Series

conditions from dim to bright sunlight, or fluorescent lighting.

Inputs: Thermocouples: J, K, T, E, N, R, S; RTD Pt100, 2-, 3-, or 4-wire, Alpha 0.00385, Thermistor:  $2252~\Omega$  at  $25^{\circ}$ C (77°F). Display: 4-digit, backlit LCD Accuracy:

 $\pm 0.15\%$  of rdg + 0.2°C at or above 0°C (+0.4°F) at or above 32°F)  $\pm 1$ °C below 0°C ( $\pm 2$ °F below 32°F)

Resolution:

0.1° to 999.9°; 1° above 1000°

**Temperature Coefficient:** 

0.01% of rdg/°C

Cold Junction Compensation: 0.0075°C/°C (0.0135°F/°F)

Ambient Temperature: 0 to 50°C (32 to 122°F)

**Storage Temperature:** 

-40 to 50°C (-40 to 122°F)

**Humidity:** 0 to 70% non-condensing **Power**: 110 Vac (standard),

Optional 230 Vac or 9 to 30 Vac/dc



Model BS6050 Single RTD Input

\$495

All models shown smaller than actual size

Model BS6000A Single Thermocouple Input

\$495



Model BS6051 Six-Channel RTD Selectable

\$595

Model BS6001A Six-Channel Thermocouple Selectable

\$595




#### Dimensions:

DP5000A, DP5050, DP5060: 96 x 48 x 120 mm (3.78 x 1.89 x 4.72") BS6000A, BS6050, BS6060: 118 x 57 x 150 mm (4.65 x 2.24 x 5.90") BS6001A,BS6051, BS6061: 148 x 67 x 190 mm (5.83 x 2.64 x 7.48")

Weight:


DP5000A, DP5050, BS5060: 255 kg (0.56 lb) BS6000A, BS6050, BS6060: 500 g (1.1 lb) BS6001A, BS6051, BS6061: 850 g (1.87 lb)





The DP5000A, B56000A and BS6001A can be used with infrared sensors for non-contact temperature measurements. Fields of view range from 90 to 0.06°.

# \$245





Companion Indicator: Six-Channel Wall Mount DP550 Series available in this section



### Input Ranges for DP5000 and BS6000 Series

Input	Rar	nge
J Iron-Constantan	-200 to 1200°C	-328 to 2192°F
	-200 to 1372°C	-328 to 2502°F
■ CHROMEGA® - Constantan	-200 to 1000°C	-328 to 1832°F
T Copper - Constantan	-200 to 400°C	-328 to 752°F
\$ Platinum - 10% Rhodium/ Platinum	-50 to 1767°C	-58 to 3212°F
R Platinum - 13% Rhodium/ Platinum	-50 to 1767°C	-58 to 3212°F
OMEGA-P® - Nicrosil OMEGA-N® - Nisil	-200 to 1300°C	-328 to 2372°F

To Order (Specify Model Number)			
Model No.	Price	Description	
DP5000A	\$245	T/C input panel meter with infrared sensor input*	
DP5050	245	RTD input panel meter	
DP5060	245	Thermistor input panel meter	
BS6000A*	495	Benchtop meter: 1 T/C and OS36, OS37 OS38 input	
BS6001A*	595	Benchtop meter: 6 T/C and OS36, OS37 OS38 inputs	
BS6050	495	Benchtop meter: 1 RTD input	
BS6051	595	Benchtop meter: 6 RTD input	
BS6060	495	Benchtop meter: 1 thermistor input	
BS6061	595	Benchtop meter: 6 thermistor inputs	

<sup>\*</sup> Can be used with **OS36-K-50** and **OS36-K-440**. Also will work with **OS37** and **OS38** units with either 20:1 or 100:1 fields of view. Comes complete with power cord, mating connector(s), operators' manual. OMEGACARE™ extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order.

**Ordering Example: B\$6050-C2**, single RTD input benchtop thermometer and RS-232 communications, \$495 + 40 = \$535. OCW-1 OMEGACARE<sup>SM</sup> extends standard 3-year warranty to a total of 4 years (\$53), \$535 + 53 = \$588

#### **Communications Options**

Order Suffix	Price	Description
-C2	\$40	RS-232 communications

#### **Power Options**

Model Number	Price	Description
-9/30	N/C	9 to 30 Vac/Vdc
-230	N/C	230 Vac

#### **Accessories**

Model Number	Price	Description
DP5000-BRACKETS	\$7	Replacement panel brackets
DP5000-SBRACKETS	7	Panel brackets with adjustable screws

For Additional Controllers, See Section P

Your One-Stop Source for Process Measurement and Control!

One Omega Drive | Stamford, CT 06907 | 1-888-TC-OMEGA (1-888-826-6342) | info@omega.com

## www.omega.com



#### **UNITED STATES**

www.omega.com 1-800-TC-OMEGA Stamford, CT.

#### **CANADA**

www.omega.ca Laval(Quebec) 1-800-TC-OMEGA

#### **GERMANY**

www.omega.de Deckenpfronn, Germany 0800-8266342

#### UNITED KINGDOM

www.omega.co.uk Manchester, England 0800-488-488

#### **FRANCE**

www.omega.fr Guyancourt, France 088-466-342

#### **CZECH REPUBLIC**

www.omegaeng.cz Karviná, Czech Republic 596-311-899

#### **BENELUX**

www.omega.nl Amstelveen, NL 0800-099-33-44



## More than 100,000 Products Available!

## Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

#### Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

## pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

## Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

## • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

#### Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters