


Miniature Electronic ice point™

MCJ Series
Starts at
\$99



MCJ-K, \$99, shown smaller than actual size with CASS-316G-12, \$28, sold separately, see page A-63.

The MCJ converts thermocouple voltages into 0°C referenced signals, for use with DMM's, voltage recorders and other electronic devices. The signals from the MCJ can be converted to temperatures, using the standard temperature-mV tables.

Features

High Stability Design

±1°C stability over entire 10 to 45°C operating range is assured through the computer designed solid state circuit.

Convenient

The MCJ is compatible with any standard thermocouple connector or jack; use ordinary copper wire to connect from the MCJ to any instrumentation for precise ice point referenced readings; with the standard adaptor pins, the MCJ can be used as either a female or male connector.

Calibration Mode

The OMEGA® MCJ can also be used in conjunction with a precision millivolt source in order to check and calibrate thermocouple thermometers and other thermocouple-ready instruments. Connections are made in a reverse mode to the MCJ. Namely, the output of the millivolt source is connected with copper wires as an input to the MCJ on the terminals labeled output. The input terminals then provide the compensated thermocouple output signal which is connected via appropriate type thermocouple wire to the input of the thermometer being checked.



RD46A-EPL, \$3347, shown.
See page S-49.



Female-to-male adaptor pins, included, can be used with MCJ Series for direct connection to panel. Shown larger than actual size.



For use with subminiature probes, see the TAS adaptor in Section G. Shown smaller than actual size.

ALL MODELS AVAILABLE FOR FAST DELIVERY!

Specifications

Reference Temperature:
0°C (32°F)
Accuracy: 0.5°C from 15 to 30°C;
1°C from 10 to 45°C
Storage Temperature:
-25 to 75°C (-13 to 167°F)
(without battery)
Output Impedance: <200 Ω
Compact Size
Weight: 57 g (< 2 oz)
Dimensions:
75 H x 25 W x 13 mm D
(2.94 x 1 x 0.5")

To Order (Specify Model Number)

Model No.	Price	Calibration	Color Code
MCJ-J	\$99	J	Black
MCJ-K	99	K	Yellow
MCJ-T	99	T	Blue
MCJ-E	99	E	Violet
MCJ-R/S	109	R and S	Green
MCJ-C	109	C*	Red
MCJ-D	109	D*	Red/white

*Comes with mating male thermocouple connector, battery and female-to-male adaptor pins.
* Not ANSI symbols. * C: W/5% Re vs. W/26% Re. * D: W/3% Re vs W/25% Re.
Ordering Example: MCJ-J, J calibration, \$99.*

Discount Schedule	
1 to 10 unitsNet
11 to 24 units5%
25 to 49 units10%
50 and upConsult Sales

Accessories

Model No.	Price	Description
MCJ-BATT-B	\$6	Replacement Battery
MCJ-BATT-R-A	6	Replacement Retro-fit kit for J, K, T, E
MCJ-BATT-R-B	6	Replacement Retro-fit kit for R, S
MCJ-BATT-R-D	6	Replacement Retro-fit kit for C, D

* MCJ-BATT-R, retro-fit kit will replace mercury batteries in units purchased prior to April 1995.

Cold Junction Compensator and Calibration Modules


**CJ Series
Starts at
\$250**



Discount Schedule	
1 to 10 unitsNet
11 to 24 units5%
25 to 49 units10%
50 and upConsult Sales

- ✓ Works as a Cold Junction Compensator or In Reverse as a Super Accurate Calibrator
- ✓ Extreme Versatility; Unit Can Be Plugged Directly into a Thermocouple or into a Jack Panel
- ✓ Color-Coded Thermocouple Calibration
- ✓ Bi-Directional Design
- ✓ Instantaneous Warm-Up
- ✓ High Reliability
- ✓ Rugged Case
- ✓ Long Battery Life

Customized Color Codes Also Available! Consult Sales.



CJ Series has male pins integral to unit for direct connection to panels. Shown smaller than actual size.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Model No.	Price	Color Code	Thermocouple Calibration
CJ-K	\$250	Yellow	CHROMEGA®-ALOMEGA®
CJ-J	250	Black	Iron-Constantan
CJ-T	250	Blue	Copper-Constantan
CJ-E	250	Violet	CHROMEGA®-Constantan
CJ-R/S	295	Green	Pt/13%-Rh/Pt/10%-Rh
CJ-G	295	Red	W/W/26% Re
CJ-C	295	Red	W/5%-W/26% Re
CJ-D	295	Red	W/3%-W/26% Re

Comes with quick disconnect male plug, banana jack adaptor and battery. CJ-BATT-B, replacement batteries, \$6 each. For units purchased prior to November 1994, order CJ-BATT-R, retro-fit kit, \$25. Please note: CJs are available with reference junction temperatures other than 0°C, \$250 each for calibrations K, J, T, E, \$295 for calibrations G, C, R/S, and D. Maximum reference temperature: 212°F. Consult Sales for details.

Specifications

Reference Temperature Setting:
0°C (32°F), standard
Compensation Accuracy: ±¼°C, @ 25°C ambient setting; ±½°C, from 15 to 35°C ambient setting; ±¾°C, from 10 to 50°C ambient setting
Storage Temperature:
-25 to 75°C (-13 to 167°F)
(without battery)
Output Impedance:
Less than 250 Ω, standard
Battery Life: 1500 hours or longer depending on calibration.
Highly Stable: Better than ±0.2°C at any stabilized temperature over the full 10 to 50°C range



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters