

Dual-Input Programmable Process Controllers

CN3000 Series
\$2452
 All Models



CN3001, \$2452, shown smaller than actual size.



- ✓ Up to 4 Independent Outputs Available as Plug-In Modules
- ✓ Dual Loop Control
- ✓ Heat Autotuning
- ✓ Multiple PID Sets
- ✓ 4-Line Vacuum Fluorescent Dot Matrix Display Shows Data and Graphics
- ✓ Universal Inputs—User Programmable for Thermocouple, RTD, Voltage, and Current
- ✓ NEMA 4 (IP65) Enclosure Available Option
- ✓ Transducer Power

GKMQSS-125G-6, low-noise thermocouple with ground strap, \$27, shown smaller than actual size. See page A-50.

PX605-10KGI, pressure transducer, \$315, shown smaller than actual size. Visit omega.com for details.

The CN3000 Series microprocessor-based ¼ DIN PID controllers provide accurate and reliable control of temperature, pressure, and other variables in both process and machine control applications. This menu-driven controller can be configured from either the front keypad or a remote PC. The front keypad offers direct digital data entry, direct access to desired displays, and soft-key macros. The CN3000 features universal inputs, an extensive selection of control programs, 4 selectable control outputs, and unparalleled application configuration and programming. The blue dot matrix display can show 4 lines of alphanumeric data plus graphics and is mounted with the keypad in a NEMA 4 (IP65) bezel.

Specifications

Accuracy: ±0.2% of range
Temperature Stability: 3 µV/°C
Operating Ambient: 5 to 55°C (41 to 131°F)
Storage Ambient: -40 to 75°C (-40 to 167°F)
Common-Mode Rejection: 140 dB typical; 120 dB minimum @ 60 Hz
Normal-Mode Rejection: 65 dB typical; 60 dB minimum @ 60 Hz
Resolution: 1° for thermocouple, 1° or 0.1° for RTD
Power: 117/240 Vac, 50/60 ±2 Hz; 4 W typical, 13.5 W max consumption
Inputs: 2 standard, user configurable; additional input available for remote setpoint or other function
Input Impedance: 10 MΩ minimum (T/C input)
Input Update: 12 updates per second

Input Filtering:

Selectable 1 to 256 samples
RTD Input: 100 Ω, α = 0.00385 or 0.00392 curve; platinum with 3-wire connection
Current Input: 0 to 20 or 4 to 20 mA; fully scalable to ±19,999 counts
Voltage Input: 0 to 10 mV up to 100 mVdc; fully scalable to ±19,999 counts
User Programmable: 128-segment linearizer for custom analog input
Sensor Break Protection: Display indicates "-----" if thermocouple or RTD input opens, outputs go off or to a preselected percent output, and alarm triggers go on
Display: Vacuum fluorescent dot matrix, 4 lines of alphanumeric data with 10 characters per line plus dot access for graphic displays
Keypad: 15 pushbutton keys on sealed NEMA 4 (IP65) front panel

Outputs: Up to 4, independent

Current Output:

4 to 20 mA into 750 Ω max

Voltage Output:

0 to 5 Vdc into 1 KΩ min

Solid State Relay:

Optically isolated form "A" contacts, 50 mA @ 240 Vac resistive

Electromechanical Relay: Form "C" contacts, rated 2.0 @ 240 Vac resistive

DC Trigger: 18 Vdc, 15 mA max

Open Collector: Requires external power up to 50 mA @ 32 Vdc

Alarm/Timer/Event Outputs: Any of the 4 outputs can be programmed as an alarm, timer or event output using SSR, EMR, DC trigger or OC board(s)

On/Off Output Deadband: 0 to 5% span, settable in 0.01% increments

Cycle Time: 1 to 511 seconds with 1 second resolution

Proportional Band: 5 to 4000 display units with 1 unit increments

Reset (Integral): 0.01 to 20 repeats per minute, settable in 0.01 increments; reset can be turned off by setting reset to 0

Anti-Reset Windup: Inhibits automatic reset when the process input is outside of the proportional band

Rate (Derivative): 0.01 to 5 minutes, settable in 0.01 minute increments; rate can be turned off by setting rate to 0

Drive Unit Deadband (Valve Positioner):

Settable 0.00 to 25.50% of span

Auto/Manual: Bumpless transfer

Autotune: User-initiated program optimizes PID parameters during "cold" start or on demand; PID values can be read and manually changed

Profile Control: Stores up to 99 profiles of up to 99 segments each with assured soak, multiple programmed events and link and loop programming position display

Control Limiters: Set rate of setpoint, change limit or rate of ramp on startup limit in units per selected time; set maximum or minimum output power in 1% increments


Enclosure: Assembly with plug-in output boards; NEMA 4 (IP65) front bezel when properly secured with tension bolt; polycarbonate flame-retardant bezel and rear terminal block

Weight:

1.6 kg (3.5 lb)



The CN3000 has a history graph that can display temperature over time.



Input Type and Range Table for Both Inputs

Input Types		Range: °C (°F)
J	Iron-Constantan	-212 to 1148 (-350 to 2100)
K	CHROMEGA®-ALOMEGA®	-212 to 1371 (-350 to 2500)
R	Pt-13%Rh/Pt	-45 to 1760 (-50 to 3200)
S	Pt-10%Rh/Pt	-45 to 1760 (-50 to 3200)
T	Copper-Constantan	-240 to 398 (-400 to 750)
N	OMEGA-P®-OMEGA-N®	-128 to 1260 (-200 to 2300)
E	CHROMEGA®-Constantan	-212 to 982 (-350 to 1800)
B	Pt-30%Rh/Pt-6%Rh	21 to 1815 (70 to 3300)
PLII	Platinel II	-73 to 1371 (-100 to 2500)
	Ni/Ni 18% Mo	-15 to 1310 (0 to 2390)
C	W5-Re/W26-Re	0 to 2315 (32 to 4200)
D	W3-Re/W25-Re	0 to 2371 (32 to 4300)
G	W/W26-Re	0 to 2315 (32 to 4200)
RTD	100 Ω Pt (0.00385)	-142 to 848 (-225 to 1560)
RTD	100 Ω Pt (0.00392)	-142 to 628 (-225 to 1160)

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
CN3001	\$2452	Single output, mechanical relay
CN3002	2452	Single output, AC SSR
CN3003	2452	Single output, 4 to 20 mA/0 to 5 Vdc
CN3004	2452	Single output, DC pulse/open collector

Comes with complete operator's manual.

Each unit supplied with mounting bracket and complete operator's manual.

Ordering Example: CN3001-R3-D3-D3, 4-output controller with 2 A mechanical relay and 2 DC pulse outputs, \$2452 + 56 + 56 + 56 = \$2620.

OCW-1, OMEGACARESM extends standard 1-year warranty to a total of 2 years (\$150), \$2620 + 150 = \$2770.

Plug-In Output Modules (Maximum 3 Output Slots Available)

Ordering Suffix	Price	Description
-R3*	\$56	2 A mechanical relay
-T3*	56	50 mA AC SSR
-F3*	107	4 to 20 mA/0 to 5 Vdc
-D3*	56	DC pulse/open collector

* **Note:** Each CN3000 controller can have up to 4 outputs (3 optional modules plus the original standard output).

Transducer Power Supply (Uses 1 Plug-In Output Slot)

Ordering Suffix	Price	Description
-X3*	\$110	Transducer power, 12/24 V, 25 mA DC

*Field installable. Can be ordered separately.

Ordering Example: CN3000-X3, field-installable transducer power supply module, \$110.





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters