

# RTD Digital Controllers

## 4200A Series



- ✓ High-Accuracy to 0.1% of Span
- ✓ Single and Dual Setpoint Models
- ✓ 1.0° and 0.1° Models
- ✓ Adjustable Proportion Band
- ✓ Bright LED Display

The OMEGA® 4200A Series is an ideal controller for RTD applications. This quality-built linearized instrument is available in both 1.0° and 0.1° resolution models. Higher accuracies, accuracies 5 to 10 times greater than the typical 1% meter indicating controller, are achieved through a unique linearizing technique.

### Specifications\*

#### RTD Input

**Type:** 100 Ω platinum;  
alpha = 0.00385 (DIN curve)

**Configuration:** 3 wires

**External Lead Wire Resistance Effect:** 0.1% span up to 10 Ω per lead wire leg

**Sensor Break Protection:** Built-in, upscale on open sensor

#### Calibration Accuracy:

**1.0° Resolution Model:**

±0.1% of span ±1 digit

**0.1° Resolution Model:**

±0.2% of span ±1 digit

**Stability:** 0.1% for 30 to 130°F, 0.1%, 10% to 15% line voltage

**Common Mode Rejection:** Maximum error ±1°C with 240 V, 60 Hz applied as common mode signal between sensor input and chassis ground

**Series Mode Rejection:** Maximum error ±1°C with series mode signal of 100 mV peak-to-peak @ 60 Hz

#### Control Output

##### 1st Setpoint

**(Adjustable Time Proportional):**

**Relay (Standard Model):** SPDT relay 7 A resistive @ 120 Vac, 5 A resistive at 240 Vac

**Option "T" (Triac):** Solid state plug-in triac rated 1 A holding and 10 A in-rush

**Option "F" (Current Proportional):** 4 to 20 mAdc into 1000 Ω maximum

**Option "DC" (DC Pulse):** 20 Vdc

\* Specifications and configurations subject to change as advances in technology allow.

#### 2nd Setpoint:

**Relay (On/Off Only):** SPDT, rated 3 A at 120 Vac

#### Adjustments

**Proportional Band (Gain):** 0 to 3% of span, or on/off; selectable

**Manual Reset (Offset):** Adjustable

**Cycle Time:** Automatically adjusts with load requirement to give least wear with minimum ripple (10 s minimum)

#### Display and Indications

**Temperature:** Filtered LED, 3 or 3½ digits, 2 readings per second update; readability is 1.0° or 0.1° (°F or °C), depending on model

**Setpoint:** By spring loaded switch, first or second setpoint is displayed in place of temperature; setpoint adjusted by 25 turn potentiometer; 1.0° or 0.1° setability

**Outputs:** LED indication for both first and second setpoints; LED are "on" when output drive signal present; "on/off" indication on relay and triac model; proportional intensity for option "F"

#### Temperature Overrange:

Red LED indication

#### Setpoint

**Resolution:** 1.0° or 0.1° (°F or °C), depending on model

**Repeatability:** ±0.1% to ±0.2% of span

**Adjustment:** By 25 turn potentiometer; see "setpoint" under "display and indication" section.

**Power:** 120/240 Vac (10%, -15%, 50/60 Hz); power consumption less than 5 W



4201APF1.

PR-10-2-100-1/4-12-E general-purpose RTD probe sold separately.

#### Environmental and Physical

**Operating Temperature:** -1 to 54°C (30 to 130°F)

**Weight:** 1 kg (2 lb)

**¼ DIN Case:** Metal; plug-in with screw terminal on rear; adjustable brackets for panel mounting; panel cutout is 92 x 92 mm (3.622 x 3.622")



OMEGACARE<sup>SM</sup> extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARE<sup>SM</sup> covers parts, labor and equivalent loaners.

Model Number	Sensor Type	Range	Resolution	Accuracy ±1 Digit	No. of Setpoints
4201APF1 4201APC1	100 Ω Platinum RTD	0 to 999°F 0 to 600°C	1°F 1°C	±0.1% of Span	Single
4202APF1 4202APC1		0 to 999°F 0 to 600°C	1°F 1°C		Dual
4201APF2 4201APC2	α = 0.00385 Ω/Ω°C	-199.9 to 199.9°F -199.9 to 199.9°C	1°F 1°C	±0.2% of Span	Single
4202APF2 4202APC2		-199.9 to 199.9°F -199.9 to 199.9°C	1°F 1°C		Dual

#### Output Options (No Additional Cost)

Order Suffix	Option Type (First Output Only)
-T	Triac
-F	4 to 20 mA
-DC	DC pulse

#### Accessory

Model No.	Description
CNQUENCHARC	Noise suppression RC snubber (2 leads), 110 to 230 Vac

Comes complete with operator's manual.

**Ordering Examples:** 4202APF1, RTD digital controller.

OCW-3, OMEGACARE<sup>SM</sup> extends standard 2-year warranty to a total of 5 years.