

Borescope with Detachable Screen for **Wireless** Viewing



- ✓ 88.9 mm (3.5") Color LCD Screen
- ✓ Detachable Screen for Wireless Viewing
- ✓ 12 mm (0.47") Diameter Camera-Tipped Probe
- ✓ Probe Features a Built-In Adjustable LED Lighting
- ✓ Records in Still Photo (JPEG) and Video (AVI), or View it Live
- ✓ NTSC or PAL Compatible
- ✓ 5 Languages: English, Spanish, French, Chinese, Portuguese

The HHB400 borescope inspection system is ideal for use in plumbing, construction and restoration, HVAC/R and any other application requiring the inspection of hard-to-reach or hard-to-see areas.

The HHB400 88.9 mm (3.5") TFT-LCD wireless color monitor can be detached from the unit for remote viewing up to 10 m (32.8') away.

The HHB400 comes with a 1 m (3.3') flexible waterproof IP67 obedient probe which retains the configured shape has a standard length of 1 m (3.3') and has optional probes up to 5.5 m (18').



Carrying case included.



Specifications

Camera Image Rotation: Always 6p

Zoom: 4x

Imaging Sensor: CMOS

Total Pixels:

704 x 576 (PAL)/320 x 240 (NTSC)

Horizontal View Angle: 50°

Transmission Frequency: 2468 MHz

Resolution: 320 x 240 pixels (NTSC)/704 x 576 pixels (PAL)

Minimum Illumination: 0 Lux

Modulation Type: FM

Bandwidth: 18 MHz

Power Source: Li-ion rechargeable batteries (included)

Unobstructed Effective Transmission Range: 10 m (32.8')

Waterproof Capacity: IP67 (probe only)

Dimensions: 186 L x 145 W x 41 mm D (7.3 x 5.7 x 1.6") (excluding flexible tube)

Weight (Approx.): 530 g (19 oz)

Monitor

Wireless: Up to 15.2 m (50')

LCD Screen Type: 88.9 mm (3.5") TFT-LCD

Effective Pixels: 320 (R.G.B.) x 240

Video System: PAL/NTSC

Transmission Frequency: 2414 MHz, 2432 MHz, 2450 MHz, 2468 MHz

Exterior Supply Voltage: 5 Vdc consumption current (maximum) 500 mA

Charge Time: 3 hours

Work Time: 2 hours

Picture/Video Pixels: 320 x 240

Video Size: 27M byte/minute

Frame Rate: 30 frame/second

Video Output Level:

0.9-1.3 Vp-p @75 Ω

Receiving Sensitivity: ≤ -85dBm

Dimensions: 100 W x 70 D x 25 mm H (4 x 2.8 x 1")

Weight (Approx.): 140 g (5 oz)

Operating Temperature: -10 to 50°C (14 to 122°F)

Operating Humidity: 15 to 85% RH

Language: English, Spanish, French, Chinese, Portuguese

Data Logging: SD card (included)



To Order

Model No.	Description
HHB400	88.9 mm (3.5") color LCD screen borescope

Accessories

Model No.	Description
PE14	Borescope probe 1 m (3.3') electrically insulated
P230-1	Replacement probe 1 m (3.3') obedient metal
P230-1X	0.9 m (2.9') obedient metal extension

Comes complete with MicroSD memory card, extension tools: (mirror, magnet, pick-up hook), video interconnect cable, USB cable, AC adaptor, li-ion rechargeable batteries, blow mold case, and operator's manual.

Ordering Example: HHB400, 88.9 mm (3.5") color LCD screen borescope.