



Seascope Waterproof Recording Video Inspection Systems

HHB660

Product Discontinued

Applications

- ✓ Inspect Sewer and Water Lines Carrying Running Water
- ✓ Diver or Snorkeler Can View Probe Video Under Water in Real Time*
- ✓ Marine Search and Rescue Operations

* Other "waterproof" inspection systems lack watertight grips and monitors.

- ✓ Includes USB Jack and Cable for PC Connection
- ✓ 10 Minute Auto Power Off
- ✓ Large and Crystal-Clear 8.7 cm (3.4") Color LCD
- ✓ Rotate Video 180° for Easier Reading of Labels and Serial Numbers
- ✓ Analog Video Out Jack
- ✓ Battery Powered (Included)
- ✓ Record Time/Date-Stamped Still Images and Videos on Included 2 GB MicroSD Memory Card
- ✓ Videos Can Be Panned by Joystick or Zoomed Up to 4X

Flexible-obedient, shape retaining probe.

HHB660 shown smaller than actual size.

Specifications

Field of View: 54°

Depth of Field: 15 to 150 mm (0.6 to 6")

Camera Illumination: 2 white LEDs

Sensor Resolution: 640 x 480 pixels

Sensor Sensitivity: 1.8V/lux-sec

Display: TFT, 8.7 cm (3.4") diagonal

Display Resolution: 320 x 240 pixels

Video Out Resolution:

640 x 480 pixels

Video Out Format: NTSC or PAL

Video Cable Length: 1.5 m (59")

Operating Temperature: 0 to 45°C (32 to 113°F)

Dimensions:

Camera-Tipped Probe: 10 mm diameter x 1 m long (0.39 x 39") close focus camera probe

Carrying Case:

330 x 267 x 114 mm (13.0 x 10.5 x 4.5")

Power Consumption: 400 mA maximum @ 6 Vdc

Weight of Carrying Case Including Contents: 500 g (1.1 lb)

Power Source: 4 "AA" batteries (included); 10 minute auto power off

The HHB660 is ideal for plumbing related tasks such as inspecting submerged structures and basements or pipes carrying running water. Suitable for inspecting the underside of boats.

The HHB660 is the first and only video inspection systems with an IP67 rated waterproof grip, monitor and camera-tipped probe. All 3 components will resist leaks at depths up to 2 m (6.6') for short periods (1 hour, maximum).

To Order

Model No.	Description
HHB660	Seascope, waterproof recording video inspection system
P600-2	2 m (6.6') probe
P600-3	3 m (9.8') probe

Comes complete with 1 m (39") probe, 4 "AA" batteries, video cable, set of 3 probe tip accessories (45° mirror, pickup hook and magnetic pickup), hard plastic protective case, 2 GB MicroSD memory card, USB jack and cable and operator's manual.

Ordering Example: HHB660, seascope, waterproof recording video inspection system.