


# “Banjo” Style Thermistor Sensor



- ✓ 300 Series Stainless Steel, Hermitically Sealed Unit
- ✓ Extremely Sensitive Sensor with Thin Cross-Section Tip Combined and Ultra-Small Diameter Extension Sheath
- ✓ Measures Water Baths, and Air and Surface Temperatures
- ✓ 3 m (10') PVC Insulated and Jacketed Cable with Phone Plug Connector Standard

To Order					
Model No.	Resistance @ 25°C	Interchangeability @ 0 to 70°C	Maximum Temperature	Cable Length	Cable Termination
ON-408-PP	2252 Ω	±0.1°C	100°C (212°F)	3 m (10')	Phone plug

## Accessories

Model No.	Description
450-ATH	Handheld thermometer, thermistor input
865F	Thermistor meter; in 0.1°F resolution mode, -70.0 to 40.1°F, -40.0 to 199.9°F
DP25-TH-A	Thermistor input meter/controller with analog output
HH41	Handheld thermistor thermometer

**Ordering Example:** ON-408-PP, “banjo” style thermistor sensor, 2252 Ω at 25°C, interchangeability of ±0.1°C, 3 m (10') of cable with a phone plug connector.