

ON-931-Series

Bolt-On Thermistor Sensor with Aluminum Flag Housing

Omega's two-wire ON-931 sensor features an improved housing design and increased gauge duplex wire which gives improved strain relief and pull strength. The bolt hole accepts #3 and #4 screws, and other screw sizes are available. These can be installed on flat surfaces by either being bolted or cemented onto the surface. Applications for this type of sensor include product performance testing; climate control/HVAC; printed circuit board manufacturing and cable manufacturing; environmental chamber temperature measurement.



Features

- Redesigned housing for improved strain relief
- Duplex wire now used for better wire protection
- Standard hole for #3 and #4 screw. #5, #6, and #8 screw sizes also available
- Small aluminum housing allows for installation on most flat surfaces
- Sensor can be bolted or cemented into place
- Accuracy is up to $\pm 0.1^{\circ}\text{C}$
- Temperature range is -80 to 100°C
- Resistance value: 2252, 3000, 5000, 10,000 or 30,000 Ohms
- Stripped ends standard, with phone plug connector available

Specifications

Process Temperature Range	-80 to 100°C
Resistance and Accuracy	2252, 3000, 5000, 10,000 and 30,000 Ohms Accuracy is $\pm 0.1^{\circ}\text{C}$ or 0.2°C
Connection Type	Stripped ends. Phone plug available (add "-PP" as suffix)
Dimensions and mounting screw	Barrel dimensions: 0.562 in. by 0.190 in. Mounting body dimension: 0.31 in. x 0.31 in. Screw sizes: #3 and #4 standard; other holes sizes available for #5, #6 and #8
Cable length	40 inches, with longer lengths available
Cable material	PFA coated duplex, 26 AWG
Mounting Style	Bolt-on or Cement-on

Ordering Example: ON-931-44004-40 Surface Thermistor probe with 2252 Ω thermistor element, with 0.116 in. hole for #3 or #4 screw. 40-inch PFA-coated leads, stripped ends.

ON-931 Available Resistances		
Resistance Suffix	Range and Accuracy	Resistance Value
-44004	-80 to 100°C, ± 0.2°C	2252 Ω
-44005	-80 to 100°C, ± 0.2°C	3000 Ω
-44006	-80 to 100°C, ± 0.2°C	5000 Ω
-44007	-80 to 100°C, ± 0.2°C	10,000 Ω
-44008	-80 to 100°C, ± 0.2°C	30,000 Ω
-44033	-80 to 75°C, ± 0.1°C	2252 Ω
-44030	-80 to 75°C, ± 0.1°C	3000 Ω
-44034	-80 to 75°C, ± 0.1°C	5000 Ω
-44031	-80 to 75°C, ± 0.1°C	10,000 Ω
-44032	-80 to 75°C, ± 0.1°C	30,000 Ω

ON-931 Screw size Designation		
Screw Size Suffix	Hole Dimension	Screw size
None	0.116 in.	#3 and #4
-H147	0.147 in.	#5 and #6
-H170	0.170 in.	#8

Ordering Example: ON-931-12-44033-40-H147: Surface Thermistor probe with 2252-ohm high accuracy thermistor element, with 0.147 in. hole for #5 and #6 screw, 40 in. leads and stripped ends

DRAWING

REVISIONS						
SYM	REVISION RECORD	ECN	DATE	DR	CHK	ENG
A	INITIAL RELEASE		3/8/2021	MA	KM	KL
B	ADD SIDE VIEW	3658	5/29/2021	MA	KM	KL
C	CHANGED DRAWING TITLE TO INCLUDE ON-931		6/11/2021	MA	KM	KL

STANDARD:

H147:

H170:

ALL DIMENSIONS FOR REFERENCE ONLY

① SIDE VIEW (ALL):

PROPRIETARY NOTICE THIS DRAWING IS PROPRIETARY PROPERTY OF OMEGA ENGINEERING, INC. IT IS SUPPLIED IN CONFIDENCE FOR A PARTICULAR LIMITED PURPOSE ONLY AND RECEIPT HEREOF IS NOT AUTHORIZED TO REPRODUCE THE DRAWING NOR MAKE THE INFORMATION DISCLOSED HEREIN FOR OTHER USE OR IN ANY MANNER THAT WOULD BE PREJUDICIAL TO OMEGA ENGINEERING, INC. UNLESS OTHERWISE NOTED.	TOLERANCES (UNLESS OTHERWISE SPECIFIED)	APPROVALS		DATE		 RTD-831 & ON-931 HOLE SIZE DRAWING
	DECIMAL	DR	MA	03/08/2021		
	FRACTIONAL	CHK	KM	03/08/2021		
	MILS	APPR	KL	03/08/2021		
DRAWN BY: _____ CHECKED BY: _____ PROJECT: _____ PART NO: _____ PART FILE: RTD-831	DRAWN BY: _____ CHECKED BY: _____ PROJECT: _____ PART NO: _____ PART FILE: RTD-831	DRAWN BY: _____ CHECKED BY: _____ PROJECT: _____ PART NO: _____ PART FILE: RTD-831	DRAWN BY: _____ CHECKED BY: _____ PROJECT: _____ PART NO: _____ PART FILE: RTD-831	DRAWN BY: _____ CHECKED BY: _____ PROJECT: _____ PART NO: _____ PART FILE: RTD-831	DRAWN BY: _____ CHECKED BY: _____ PROJECT: _____ PART NO: _____ PART FILE: RTD-831	DRAWN BY: _____ CHECKED BY: _____ PROJECT: _____ PART NO: _____ PART FILE: RTD-831