

Compact Non-Contact Temperature Sensor With Controllable Emissivity Setting



OS212, OS152, OS302 and
OS802 Series



Optional†



OS212-LT sensor head shown with optional OS210-PT emissivity adjuster (actual size).

- ✓ Temperature Range -20 to 500°C (-4 to 932°F)
- ✓ 2-Wire 4 to 20 mA Output Proportional to Target Temperature
- ✓ 4 to 20 mA Input to Control Emissivity Setting
- ✓ Optional Manual Emissivity Adjuster
- ✓ Field of View: 2:1, 15:1, 30:1 or Close Focus
- ✓ Fast Response with High Stability
- ✓ Stainless Steel Housing, Sealed to IP65
- ✓ Quick and Easy Installation
- ✓ Optional Air/Water Cooled Housing, Air Purge Collar, Laser Sighting Tool and Mounting Brackets

The Omega™ Infrared Series is a range of high quality, low cost, compact sensors which measure the temperature of inaccessible or moving objects and materials. They measure temperatures from -20 to 500°C (-4 to 932°F), accurately and consistently, with an outstanding response time of 240 mS. Omega sensors transmit the target temperature as a 4 to 20 mA output and offer a simple solution for most non-contact temperature measurement applications. The sensor's emissivity setting can be adjusted from 0.2 to 1.0 to cope with different target materials and is controlled by a 4 to 20 mA input. This gives the opportunity to adjust the emissivity setting automatically from a programmable logic controller (PLC). Alternatively the emissivity setting can be adjusted manually using the OS210-PT. If the 4 to 20 mA input is left open or short-circuit the emissivity setting defaults to 0.95.

† Refer to accessory chart on J-3 for NIST calibration ordering information.

Specifications

Infrared Sensor Output: 4 to 20 mA

Accuracy: $\pm 1\%$ of reading or $\pm 1^\circ\text{C}$ whichever is greater

Repeatability: $\pm 0.5\%$ of reading or $\pm 0.5^\circ\text{C}$ whichever is greater

Emissivity: 0.2 to 1.0 via 4 to 20 mA input

Response Time t_{90} : 240 mS (90% response)

Spectral Range: 8 to 14 μm

Supply Voltage: 24 Vdc (28 Vdc max)

Min Sensor Voltage: 6 Vdc

Max Loop Impedance: 900 Ω (4 to 20 mA output)

Input Impedance: 50 Ω

Mechanical

Construction: Stainless Steel

Dimensions: 103 L x 18 mm D (4.05 x 0.71")

Thread Mounting: M16 x 1 mm pitch

Cable Length: 1 m (3.3') longer lengths available to order

Weight: 95 g (3.4 oz) with cable

Environmental Rating: IP65

Ambient Temperature Range: 0 to 70°C (32 to 158°F)

Relative Humidity: 95% max non-condensing

Tune Emissivity Adjuster Specifications (OS210-PT)

Output: 4 to 20 mA

Supply Voltage: 24 Vdc (13V to 28 Vdc)

Display Format: 3.5 digit LCD

Display Units:

Emissivity: 0.2 to 1.0

Current: 4 to 20 mA

Adjustment: Pushbuttons (raise/lower/set)

Mechanical

Construction: Polycarbonate with gasket, transparent lid (PC) and quick release screws

Mounting: Surface

Dimensions: 65 H x 50 W x 35 mm D (2.56 x 1.97 x 1.38")

Weight: 72 g (2.5 oz)


Environmental

Rating: IP65

Ambient Temperature Range: 0 to 70°C (312 to 158°F)

Relative Humidity: 95% max non-condensing

Wiring Diagram and Distance: Spot Ratios



To Order			
Model No.	Optics	Temperature Range	Output with Adjustable Emissivity
OS212-LT	2:1	-20 to 100°C (-4 to 212°F)	4 to 20 mA
OS212-MT	2:1	0 to 250°C (32 to 482°F)	4 to 20 mA
OS152-LT	15:1	-20 to 100°C (-4 to 212°F)	4 to 20 mA
OS152-MT	15:1	0 to 250°C (32 to 482°F)	4 to 20 mA
OS152-HT	15:1	0 to 500°C (32 to 932°F)	4 to 20 mA
OS302-LT	30:1	-20 to 100°C (-4 to 212°F)	4 to 20 mA
OS302-MT	30:1	0 to 250°C (32 to 482°F)	4 to 20 mA
OS302-HT	30:1	0 to 500°C (32 to 932°F)	4 to 20 mA
OS802-LT	Close-focus	-20 to 100°C (-4 to 212°F)	4 to 20 mA
OS802-MT	Close-focus	0 to 250°C (32 to 482°F)	4 to 20 mA
OS802-HT	Close-focus	0 to 500°C (32 to 932°F)	4 to 20 mA

Comes complete with sensor head, 1 m (3.3') cable and operator's manual.

Ordering Examples: OS212-MT, 2:1 optics, 0 to 250°C (32 to 482°F) temperature range, 4 to 20 mA output, adjustable emissivity.

OS302-HT, 30:1 optics, 0 to 500°C (32 to 932°F) temperature range, 4 to 20 mA output, adjustable emissivity.

Options (Not Field Installable)

Suffix	Description
-WC	For air/water cooled jacket (includes air purge collar) must be ordered with sensor; cannot be retrofitted
-CE(*)	Cable extended, for uncooled PE sensor, 30 m (98') max total cable length
-CEHT(*)	Cable extended, high temperature, for cooled PE sensor, 30 m (98') max total cable length

* 1 m (3.3') cable is included as standard on every sensor. Extended cable is added to that length, add suffix to model number. Insert cable length in meters.

Accessories

Model No.	Description
OS210-PT	Tune emissivity adjuster, 24 Vdc input, 4 to 20 mA output
OS210-FBS	Fixed bracket for compact sensors
OS210-ABS	Adjustable bracket for compact sensors
OS210-APSW	Air purge collar for compact 2:1 sensors
OS210-APSN	Air purge collar for compact 15:1, 30:1 and close-focus sensors
OS210-LSTS	Laser sighting tool for compact sensors
CAL-3-IRT†	NIST-traceable calibration

Power Supplies

Model No.	Description
PSR-24S	Regulated power supply, US plug, 90 to 264 Vac input, 24 Vdc output, 400 mA, screw terminals, UL
PSR-24L	Regulated power supply, US plug, 90 to 264 Vac input, 24 Vdc output, 400 mA, stripped leads, UL
PSR-24L-230	Regulated power supply, european plug, 230 Vac input, 24 Vdc output, 400 mA, stripped leads, CE
TX8-100	Power/output cable, 30 m (100')