

Low-Cost Infrared Thermometer with Built-In Dot Laser Sighting



- ✓ Fixed 0.95 Emissivity
- ✓ 10:1 Field of View
- ✓ Long Battery Life
- ✓ Large, Backlit LCD Screen
- ✓ Auto Power-Off
- ✓ Soft Carrying Case Included

PATENTED

Covered by U.S. and International patents and pending applications.

The OS561 is an economical tool for temperature measurements, with non-contact measurement capability, user-friendly 2-key operation, and max and hold modes. The backlit LCD screen and the laser stay on when the trigger is depressed; auto power-off is fixed at 15 seconds for the LCD screen. The OS561 uses 2 "AAA" batteries (included) and has an ultra-long battery life.

Specifications

Measurement Range: -60 to 500°C

(-76 to 932°F)

Accuracy: ±2% of reading or 2°C (4°F), whichever is greater

Resolution: 1°C/1°F (0.1°C/0.1°F between -9.9 and 199.9)

Response Time: 1 s

Emissivity: Fixed 0.95

Field of View: 10:1

Operating Temperature: 0 to 50°C (32 to 122°F)

Power: 2 "AAA" alkaline batteries (included)

Battery Life: 18 hour continuous use with laser and backlight; 180 hour without laser and backlight

Dimensions:


175.2 L x 39.0 D x 71.9 mm W (6.9 x 1.53 x 2.8")

Weight: 179 g (6.3 oz) including batteries



OS561.

CAUTION! – This product is not intended for medical use or use on humans



To Order

Model No.	Description
OS561	10:1 infrared thermometer

Comes complete with soft carrying case, 2 "AAA" alkaline batteries and operator's manual.
Ordering Example: OS561, 10:1 infrared thermometer.