

FILTER FAN

NEW

FF018 Series
Starts at
\$73



- Very Low Noise
- Minimal Depth in Enclosure
- Functional Design
- Time-Saving Installation

In addition to the easy mounting axial fan, the self-adhesive seal of the mounting frame prevents dust and water from entering the cabinet. The functional design of the intake and exhaust fan hoods very effectively prevents direct infiltration of falling water and dust. The design also provides air channeling which makes the filter fan particularly quiet in operation.

SPECIFICATIONS

Free Blowing Air Flow: 21 m³/h (12 cfm), 60 m³/h (35 cfm), 102 m³/h (55 cfm)

Voltage: 120 Vac, 60 Hz

Environmental Ratings: UL 12/NEMA 3S (IP54)

Agency Approvals: UL, VDE

Power Consumption:

FF01801800001: 13 W

FF01801801001, FF01801802001: 15 W

Air Flow with Exit Filter: 16 m³/h (9 cfm), 42 m³/h (24 cfm), 68 m³/h (40 cfm)

Current Consumption:

FF01801800001: 160 mA

FF01801801001, FF01801802001: 180 mA

Average Noise level at 0.9 m (3') (DIN EN ISO 4871):

FF01801800001: 31 dB (A)

FF01801801001: 40 dB (A)

FF01801802001: 39 dB (A)

Weight:

FF01801800001: 0.6 kg (1.3 lb)

FF01801801001: 1.0 kg (2.2 lb)

FF01801802001: 1.3 kg (2.9 lb)

Filter Fan Housing: Plastic, UL 94V-0, light gray


Filter Fan Hood: Plastic, UL 94V-0, light gray, weather proof and UV light resistant according to UL 746C (f1)

Filter Mat: Medium grade 350 g/m², filtering degree 94% for particle Ø <10 µm, G4 (EN 779)




FF01801800001, \$73, shown smaller than actual size.


Dimensions:
mm (in)



FF01801800001



FF01801801001



FF01801802001

Filter Material: Synthetic fiber with progressive construction, temperature resistant to 100°C (212°F), self-extinguishing class F1. Moisture resistant to 100% RH. Can be cleaned by washing or vacuuming for reuse. Replacement filter mats available on request.

Axial Fan: Ball bearing, aluminum frame, plastic impeller UL 94V-0, operational life min 50,000 hrs at 25°C (77°F) (RH 65%)

Operating Temperature: -45 to 70°C (-49 to 158°F), 2 lead wires 102 mm (4") long with pressure clamps, type AWG 14 max

Mounting Frame: With double sided industrial adhesive band for affixing to the outside of enclosure; certain operating circumstances may make the additional use of screws necessary

Operating/Storage Temperature: -45 to 70°C (-49 to 158°F)

Protection Type: NEMA 3S (IP54) (using fine filter mat type F5 increases the protection type to NEMA 4 (IP55) but reduces the air volume)

Protection Class: I (grounded)

To Order (Specify Model Number)

AVAILABLE FOR FAST DELIVERY!

MODEL NO.	PRICE	DESCRIPTION
FF01801800001	\$73	Standard filter fan, 24 m ³ /h (14 cfm)
FF01801801001	82	Standard filter fan, 63 m ³ /h (40 cfm)
FF01801802001	96	Standard filter fan, 117 m ³ /h (69 cfm)

Comes complete with operator's manual.

Ordering Examples: FF01801800001, filter fan, 24 m³/h (14 cfm), \$73. FF01801802001, filter fan, 117 m³/h (69 cfm), \$96.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters