

# Models Q and QP

Head 1.16" OD

## Model Q With 6" Stem



Used by inspectors, technicians, maintenance and service men for general testing and checking of refrigeration, hot asphalt, dairy and food products, air conditioning systems, stack temperatures and hundreds of other uses where a quick temperature indication is needed.

Made entirely of corrosion resistant stainless steel (except optically clear crystal and aluminum dial). Brightly polished head, bezel and stem for sanitation and easy cleaning.

### Ranges and °Divisions

Fahrenheit	
Range	Div
*25 to 125°F	1°
-40 to 160°F	2°
0 to 200°F	2°
0 to 250°F	2°
50 to 300°F	2°
50 to 500°F	5°
150 to 750°F	10°
200 to 1000°F	10°

Celsius	
Range	Div
-40 to 70°C	1°
0 to 100°C	1°
-10 to 110°C	1°
0 to 150°C	1°
0 to 300°C	1°
50 to 400°C	5°

Dual	
Range	Div
0 to 200°F	2°
-10 to 90°C	1°
50 to 500°F	5°
10 to 260°C	5°
200 to 1000°F	10°
100 to 500°C	10°

\* Minimum stem length 4".

To order Q, specify\*:

### Model - Range - Stem Length - Mounting

**Ordering Examples:** Q--40-160F-9-PLAIN, model Q with -40 to 160°F range, 9" stem and plain bushing.

Reset bushing now available, consult Sales Department.

**Q-0-200F-4-1/2**, model Q with 0 to 200°F range, 4" stem and 1/2 NPT mounting.

**Q-0-200F-4-1/4**, model Q with 0 to 200°F range, 4" stem and 1/4 NPT mounting.


\* For stem lengths and pricing visit us online

To order QP, specify: Model - Range


**Ordering Example:** QP-25-125F, model QP with 25 to 125°F range. Reset bushing standard (on QP models), 5" stem length. Pointed stem available, add "-PS" for an additional cost.



## Model QP With 5" Stem and Pocket Case



Model Q, for stem lengths and pricing visit us online



Model QP, only 5" stem length available.

A handy, strong pocket case (with pen type clip for safe pocket carrying that prevents accidental loss) is supplied when ordering the Model "QP".



## Model G

All Stainless Steel (except dial)  
Head 1.73" OD


### Ranges and °Divisions

Fahrenheit	
Range	Div
*25 to 125°F	1°
-100 to 100°F	2°
-40 to 160°F	2°
0 to 200°F	2°
0 to 250°F	2°
20 to 240°F	2°
50 to 300°F	2°
50 to 500°F	5°
100 to 800°F	10°
150 to 750°F	10°
200 to 1000°F	10°
0 to 220°F	10°
-50 to 300°F	10°

Celsius	
Range	Div
-50 to 50°C	1°
-50 to 100°C	2°
-40 to 70°C	1°
0 to 100°C	2°
-10 to 110°C	1°
-20 to 120°C	1°
*0 to 50°C	1°
0 to 150°C	1°
0 to 300°C	5°
0 to 400°C	5°
50 to 400°C	5°
0 to 200°C	5°

Dual	
Range	Div
0 to 200°F	2°
-10 to 90°C	2°
50 to 500°F	2°
10 to 260°C	2°
200 to 1000°F	2°
100 to 500°C	1°
-100 to 100°F	2°
-70- to 40°C	2°
-40 to 160°F	5°
-40 to 70°C	5°
20 to 240°F	10°
-10 to 115°C	10°
*25 to 125°F	10°
-5 to 50°C	10°
50 to 300°F	10°
10 to 150°C	10°

\* Minimum stem length 4".



## Model G With 6" Stem

To order G, specify\*:

### Model - Range - Stem Length - Mounting

**Ordering Examples:** G-40-160F-9-PLAIN, model G with -40 to 160°F range, 9" stem and plain bushing.

External mounting bracket available for an additional cost. Reset bushing now available, consult Sales Department.

**G-0-100C-21/2-1/4**, model G with 0 to 100°C range, 2 1/2" stem and 1/4 NPT mounting.

\* For stem lengths and pricing visit us online

