

Isolated

Linearized

Field Rangeable

# 170 Basic Unit A/IN € A/OUT € € DIN Rail 2-Wire Temperature Transmitters DRA-TCI-2 Thermocouple Input Model DRA-RTI-2 RTD Input Model

Models DRA-TCI-2 and DRA-RTI-2 are linearized temperature transmitters that produce a 4-20 mA process signal that is directly proportional to temperature. These transmitters have exceptionally high input to output common mode rejection (CMR), a high degree of filtering that eliminates false output signals and provides a low ripple current.

Model DRA-TCI-2 is available for thermocouple types J, K, T, E, R, S or B and provides exceptional temperature linearization by applying eight segment linearization circuitry.

Model DRA-RTD-2 accepts 2 or 3 wire Pt-100 RTDs, alpha = 0.00385. Both models are field rangeable using a set of six internal dip switches for coarse ranging and front accessible zero and span potentiometers for fine adjustment. Test terminals are provided to monitor the transmitter's 4-20 mA output without disturbing the actual process loop.

### Specifications

### **COMMON SPECIFICATIONS**

Output: 4 to 20 mA

Supply Voltage: 10-40 Vdc

**Loop Resistance:**  $R_{max}$  (ohms) =  $(V_{supply} - 10) / 0.02$ 

Temperature Stability: <±0.1% of span/°C

**Common Mode Rejection (CMR):** 127 dB typical dc to 60 Hz

**Isolation:**1500 Vdc or peak ac **Response Time:** 160 msec (0 to 98%)

Test Terminals: 40 to 200 mV represents 4-20 mA

**Ambient Temperature Range:** -20 to 70°C (-4 to 158°F), 5 to 95% RH

Storage Temperature Range: -30 to 85°C (-22 to 185°F)

**Field Ranging:** done by three "zero" DIP switches, three "span" DIP switches and two fine tuning potentiometers

**Enclosure:** polycarbonate, IP40 protection

**Terminal Housing:** polycarbonate, IP20 protection **Mounting:** 35 mm DIN rail **Dimensions:** 3.23" H x 0.9" W x 3.90" D (82 x 22.5 x 99 mm) **Weight:** 4.6 oz. (130 g **Model DRA-TCI-2 Input:** Thermocouple types J, K, T, E,R,S,B (see thermocouple input types and ranges table)

**Burnout Protection:** upscale **Cold Junction Error:** ±0.9°C typical for 0 to 60°C ambient change (±3°C for types R and S)

Accuracy (Including Linearity):  $\pm 0.08\%$  of span for type K,  $\pm 0.1\%$  to  $\pm 0.2\%$  for other thermocouple types, typical

#### **MODEL DRA-RTI-2**

**Input:** 2 or 3-wire Pt-100 RTD, alpha = 0.00385

Accuracy (Including Linearity, Hysteresis and Repeatability): <±0.1% of span

Minimum Span: 79°F (26°C) Input Span Range:

79 to 1490°F (26 to 810°C) adjusted by three DIP switches and span potentiometer

Input Zero Range: -80 to 450°F (-62 to 232°C) adjusted by three DIP switches and zero potentiometer

### Thermocouple Input Types and Ranges

Туре	Input Range Low, °F (°C)	Input Range High, °F (°C)	Min Span °F (°C)	
K	32 (0)	2462 (1350)	180 (100)	
J   T	32 (0) 32 (0)	1400 (760) 752 (400)	180 (100) 180 (100)	
E	32 (0)	1832 (1000)	180 (100)	
R S	32 (0) 32 (0)	3092 (1700) 3092 (1700)	1170 (650) 1170 (650)	
В	32 (0)	3092 (1700)	1170 (650)	
To Order (Specify Model Number)				

To Order (Specify Model Number)			
Model No.	Price	Description	
DRA-TCI-2-(*)	\$210	DIN rail 2-wire thermocouple input temperature transmitter	
DRA-RTI-2	170	DIN rail 2-wire RTD input temperature transmitter	
DRN-PS-1000	150	Power supply, 95-240 Vac input, 24 Vdc @ 1A output	

Each unit supplied with complete owner's manual. \*Specify thermocouple type J,K,T,E,R,S, or B.

**Ordering Example:** DRA-TCI-2-J DIN rail 2-wire J thermocouple input temperature transmitter with DRN-PS-1000 power supply, \$210 +150 = **\$360**.

Lead Compensation Error: <0.1°C/20 Ohms lead resistance Sensor Excitation: 1 mA



### H-59

# omega.com®

Your One-Stop Source for Process Measurement and Control!

One Omega Drive | Stamford, CT 06907 | 1-888-TC-OMEGA (1-888-826-6342) | info@omega.com

# www.omega.com



UNITED STATES www.omega.com 1-800-TC-OMEGA Stamford, CT.

CANADA www.omega.ca Laval(Quebec) 1-800-TC-OMEGA

GERMANY www.omega.de

Deckenpfronn, Germany 0800-8266342 UNITED KINGDOM www.omega.co.uk Manchester, England 0800-488-488

FRANCE www.omega.fr Guyancourt, France 088-466-342

CZECH REPUBLIC www.omegaeng.cz Karviná, Czech Republic 596-311-899

> BENELUX www.omega.nl Amstelveen, NL 0800-099-33-44



# More than 100,000 Products Available!

## Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

## Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

# pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

# Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

# Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

## Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters

## ● click here to go to the omega.com home page ●