MEDIUM-WEIGHT-OIL IMMERSION HEATER



- ✓ 2-Element Design
- ✓ 2 NPT Steel Screw Plug
- Heavy-Duty Steel Sheath for Use with Medium-Weight Oils
- Low Watt Density
- 🖊 2 to 6 kW
- 240 and 480 V, 1 Phase
- General Purpose NEMA 1 (IP00) Enclosure or Moisture-Resistant/ Explosion-Resistant^{2†} Enclosure Available[†]


CAUTION AND WARNING! Fire and electrical shock may result if products are used improperly or installed or used by non-qualified personnel. See inside back cover for additional warning.

Order (Creatify Madel Numb

SPECIFICATIONS

Wattage: 2 to 6 kW Power: 240 and 480 V, 1 phase Watt Density: 15 W/in² Sheath: 12 mm (0.475") diameter Screw Plug: 2 NPT steel Enclosure: E1 general purpose, NEMA 1 (IP00) rated¹, or E2 moistureresistant/explosion-resistant enclosure²

Please Note: This immersion heater should be used with an approved temperature control device to ensure safe operation. See the Section P for our selection of process controllers.



TTO-2020/240, \$377, shown smaller than actual size.

MTO-2060E2/480, \$948, shown smaller than actual size.

MOST POPULAR MODELS HIGHLIGHTED!

io urder (<i>Specity model number)</i>									
				E1 General Purpose Enclosure ¹			E2 Moist-/Explos-Res. Enc. ^{2†}		
kW	W/in ²	No. Htg. Elem.	Dim. B cm (in)	Model No.	Price	Wt. kg (lb)	Model No.	Price	Wt. kg (lb)
2	15	2	63 (24%)	MTO-2020/*	\$377	7 (4)	MTO-2020E2/*	\$572	3 (7)
2.66	15	2	83 (32¾)	MTO-2026/*	455	3 (6)	MTO-2026E2/*	649	4 (9)
3.33	15	2	102(40¼)	MTO-2033/*	529	3 (7)	MTO-2033E2/*	724	5 (10)
4	15	2	121 (47¾)	MTO-2040/**	606	3 (7)	MTO-2040E2/**	796	5 (10)
5	15	2	146 (57½)	MTO-2050/*	674	4 (8)	MTO-2050E2/*	866	5 (11)
6	15	2	172 (67¾)	MTO-2060/*	759	4 (9)	MTO-2060E2/*	948	5 (12)

* Designate voltage: insert "240" for 240 Vac or "480" for 480 Vac.

** Designate voltage: insert "208" for 208 Vac, "240" for 240 Vac or "480" for 480 Vac.

[†] Caution: Explosion-resistant type E2 construction refers to heater design features that provide explosion-resistant containment of electrical wiring according to National Electric Code. Use of heaters at excessive temperatures can create hazardous conditions that can lead to fire. Not intended for use in hazardous areas.

Consult Section Z for data on allowable watt densities for more viscous materials.

Higher kW ratings are available. Contact OMEGALUX®.

¹ Heaters with general purpose enclosures are UL listed and CSA certified.

² Heaters with moisture-resistant/explosion-resistant enclosures are CSA NRTL/C certified.

Ordering Example: MTO-2020/240, 2 kW heater powered by 240 Vac, \$377.

omega.com®

Your One-Stop Source for Process Measurement and Control!

One Omega Drive | Stamford, CT 06907 | 1-888-TC-OMEGA (1-888-826-6342) | info@omega.com

www.omega.com



UNITED STATES www.omega.com 1-800-TC-OMEGA Stamford, CT.

CANADA www.omega.ca Laval(Quebec) 1-800-TC-OMEGA

GERMANY www.omega.de

Deckenpfronn, Germany 0800-8266342 UNITED KINGDOM www.omega.co.uk Manchester, England 0800-488-488

FRANCE www.omega.fr Guyancourt, France 088-466-342

CZECH REPUBLIC www.omegaeng.cz Karviná, Czech Republic 596-311-899

> BENELUX www.omega.nl Amstelveen, NL 0800-099-33-44



More than 100,000 Products Available!

Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters

● click here to go to the omega.com home page ●