

Series 445S Standard Threaded Well for Industrial Glass Thermometers *



Application:

Fits liquid-in-glass thermometers made to S.A.M.A. standards. Tapered bore is made 0.008" oversize to eliminate possibility of thermometer bulb expanding into the well, thus preventing removal.

Connection Size:

3/4 and 1 NPT are standard. Other thread sizes are available upon request.

Protective Coatings for Thermowells:

- Resist Corrosion
- For Chemical Baths
- Color-Coded Sensors for Process Control

* See Vapor Actuated Assembly on page E-17 for Additional Wells in the 445 Series

- Available in PFA, Epoxy and other materials. Consult Sales Department for complete information.


Materials:

Carbon Steel (C-1018), Brass (ASTM B-16), A.I.S.I. 304, A.I.S.I. 316, Monel. Many other materials available upon request.

Additional Designs:

Other designs of wells to fit this class of thermometer are available. These include socket weld, heavy duty and flanged types.


Series 445S—General Use



Metric Models Available!
See Pages B-37 and B-38

Shown smaller than actual size.

MOST POPULAR MODELS HIGHLIGHTED!



To Order (Specify Model Number)									
Ext Thread P	Model Number	Materials and Prices				Nominal Bulb Lgth	Bulb Lgth A	Insert Lgth U	Shank Dia. Q
		Stainless Steel 304	Stainless Steel 316	Carbon Steel	Brass				
3/4 NPT	3/4-445S-S31/2-(*)	\$46.50	\$58.50	\$30.00	\$30.00	3 1/2	3 5/8	2 9/16	—
	3/4-445S-S6-(*)	70.50	88.00	44.00	44.00	6	6 1/8	5 1/16	7/8
	3/4-445S-S9-(*)	107.50	135.00	68.00	68.00	9	9 1/8	8 1/16	7/8
	3/4-445S-S12-(*)	146.00	183.00	83.50	83.50	12	12 1/8	11 1/16	7/8
	3/4-445S-S18-(*)	176.00	222.00	110.50	110.50	18	18 1/8	17 1/16	7/8
	3/4-445S-S24-(*)	228.00	279.00	133.00	133.00	24	24 1/8	23 1/16	7/8
1 NPT	1-445S-S31/2-(*)	\$46.50	\$58.50	\$30.00	\$30.00	3 1/2	3 5/8	2 9/16	—
	1-445S-S6-(*)	70.50	88.00	44.00	44.00	6	6 1/8	5 1/16	1
	1-445S-S9-(*)	107.50	135.00	68.00	68.00	9	9 1/8	8 1/16	1
	1-445S-S12-(*)	146.00	183.00	83.50	83.50	12	12 1/8	11 1/16	1
	1-445S-S18-(*)	176.00	222.00	110.50	110.50	18	18 1/8	17 1/16	1
	1-445S-S24-(*)	228.00	279.00	133.00	133.00	24	24 1/8	23 1/16	1

* Specify material type "304SS" for 304 Stainless Steel, "316SS" for 316 Stainless Steel, "CS" for Carbon Steel or "BRASS" for brass. PFA coating available, see page B-16.

Ordering Example: 3/4-445S-S6E-304SS, 304 stainless steel thermowell with 3/4 NPT external thread, 0.445" internal diameter for a glass thermometer, 5/16" insertion length and a 6" nominal bulb length, \$70.50.

For Assistance in Choosing Head and Well Assemblies, See guide on page B-5. These wells are compatible with OMEGA® NB1, NB2 (page B-8); PR-12, PR-14, and NPT-style probes (page C-95), as well as DialTemp™ Thermometers (page E-11).

Pressure-Temperature rating—lb per square inch

Well Type	Material	Temperature — °F					
		70°	200°	400°	600°	800°	1000°
3/4"-445S and 3/4"-445L (See Note)	Brass	640	575	100	—	—	—
	Carbon Steel	720	690	660	630	480	210
	A.I.S.I. 304	940	850	770	740	720	625
	A.I.S.I. 316	940	940	875	850	840	700
	Monel	900	825	740	730	710	210
1"-445S and 1"-445L (See Note)	Brass	1470	1320	230	—	—	—
	Carbon Steel	1650	1590	1520	1450	1100	480
	A.I.S.I.-304	2150	1950	1770	1710	1670	1430
	A.I.S.I.-316	2150	2150	2010	1960	1920	1610
	Monel	2070	1900	1700	1690	1640	480

Note: Wells with 2 9/16" insertion length have three times the pressure ratings shown. See Page B-31 for Maximum Fluid Velocity.

Increase Response Rate!
Use OT-201 Conductive Silicon Paste; see page B-40.

Discount Schedule	
1-10.....	Net
25-100.....	20%
11-24.....	10%
101 and up....	Consult Sales

Discounts apply to similar thermowells.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters