DEFINITE PURPOSE CONTACTORS

C25 Series



- Open Style with Metal Mounting Plate
- 1-, 2- and 3-Pole Models
- 25 to 75 A Capacity
- Kits for Side Auxiliary Contact
- NEMA 1 Enclosure Available

Definite purpose (DP) contactors are designed to improve control of refrigeration, air conditioning, ventilation and resistance heating applications. The complete line offers everything from compact DPs to the smallest 50 ampere DP contactor in the world an average of 20% smaller than the competition. Always looking for new ways to improve the customer experience, the 50 mm (2") DP contactor with an innovative sealed housing is designed to keep out contaminants and lower noise. Building on that success, the new series of Compact DPs are now available in a sleek new sealed design. Continuing to innovate and upgrade products, we offer the perfect definite purpose solution for your **HVACR** applications.

# New Compact Models Definite Purpose Contactors

The new 30 ampere, single- and double-pole, Type C25 compact DP contactors feature a compact, efficient design with a low VA coil and straight through wiring. These devices are economically priced, UL recognized/ CSA certified, are current rated and hp/kW rated with magnet coils rated Class F, 155°C (311°F) [most are Class B, 130°C (266°F)] and designed with low VA current ratings for less energy consumption. With the ability to be mounted vertically, horizontally or tabletop, the new series of compact DPs will meet all your definite purpose application needs.







C25DND330A







K-30

# **COMPACT SERIES**

#### **SPECIFICATIONS**

#### **COMPACT MODELS**

**UL Recognized Components:** UL File number E1491, Guides NLDX2 and NLDX8

**CSA Certified Components:** CSA C22.2 No. 14-05, File number 238083 Class

3211 84 IEC: 60947-4-1 **EN**: 60947-4-1

ARI: 780/790 Standard **RoHS:** Compliant **Insulation Voltage: 690V** Current Rated and hp/kW Rated

Contacts: Double break

Magnet Coil: Class F, 155°C (311°F) Contact Arc Covers: Standard on all

contactors

Contactors are Marked with Line and **Load Terminal Designations** Operating Temperature Range: -13 to 158°F (-25 to 70°C)

#### **TERMINAL WIRE RANGE**

Hex Washer Head Screws: 16-10 AWG. 30 lb-in torque rating

**Box Lugs:** 


16-10 AWG: 35 lb-in torque rating 8 AWG: 40 lb-in torque rating 6-4 AWG: 45 lb-in torque rating Mounting Position: Vertical, horizontal

or tabletop

#### **AMPERE RATINGS**








OOIL OII	IIIAOILI	110100	
AC COIL VOLTAGE 50/60 HZ	MAX INRUSH VA	MAX SEALED VA	MAX SEALED WATTS
1-POLE			
24	33	6	2
120	33	6	2
2-POLE			
24	41	6.5	3
120	41	6.5	3
208/240	41	6.5	3

COIL CHARACTERISTICS


## **LIGHTING DUTY RATINGS** (25 TO 50 A ONLY)

C25D INDUCTIVE RATING	TUNGSTEN AND BALLAST (480V)
25 A	30 A
30 A	40 A
50 A	60 A

INDUCTIVE			LOCKED ROTOR		MAX. M HORSEF		MAX. M KILOW	
FULL LOAD	RESISTIVE	240-277V	480V	600V	115V	230V	115V	230V
SINGLE-POLE	WITH SHUNT							
30	40	150	75	50	2	5	1.5	3.7
DOUBLE-POL	.E							
30	40	150	125	100	2	5	1.5	3.7
40	50	240	200	160	3	7.5	2.2	5.5



## STANDARD SERIES



and 122201

**IEC**: 60947-4-1 EN: 60947-4-1

RoHS Compliance: 25 to 50 A only

**Magnet Coil** 

**Class F:** (C25D and L), 155°C (311°F) Class H: (C25D), 180°C (356°F) (Available as factory installed option)

Contacts: Double break Coil Terminals: 10-14 AWG **Ambient Temperature:** 65°C (150°F) maximum

Approvals: ÚL recognized, CSA certified and conform to ARI 780 CE mark

**Terminal Wire Range** 

#8-32 Screw/Pressure Plate: 1-Conductor: 14-8 AWG 2-Conductors: 14-8 AWG

**Box Lugs—15 to 50 A:** #2 posidrive screw or ½ hex socket screw

Upper Level: 14-4 AWG

(1-conductor)

Lower Level: 14-6 AWG

(1-conductor) Box Lugs—75 A

> Upper Level: 14–2 AWG Lower Level: 14-6 AWG

Note: The box lugs on the 25-75A device can accept two conductors per pole.

## LIGHTING DUTY RATINGS (25A TO 50A ONLY)

C25D INDUCTIVE RATING	TUNGSTEN AND BALLAST (480V)
25 A	30 A
30 A	40 A
50 A	60 A

### IEC/CE RATINGS (IEC 60947-4-1, EN 60947-4-1) FOR 25 TO 50 A C25D CONTACTORS

C25D_ INDUCTIVE RATING	AC-	1 (IC)	AC-	3 (IE)	AC-4	(IE)	AC	-8A
	480V	600V	480V	600V	480V	600V	480V	600V
25 A	30 A	30 A	25 A	25 A	25 A	_	25 A	25 A
30 A	40 A	40 A	30 A	30 A	30 A		30 A	30 A
50 A	65 A	65 A	50 A	50 A	50 A	_	50 A	50 A

## DC RATINGS (25 TO 50 A ONLY)


	3-POLE, 15 TO 30 A INDUCTIVE			40		OLE, DUCTIVE
	UL/CSA		UL/CSA DC-3/DC-5		CSA	DC-3/DC-5
VOLTAGE	FLA	HP	Ш	FLA	HP	IE
240 Vdc 3 Poles in Series	4.0	3/4	4.0	5.0	1.0	5.0
120 Vdc 3 Poles in Series	8.0	3/4	8.0	10.0	1.0	10.0
120 Vdc 2 Poles in Series	5.5	1/2	5.5	8.0	3/4	8.0
120 Vdc per Pole	2.0	1/10	2.0	3.5	1/4	3.5
24 Vdc per Pole	15.0		15.0	20.0	_	20.0

#### **CONTACTOR TORQUE RATINGS**

<b>CONTACTOR SIZE</b>	TERMINAL	WIRE RANGE	TIGHTENING TORQUE
	Screw/Pressure Plate	8-14 AWG	15 lb-inch
		12-14 AWG	15 lb-inch
25 to 50 A	Box Lug	10 AWG	25 lb-inch
		8 AWG	40 lb-inch
		4-6 AWG	45 lb-inch
		10-14 AWG	40 lb-inch
75 A	Box Lug	8 AWG	45 lb-inch
		3-6 AWG	50 lb-inch

**DIMENSIONS: STANDARD SERIES mm (inch)** 

Dimerion	0110. 01711	10/110	OLITIES	/	··· <i>j</i>						
AMPERE	NUMBER	WIDE	HIGH	DEEP	MOUNTING					SIDE AUXILIARY CONTACT ADDER	SHIPPING WEIGHT
SIZE	<b>OF POLES</b>	Α	В	С	D	E	F	G	H	J	KG (LBS)
25-50	2 and 3	61.0 (2.40)	95.0 (3.75)	85.0 (3.35)	83.0 (3.25)	51.0 (2.00)	_	79.0 (3.13)	38.0 (1.50)	8.6 (0.34)	0.6 (1.3)
75	2 and 3	67.0 (2.63)	95.0 (3.75)	101.0 (3.97)	83.0 (3.25)	51.0 (2.00)	38.0 (1.5)	79.0 (3.13)	38.0 (1.5)	9.5 (0.37)	1.3 (2.8)
NEMA 1 E	ENCLOSURE	Ξ									
25-50	2 and 3	104.0 (4.10)	171.0 (6.75)	89.0 (3.50)	70.0 (2.75)	124.0 (4.88)	_	_	_	_	1.5 (3.4)



To Order Visit omeg	a.com/c25 for Pricing and Details	
MODEL NO.		
COMPACT MODELS	DESCRIPTION	TERMINATION
C25CNB130A	1-pole 30 A contactor w/shunt 120 Vac coil	Binding head screw and quick connect terminals (side by side)
C25CNB130T	1-pole 30 A contactor w/shunt 24 Vac coil	Binding head screw and quick connect terminals (side by side)
C25BNB230A	2-pole 30 A contactor 120 Vac coil	Binding head screw and quick connect terminals (side by side)
C25BNB230B	2-pole 30 A contactor 240 Vac coil	Binding head screw and quick connect terminals (side by side)
C25BNB230T	2-pole 30 A contactor 24 Vac coil	Binding head screw and quick connect terminals (side by side)
C25BNF240A	2-pole 40 A contactor 120 Vac coil	Box lugs (Posidrive Setscrew) and quick connect terminals (side by side)
C25BNF240B	2-pole 40 A contactor 240 Vac coil	Box lugs (Posidrive Setscrew) and quick connect terminals (side by side)
C25BNF240T	2-pole 40 A contactor 24 Vac coil	Box lugs (Posidrive Setscrew) and quick connect terminals (side by side)

Ordering Example: C25BNB230A, 2-pole, 30 A contactor with 120 Vac coil.



MODEL NO.		
STANDARD MODELS	DESCRIPTION	TERMINATION
C25DND325A	3-pole 25 A contactor 120 Vac coil	Screw/pressure plate and quick connect terminals (side by side)
C25DND325B	3-pole 25 A contactor 240 Vac coil	Screw/pressure plate and quick connect terminals (side by side)
C25DND330A	3-pole 30 A contactor 120 Vac coil	Screw/pressure plate and quick connect terminals (side by side)
C25DND330B	3-pole 30 A contactor 240 Vac coil	Screw/pressure plate and quick connect terminals (side by side)
C25DND330T	3-pole 30 A contactor 24 Vac coil	Screw/pressure plate and quick connect terminals (side by side)
C25DNF340A	3-pole 40 A contactor 120 Vac coil	Box lugs (Posidrive Setscrew) and quick connect terminals (side by side)
C25DNF340B	3-pole 40 A contactor 240 Vac coil	Box lugs (Posidrive Setscrew) and quick connect terminals (side by side)
C25DNF340T	3-pole 40 A contactor 24 Vac coil	Box lugs (Posidrive Setscrew) and quick connect terminals (side by side)
C25DNJ350A	3-pole 50 A contactor 120 Vac coil	Box lugs (Posidrive Setscrew) and quick connect terminals (side by side)
C25DNJ350B	3-pole 50 A contactor 240 Vac coil	Box lugs (Posidrive Setscrew) and quick connect terminals (side by side)
C25DNJ350T	3-pole 50 A contactor 24 Vac coil	Box lugs (Posidrive Setscrew) and quick connect terminals (side by side)
C25FNF375A	3-pole 75 A contactor 120 Vac coil	Box lugs (Posidrive Setscrew) and quick connect terminals (side by side)
C25FNF375B	3-pole 75 A contactor 240 Vac coil	Box lugs (Posidrive Setscrew) and quick connect terminals (side by side)
C25FNF375T	3-pole 75 A contactor 24 Vac coil	Box lugs (Posidrive Setscrew) and quick connect terminals (side by side)
ACCESSORIES		
C320KG1	1 NO side auxiliary contact kit	
C320KG3	1 NO-1NC side auxiliary contact kit	
C799B18	NEMA 1 enclosure for 25 to 50 A, 2- and 3	3-pole models

Ordering Example: C25FNF375B, 3-pole, 75 A contactor with 240 Vac coil.