## **Magnetic Non-Contact Safety Switches**



## With European Industry Standard Fitting

LMR and LPR Series






















- Magnetic High Power Switching Up to 1 A
- ✓ Volt Free Contacts
- ✓ High Temperature Stability
- ✓ Wide Sensing at 12 mm (0.47") with High Tolerance to Guard Misalignment
- ✓ Will Operate with Most Safety Relays
- ✓ Popular European Fitting Suitable for All Industry Applications
- Can be High Pressure Hosed at High Temperature Due to NEMA PW12 (IP69K) Rating
- ✓ Up to: PLe ISO13849-1
- ✓ 2 NC 1 NO Circuits-High Switching Life-**No Moving Parts**
- ✓ LMR Series: 316 SS Body Mirror Polished to Ra4—Suitable for CIP and SIP Cleaning—Food Splash Zones **EHEDG Guidelines**
- ✓ LPR Series: High Specification Polyester Housing with Integral Back Plate


The LMR and LPR Series magnetic non-contact safety switches with European industry standard fitting have been designed to enable the conformance to EN60947-5-3 and be used as directed by ISO12100, ISO14121 and EN60204-1. They have magnetic sensing which provides a wide sensing distance and provides a high tolerance to misalignment after sensing. They can operate from 4 directions even in extreme environments of temperature and moisture. They have volt free high power switching capability and can be used independently to switch low risk applications or connect to a safety relay to provide higher safety levels. When used in combination with most dual channel safety monitoring relays they can be used to provide up to PLe/Category 4 to ISO13849-1.

LMR and LPR Series magnetic non-contact safety switches are designed to interlock hinged, sliding or removable guard doors. LMR Series stainless steel safety switches have been designed for applications in the food processing, pharmaceutical, packaging and petrochemical industries. LPR Series switches have been developed for applications in general factory automation, packaging and some food processing industries.

They are specifically advantageous when:

- Poor guard alignment exists and a wide tolerance to misalignment is required
- High levels of hygiene is a requirement, e.g. high pressure chemical or water hosing in the food industry environment
- Environments where high switching capacity is a requirement





## **Specifications**

Standards: ISO14119, EN60947-5-1, EN60204-1, ISO13849-1,

EN62061, UL508

Safety Classification and Reliability Data:

Mechanical Reliability B10d: 3.3 x 106 operations

at 100 mA load

ISO13849-1: Up to PLe Category 4 depending upon system

architecture

**EN62061:** Up to SIL3 depending upon system architecture

Safety Data - Annual Usage: 8 cycles per hour/24 hours per

day/365 days **PFHd:** 2.52 x 10<sup>-8</sup>

Proof Test Interval (Life): 47 years

MTTFd: 470 years

Safety Channel 1 NC: Voltage free, 250 Vac 1.0 A max rating Safety Channel 2 NC: Voltage free, 250 Vac 1.0 A max rating Safety Channel 3 NO: Voltage free, 24 Vdc 0.2 A max rating

Fuse: Internal 1.0 A (F); External 0.8 A (F) (User)

Contact Release Time: <2 ms Initial Contact Resistance: <500 m $\Omega$  Minimum Switched Current: 10 Vdc, 1 mA

Dielectric: Withstand 250 Vac Insulation Resistance: 100  $M\Omega$ 

Recommended Setting Gap: 5 mm (0.2") Switching Distance: Sao 10 mm (0.4") Close (Target to Target): Sar 20 mm (0.8") Open

Tolerance to Misalignment: 5 mm (0.2") in any direction from

5 mm (0.2") setting gap

Switching Frequency: 1.0 Hz maximum

Approach Speed: 200 mm/min to 1000 mm/sec

**Body Material:** 

LMR Series: 316 SS mirror polished finish to Ra4

LPR Series: UL approved polyester

**Operating Temperature:** 

LMR Series (CIP SIP Cleaning): -25 to 105°C (-13 to 221°F)

LPR Series: -25 to 80°C (-13 to 176°F)

Enclosure Protection: NEMA PW12 (IP69K), NEMA 6 (IP67)

Shock Resistance: IEC68-2-27; 11 ms, 30 g

**Vibration Resistance:** IEC68-2-6; 10 to 55 Hz, 1 mm **Cable Type:** PVC 6 core, 6 mm (0.23") OD; conductors,

0.25 mm<sup>2</sup>

Mounting Bolts: 2 x M4; tightening torque, 1.0 Nm

Mounting Position: Any

**Dimensions:** See dimensional drawing above **Weight (of Switch, Actuator and Cable):** 

**LMR Series:** 435 g (0.96 lb) with 5 m (16.4') cable;

685 g (1.51 lb) with 10 m (32.8') cable

**LPR Series:** 330 g (0.73 lb) with 5 m (16.4') cable;

580 g (1.28 lb) with 10 m (32.8') cable

To Order			
Model No.	Description	Circuits	Cable Length
LMR-133014	Stainless steel magnetic non-contact safety switch with European fitting	2 NC (safety) 1 NO (auxiliary)	5 m (16.4')
LMR-133015	Stainless steel magnetic non-contact safety switch with European fitting	2 NC (safety) 1 NO (auxiliary)	10 m (32.8')
LPR-110014	Magnetic non-contact safety switch with European fitting	2 NC (safety) 1 NO (auxiliary)	5 m (16.4')
LPR-110015	Magnetic non-contact safety switch with European fitting	2 NC (safety) 1 NO (auxiliary)	10 m (32.8')

All switches include actuator.

**Ordering Example: LPR-110014** magnetic non-contact safety switch with European fitting, 2 NC (safety) and 1 NO (auxiliary) circuits and 5 m (16.4') cable.