PRE-CUT FRONT PANELS FOR DIN METERS AND CONTROLLERS FOR NEMA 4X FIBERGLASS ENCLOSURES

OM-HFPU Series

- Aluminum Hinged Front Panels
- Cut-Outs for ½2, ¼6, ¼ and¼ DIN Size Controllers
- Easy Field-Installed Panel Kit
- Stainless Steel Hardware
- Latch Design Secures Panel in Place with ¼ Turn


Pre-Cut Panel Kits

These front panels are 2 mm (0.090") thick aluminum and are pre-cut for up to 4 DIN size controllers, depending on the size of the enclosure. The kits are simple to assemble requiring drilling three holes with the provided template. All stainless steel hardware is included along with installation instructions. These kits are available for two NEMA 4X fiberglass enclosure models, 0.3 H x 0.25 W x 0.15 m D (12 x 10 x 6") and 0.40 H x 0.35 W x 0.20 m D (16 x 14 x 8"). Rear sub-panels are also available for mounting additional electrical components.

Enclosures

OM-AMU series non-metallic fiberglass enclosures are designed to insulate and protect electrical controls and components in both indoors and outdoors applications and are especially well suited for higher temperatures and corrosive environments. These NEMA 4X (IP66) fiberglass JIC junction boxes feature clear polycarbonate covers with a variety of screw or latching options.









OM-HFPU120-116DIN-2 shown installed in OM-AMU1206LCCF fiberglass enclosure with two CNi Series % DIN controllers, shown much smaller than actual size.

FRONT PANELS WITH DIN CUT-OUTS

FRUNT FANELS WITH DIN COT-0015				
To Order	•			
MODEL NO.	PANEL CUT-OUTS	DIN SIZE		
FRONT PANELS FOR 0.3 H x 0.25 W x 0.15 m D (12 x 10 x 6") FIBERGLASS ENCLOSURES				
OM-HFPU120-132DIN-1	One	1/32		
OM-HFPU120-132DIN-2	Two	1/32		
OM-HFPU120-116DIN-1	One	1/16		
OM-HFPU120-116DIN-2	Two	1/16		
OM-HFPU120-18DIN-1	One	1/8		
OM-HFPU120-18DIN-2	Two	1/8		
OM-HFPU120-14DIN-1	One	1/4		
FRONT PANELS FOR 0.40 H x 0.35 W x 0.20 m D (16 x 14 x 8") FIBERGLASS ENCLOSURES				
OM-HFPU164-132DIN-1	One	1/32		
OM-HFPU164-132DIN-2	Two	1/32		
OM-HFPU164-132DIN-3	Three	1/32		
OM-HFPU164-116DIN-1	One	1/16		
OM-HFPU164-116DIN-2	Two	1/16		
OM-HFPU164-116DIN-3	Three	1/16		
OM-HFPU164-18DIN-1	One	1/8		
OM-HFPU164-18DIN-2	Two	1/8		
OM-HFPU164-14DIN-1	One	1/4		
OM-HFPU164-14DIN-2	Two	1/4		

NEMA 4X FIBERGLASS ELECTRICAL ENCLOSURES

MODEL NO.	DESCRIPTION	DIMENSIONS
OM-AMU1206CCHF	Hinge and screw closure	12 H x 10 W x 6" D
OM-AMU1206LCCF	Hinge and snap latch cover	12 H x 10 W x 6" D
OM-AMU1206TCCF	Hinge and twist latch cover	12 H x 10 W x 6" D
OM-AMU1648CCHF	Hinge and screw closure	16 H x 14 W x 8" D
OM-AMU1648LCCF	Hinge and snap latch cover	16 H x 14 W x 8" D
OM-AMU1648TCCF	Hinge and twist latch cover	16 H x 14 W x 8" D

ACCESSORIES

MODEL NO.	DESCRIPTION	
OM-AMPOLEMNT-10	Pole mount kit for 0.25 m (10") wide fiberglass enclosure	
OM-AMPOLEMNT-14	Pole mount kit for 0.35 m (14") wide fiberglass enclosure	
SCE-12P10	Steel sub-panel (rear) for 0.3 x 0.25 m (12 x 10") enclosure	
SCE-16P14	Steel sub-panel (rear) for 0.40 x 0.35 m (16 x 14") enclosure	

Comes complete with installation instructions.

Ordering Examples: OM-HFPU120-132DIN-2, front panel with two cut-outs for $^{1}/_{32}$ DIN controllers or meters, and OM-AMU1206LCCF, NEMA 4X fiberglass enclosure with snap latches, 12 H x 10 W x 6" D.

OM-HFPU164-116DIN-3, front panel with three cut-outs for $\frac{1}{16}$ DIN controllers or meters, **OM-AMU1648LCCF**, NEMA 4X fiberglass enclosure with snap latches, 16 H x 14 W x 8" D, and **SCE-16P14**, rear sub-panel for 0.40 x 0.35 m (16 x 14") enclosure.